

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002067103**
Status: **Active**
Overview: Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Description: 1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with 2.54µm Tin (Sn) Plated Brass Contact, Bag Packaged

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	1779
Application	Power, Wire-to-Wire
Comments	PC Tail Brass for Standard .062" Housing
Crimp Quality Equipment	Yes
Overview	<u>Standard .062"+ and Standard .062" Pin and Socket Connector Systems</u>
Product Name	Standard .062"
UPC	800753618404

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.160/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.00mm max.
Wire Size AWG	N/A
Wire Size mm ²	N/A

Material Info

Engineering Number 1779-(P909)L

Reference - Drawing Numbers

Packaging Specification PK-1190-003-001
 Sales Drawing SD-1779-X-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

1779 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	11030002
---	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[02-06-7103](#)