


STPS3L40


Datasheet

40 V, 3 A low drop Schottky rectifier



SMB Flat

SMB Flat Notch



Features

- Negligible switching losses
- Low forward voltage drop
- Low thermal resistance
- Avalanche rated
- ECOPACK2 component

Applications

- Telecom power supply
- Set-top box power supply
- TV power supply
- Battery charger

Description

Schottky rectifier suited for switch mode power supplies and high frequency DC to DC converters.

Packaged in SMB Flat Notch, SMB Flat and SMC, the STPS3L40 is ideal for surface mounting and used in DC/DC chargers.

Product status					
STPS	STPS3L40				
Product summary					
Symbol Value					
I _{F(AV)}	3 A				
V _{RRM}	40 V				
T _{j(max.)}	150 °C				
V _{F(typ.)}	0.40 V				

1 Characteristics

Symbol	Parameter		Value	Unit	
V _{RRM}	Repetitive peak reverse voltage				V
	Average forward current, $\delta = 0.5$, square	SMB Flat, SMB Flat Notch	T _L = 120 °C	2	
F(AV) wave	SMC	T _L = 115 °C	- 3	A	
I _{FSM}	Surge non repetitive forward current t_p = 10 ms sinusoidal				Α
P _{ARM}	Repetitive peak avalanche power $t_p = 10 \ \mu s, T_j = 125 \ ^{\circ}C$			95	W
T _{stg}	Storage temperature range	-65 to +150	°C		
Тj	Maximum operating junction temperature ⁽¹⁾				°C

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)

1. $(dP_{tot'}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 2. Thermal resistance parameter

Symbol	Parameter		Max. value	Unit
Paran	lupation to load	SMB Flat, SMB Flat Notch	15	°C/W
r×tn(j−i)	R _{th(j-l)} Junction to lead	SMC	18	C/VV

For more information, please refer to the following application note :

AN5088 : Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I_ (1)	Poveraa lookaga eurrant	T _j = 25 °C	V _R = V _{RRM}	-		100	μA
IR	I _R ⁽¹⁾ Reverse leakage current	T _j = 125 °C		-	16	40	mA
		T _j = 25 °C	I _F = 3 A	-		0.50	
V _E ⁽¹⁾	Forward voltage drap	T _j = 125 °C		-	0.40	0.44	V
VF	Forward voltage drop	T _j = 25 °C	I _F = 6 A	-		0.62	v
		T _j = 125 °C		-	0.52	0.58	

1. Pulse test: $t_p = 380 \ \mu s, \ \delta < 2\%$


To evaluate the conduction losses, use the following equation:


 $P = 0.30 \text{ x } I_{F(AV)} + 0.047 \text{ x } I_{F}^{2}(RMS)$

For more information, please refer to the following application notes related to the power losses :


- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode


1.1 **Characteristics (curves)**





























DS194	17 - Rev 5
Downloaded from	Arrow.com.

2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 SMB Flat package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 12. SMB Flat package outline





Table 4. SMB Flat mechanical data

			Di	mensions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	0.90		1.10	0.035		0.044
b	1.95		2.20	0.076		0.087
С	0.15		0.40	0.005		0.016
D	3.30		3.95	0.129		0.156
E	5.10		5.60	0.200		0.221
E1	4.05		4.60	0.159		0.182
L	0.75		1.50	0.029		0.060
L1		0.40			0.016	
L2		0.60			0.024	









2.2 SMB Flat Notch package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 14. SMB Flat Notch package outline





	Dimensions						
Ref.		Millimeters		Inches			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А	0.90		1.10	0.035		0.043	
A1		0.05			0.002		
b	1.95		2.20	0.077		0.087	
С	0.15		0.40	0.006		0.016	
D	3.30		3.95	0.130		0.156	
E	5.20		5.60	0.205		0.220	
E1	4.05		4.60	0.159		0.181	
G		2.00			0.079		
G1		1.20			0.047		
L	0.75		1.20	0.030		0.047	
L1		0.30			0.012		
L2		0.60			0.024		
L3	0.02			0.001			
V			8°			8°	
V1			8°			8°	

Table 5. SMB Flat Notch mechanical data




Figure 15. Footprint recommendations, dimensions in mm (inches)

2.3 SMC package information

57

• Epoxy meets UL94, V0

Figure 16. SMC package outline





Table 6. SMC package mechanical data

	Dimensions					
Ref.	Millin	neters	Inches (for reference only)			
	Min.	Max.	Min.	Max.		
A1	1.90	2.45	0.0748	0.0965		
A2	0.05	0.20	0.0020	0.0079		
b	2.90	3.20	0.1142	0.1260		
с	0.15	0.40	0.0059	0.0157		
D	5.55	6.25	0.2185	0.2461		
E	7.75	8.15	0.3051	0.3209		
E1	6.60	7.15	0.2598	0.2815		
E2	4.40	4.70	0.1732	0.1850		
L	0.75	1.50	0.0295	0.0591		

Figure 17. SMC recommended footprint



3 Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS3L40UFN	B34	SMB Flat Notch	0.056 g	5 000	Tape and reel
STPS3L40UF	FS3L4	SMB Flat	0.050 g	5000	Tape and reel
STPS3L40S	S3L4	SMC	0.243 g	10 000	Tape and reel

Table 7. Ordering information

Revision history

Date	Version	Changes
Jul-2003	2A	Last update.
08-Feb-2007	3	Reformatted to current standard. Added ECOPACK statement. Added SMBflat package.
20-May-2013	4	Updated SMC package information. Updated ECOPACK statement. Corrected Y axis labels of Figure 12.
31-Jan-2020	5	Added Section 2.2 SMB Flat Notch package information.

Table 8. Document revision history



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved