

## STTH1R02

### Ultrafast recovery diode

#### Main product characteristics

I <sub>F(AV)</sub>	1.5 A
V <sub>RRM</sub>	200 V
T <sub>j</sub> (max)	175° C
V <sub>F</sub> (typ)	0.7 V
t <sub>rr</sub> (typ)	15 ns


#### Features and benefits

- Very low conduction losses
- Negligible switching losses
- Low forward and reverse recovery times
- High junction temperature

#### **Description**

The STTH1R02 uses ST's new 200 V planar Pt doping technology, and it is specially suited for switching mode base drive and transistor circuits.

Packaged in DO-41, DO-15, SMA, and SMB, this device is intended for use in low voltage, high frequency inverters, free wheeling and polarity protection.



#### **Order codes**

Part Number	Marking
STTH1R02	STTH1R02
STTH1R02RL	STTH1R02
STTH1R02A	R1A
STTH1R02Q	STTH1R02Q
STTH1R02QRL	STTH1R02Q
STTH1R02U	1R2S

**Characteristics** STTH1R02

## **Characteristics**

Absolute ratings (limiting values at  $T_i$  = 25° C, unless otherwise specified) Table 1.

Symbol	Parameter			Value	Unit
V <sub>RRM</sub>	Repetitive peak reverse voltage			200	V
I <sub>FRM</sub>	Repetitive peak forward current	DO-41 <sup>(1)</sup> DO-15 <sup>(1)</sup> SMA / SMI	t <sub>p</sub> = 5 μs, F = 5 kHz	30	А
I <sub>F(RMS)</sub>	RMS forward current	DO-41 / DO-15 SMA /SMB		50	Α
		DO-41	T <sub>lead</sub> = 110° C T <sub>lead</sub> = 110° C		
I <sub>F(AV)</sub>	Average forward current, $\delta = 0.5$	SMA SMB	$T_{c} = 110^{\circ} \text{ C}$ $T_{c} = 110^{\circ} \text{ C}$	1.5	Α
I <sub>FSM</sub>	Surge non repetitive forward current			60	Α
T <sub>stg</sub>	Storage temperature range			-65 to + 175	ç
T <sub>j</sub>	Maximum operating junction temperature			175	°C

<sup>1.</sup> On infinite heatsink with 10 mm lead length

Table 2. Thermal parameters

Symbol		Parameter			
В	lunation to load	Load Longth - 10 mm on infinite heateink	DO-41	45	
nth(j-l)	R <sub>th(j-l)</sub> Junction to lead	Lead Length = 10 mm on infinite heatsink	DO-15	45	°C/W
В	lunation to acco		SMA	30	C/VV
$R_{th(j-c)}$ Junction to case			SMB	30	

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур	Max.	Unit
I <sub>R</sub> <sup>(1)</sup>	Reverse leakage current	current $ \frac{T_j = 25^{\circ} \text{ C}}{T_j = 125^{\circ} \text{ C}} \text{ V}_{\text{R}} = \text{V}_{\text{RRM}} $			3		
'R`				2	20	μΑ	
		T <sub>j</sub> = 25° C	I <sub>F</sub> = 4.5 A			1.2	
V (2)	V <sub>F</sub> <sup>(2)</sup> Forward voltage drop	T <sub>j</sub> = 25° C			0.89	1	V
VF` ′		T <sub>j</sub> = 100° C	I <sub>F</sub> = 1.5 A		0.76	0.85	V
		T <sub>j</sub> = 150° C			0.70	0.80	

<sup>1.</sup> Pulse test:  $t_p$  = 5 ms,  $\delta$  < 2 %

To evaluate the conduction losses use the following equation: P = 0.68 x  $I_{F(AV)}$  + 0.08  $I_{F}^{2}_{(RMS)}$ 

$$P = 0.68 \times I_{E(AV)} + 0.08 I_{E}^{2} (DMS)$$

<sup>2.</sup> Pulse test:  $t_p$  = 380  $\mu$ s,  $\delta$  < 2 %

STTH1R02 Characteristics

Table 4. Dynamic characteristics

Symbol	Parameter	Test conditions	Min.	Тур	Max.	Unit
+	Reverse recovery time	$I_F$ = 1 A, $dI_F/dt$ = -50 A/ $\mu$ s, $V_R$ = 30 V, $T_j$ = 25° C		23	30	ns
t <sub>rr</sub>	Heverse recovery time	$I_F = 1 \text{ A, } dI_F/dt = -100 \text{ A/}\mu\text{s,}$ $V_R = 30 \text{ V, } T_j = 25^{\circ} \text{ C}$		15	20	115
I <sub>RM</sub>	Reverse recovery current	$I_F = 1.5 \text{ A}, dI_F/dt = -200 \text{ A/}\mu\text{s}, \ V_R = 160 \text{ V}, T_j = 125^{\circ} \text{ C}$		3	4	Α
t <sub>fr</sub>	Forward recovery time	$I_F = 1.5 \text{ A}, dI_F/dt = 100 \text{ A/}\mu\text{s}$ $V_{FR} = 1.1 \text{ x } V_{Fmax}, T_j = 25^{\circ} \text{ C}$		50		ns
V <sub>FP</sub>	Forward recovery voltage	$I_F = 1.5 \text{ A}, dI_F/dt = 100 \text{ A/}\mu\text{s},$ $T_j = 25^{\circ} \text{ C}$		2.1		<b>V</b>

Figure 1. Peak current versus duty cycle

Figure 2. Forward voltage drop versus forward current (typical values)





Figure 3. Forward voltage drop versus forward current (maximum values)

Figure 4. Relative variation of thermal impedance junction to case versus pulse duration (SMA)



Characteristics STTH1R02

Figure 6.

Figure 5. Relative variation of thermal impedance junction to case versus pulse duration (SMB)

1.0

0.9

0.8

0.7

0.6

0.3

0.2

0.1

0.0

1.E-02

1.E-01



Relative variation of thermal impedance junction to case versus pulse duration (DO-41)





Figure 7. Relative variation of thermal impedance junction to case versus pulse duration (DO-15)

1.E+01

1.E+02

1.E+00

Figure 8. Junction capacitance versus reverse applied voltage (typical values)






Figure 9. Reverse recovery charges versus dl<sub>F</sub>/dt (typical values)





Figure 10. Reverse recovery time versus dl<sub>F</sub>/dt (typical values)



STTH1R02 Characteristics

Figure 11. Peak reverse recovery curent versus dl<sub>E</sub>/dt (typical values)




Figure 12. Dynamic parameters versus junction temperature





Figure 13. Thermal resistance, junction to ambient, versus copper surface under each lead - SMA (Epoxy FR4, copper thickness = 35 µm)

Figure 14. Thermal resistance, junction to ambient, versus copper surface under each lead - SMB (Epoxy FR4, copper thickness = 35 μm)









Figure 15. Thermal resistance, junction to ambient, versus copper surface under each lead - DO 15 (Epoxy FR4, copper thickness = 35 μm)

Figure 16. Thermal resistance, junction to ambient, versus copper surface under each lead - DO-41 (Epoxy FR4, copper thickness = 35 μm)






## 2 Ordering information scheme



## 3 Package information


Epoxy meets UL94, V0

Table 5. DO-41 dimensions



	Dimensions				
Ref.	Millim	neters	Inc	hes	
	Min.	Max.	Min.	Max.	
Α	4.1	5.20	0.160	0.205	
В	2	2.71	0.080	0.107	
С	25.4		1		
D	0.712	0.863	0.028	0.034	

Table 6. DO-15 dimensions




	Dimensions			
Ref.	Millimeters		Inc	hes
	Min.	Max.	Min.	Max.
Α	6.05	6.75	0.238	0.266
В	2.95	3.53	0.116	0.139
С	26	31	1.024	1.220
D	0.71	0.88	0.028	0.035

577


STTH1R02 Package information

Table 7. SMA dimensions




	DIMENSIONS				
REF.	Millim	neters	Inc	hes	
	Min.	Max.	Min.	Max.	
A1	1.90	2.03	0.075	0.080	
A2	0.05	0.20	0.002	0.008	
b	1.25	1.65	0.049	0.065	
С	0.15	0.41	0.006	0.016	
Е	4.80	5.60	0.189	0.220	
E1	3.95	4.60	0.156	0.181	
D	2.25	2.95	0.089	0.116	
L	0.75	1.60	0.030	0.063	

Figure 17. SMA footprint (dimensions in mm)




Package information STTH1R02

Table 8. SMB dimensions



	Dimensions			
Ref.	Millim	neters	Inc	hes
	Min.	Max.	Min.	Max.
A1	1.90	2.45	0.075	0.096
A2	0.05	0.20	0.002	0.008
b	1.95	2.20	0.077	0.087
С	0.15	0.41	0.006	0.016
Е	5.10	5.60	0.201	0.220
E1	4.05	4.60	0.159	0.181
D	3.30	3.95	0.130	0.156
L	0.75	1.60	0.030	0.063

Figure 18. SMB footprint (dimensions in mm)



In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a lead-free second level interconnect. The category of second level interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com.

# 4 Ordering information

Part Number	Marking	Package	Weight	Base qty	Delivery mode
STTH1R02	STTH1R02	DO-41	0.34 g	2000	Ammopack
STTH1R02RL	STTH1R02	DO-41	0.34 g	5000	Tape and reel
STTH1R02A	R1A	SMA	0.068 g	5000	Tape and reel
STTH1R02Q	STTH1R02Q	DO-15	0.49 g	1000	Ammopack
STTH1R02QRL	STTH1R02Q	DO-15	0.49 g	6000	Tape and reel
STTH1R02U	1R2S	SMB	0.11 g	2500	Tape and reel

# 5 Revision history

Date	Revision	Description of changes
03-May-2006	1	First issue
13-Oct-2006	2	Added DO-15 and SMB packages.
08-Mar-2007	3	Replaced Figure 8. Replaced e <sub>cu</sub> with copper thickness.

**577** 

#### Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

577