ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI: and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application is provided for uses as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi roducts for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs

Analog Multiplexers / Demultiplexers

The MC14067 multiplexer/demultiplexer is a digitally controlled analog switch featuring low ON resistance and very low leakage current. This device can be used in either digital or analog applications.

The MC14067 is a 16–channel multiplexer/demultiplexer with an inhibit and four binary control inputs A, B, C, and D. These control inputs select 1–of–16 channels by turning ON the appropriate analog switch (see MC14067 truth table.)

Features

- Low OFF Leakage Current
- Matched Channel Resistance
- Low Quiescent Power Consumption
- Low Crosstalk Between Channels
- Wide Operating Voltage Range: 3 to 18 V
- Low Noise
- Pin for Pin Replacement for CD4067B
- These Devices are Pb-Free and are RoHS Compliant
- NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q100 Qualified and PPAP Capable

MAXIMUM RATINGS (Voltages Referenced to VSS)

Symbol	Parameter	Value	Unit
V _{DD}	DC Supply Voltage Range	– 0.5 to + 18.0	V
V _{in} , V _{out}	Input or Output Voltage Range (DC or Transient)	– 0.5 to V _{DD} + 0.5	V
l _{in}	Input Current (DC or Transient), per Control Pin	±10	mA
I _{sw}	Switch Through Current	±25	mA
PD	Power Dissipation, per Package (Note 1)	500	mW
T _A	Ambient Temperature Range	– 55 to + 125	°C
T _{stg}	Storage Temperature Range	– 65 to + 150	°C
TL	Lead Temperature (8–Second Soldering)	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Temperature Derating:

Plastic "P and D/DW" Packages: - 7.0 mW/°C From 65°C To 125°C

This device contains protection circuitry to guard against damage due to high static voltages or electric fields. However, precautions must be taken to avoid applications of any voltage higher than maximum rated voltages to this high-impedance circuit. For proper operation, V_{in} and V_{out} should be constrained to the range $V_{SS} \leq (V_{in} \text{ or } V_{out}) \leq V_{DD}.$

Unused inputs must always be tied to an appropriate logic voltage level (e.g., either V_{SS} or V_{DD}). Unused outputs must be left open.



ON Semiconductor®

http://onsemi.com



SOIC-24 DW SUFFIX CASE 751E

MARKING DIAGRAM



A = Assembly Location

WL = Wafer Lot

YY = Year

WW = Work Week

G = Pb-Free Package

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.


TRI	JTH	TAB	LE
-----	-----	-----	----

	Selected							
Α	В	С	D	Inh	Channel			
Х	Х	Х	Х	1	None			
0	0	0	0	0	X0			
1	0	0	0	0	X1			
0	1	0	0	0	X2			
1	1	0	0	0	ХЗ			
0	0	1	0	0	X4			
1	0	1	0	0	X5			
0	1	1	0	0	X6			
1	1	1	0	0	X7			
0	0	0	1	0	X8			
1	0	0	1	0	X9			
0	1	0	1	0	X10			
1	1	0	1	0	X11			
0	0	1	1	0	X12			
1	0	1	1	0	X13			
0	1	1	1	0	X14			
1	1	1	1	0	X15			


PIN ASSIGNMENT

хC	1•	24] V _{DD}
X7 [2	23] X8
X6 [3	22] X9
X5 [4	21] X10
X4 [5	20] X11
X3 [6	19] X12
X2 [7	18	X13
X1 [8	17] X14
X0 [9	16] X15
Α	10	15] INHIBIT
В	11	14] C
v _{ss} [12	13] D

FUNCTIONAL DIAGRAM



16-Channel Analog Multiplexer/Demultiplexer



ELECTRICAL CHARACTERISTICS

				– 55°C		– 55°C 25°C			125°C			
Characteristic	Symbol	V_{DD}	Test Conditions	Min	Max	Min	Typ ⁽²⁾	Max	Min	Max	Unit	
SUPPLY REQUIREMENTS	(Voltages	Refere	nced to V _{SS})	1	1				1			
Power Supply Voltage Range	V _{DD}	-		3.0	18	3.0	_	18	3.0	18	V	
Quiescent Current Per Package	I _{DD}	5.0 10 15	$\begin{array}{l} \mbox{Control Inputs: $V_{in =}$} \\ V_{SS} \mbox{ or } V_{DD}, \\ \mbox{Switch I/O: } V_{SS} \leq V_{I/O} \leq \\ V_{DD}, \mbox{ and } \\ \Delta V_{switch} \leq 500 \mbox{ mV } \end{tabular} \end{array}$		5.0 10 20		0.005 0.010 0.015	5.0 10 20	- -	150 300 600	μA	
Total Supply Current (Dynamic Plus Quiescent, Per Package	I _{D(AV)}	5.0 10 15	T _A = 25°C only (The channel component, (V _{in} – V _{out})/R _{on} , is not included.)	(0.07 μA/kHz) f + I _{DD} Typical (0.20 μA/kHz) f + I _{DD} (0.36 μA/kHz) f + I _{DD}				μΑ				
CONTROL INPUTS — INH	IBIT, A, B,	C , D (∖	/oltages Referenced to V _{SS})	1	1	r	1	r			1	
Low-Level Input Voltage	V _{IL}	5.0 10 15	R _{on} = per spec, I _{off} = per spec	- - -	1.5 3.0 4.0	_ _ _	2.25 4.50 6.75	1.5 3.0 4.0	- - -	1.5 3.0 4.0	V	
High-Level Input Voltage	V _{IH}	5.0 10 15	R _{on} = per spec, I _{off} = per spec	3.5 7.0 11		3.5 7.0 11	2.75 5.50 8.25	_ _ _	3.5 7.0 11	- - -	V	
Input Leakage Current	l _{in}	15	V _{in} = 0 or V _{DD}	-	± 0.1	-	±0.00001	± 0.1	-	1.0	μA	
Input Capacitance	C _{in}			-	-	-	5.0	7.5	_	-	pF	
SWITCHES IN/OUT AND C	OMMONS	OUT/II	N — X, Y (Voltages Referen	ced to \	√ _{SS})							
Recommended Peak-to- Peak Voltage Into or Out of the Switch	V _{I/O}	_	Channel On or Off	0	V _{DD}	0	-	V _{DD}	0	V _{DD}	V _{p-p}	
Recommended Static or Dynamic Voltage Across the Switch ⁽³⁾ (Figure 1)	ΔV_{switch}	_	Channel On	0	600	0	-	600	0	300	mV	
Output Offset Voltage	V _{OO}	-	V _{in} = 0 V, No Load	-	-	-	10	-	-	-	μV	
ON Resistance	R _{on}	5.0 10 15	$\begin{array}{l} \Delta V_{\text{switch}} \leq 500 \text{ mV} \ ^{(3)}, \\ V_{\text{in}} = V_{\text{IL}} \text{ or } V_{\text{IH}} \\ (\text{Control}), \text{ and } V_{\text{in}} \\ 0 \text{ to } V_{\text{DD}} \ (\text{Switch}) \end{array}$	- - -	800 400 220	- - -	250 120 80	1050 500 280		1300 550 320	Ω	
∆ON Resistance Between Any Two Channels in the Same Package	ΔR_{on}	5.0 10 15		- - -	70 50 45	- - -	25 10 10	70 50 45	- - -	135 95 65	Ω	
Off-Channel Leakage Current (Figure 2)	I _{off}	15	V _{in} = V _{IL} or V _{IH} (Control) Channel to Channel or Any One Channel	-	± 100	_	± 0.05	±100	_	±1000	nA	
Capacitance, Switch I/O	C _{I/O}	-	Inhibit = V _{DD}	-	_	—	10	_	_	-	pF	
Capacitance, Common O/I	C _{O/I}	-	Inhibit = V _{DD} (MC14067B) (MC14097B)				100 60		-		рF	
Capacitance, Feedthrough (Channel Off)	C _{I/O}		Pins Not Adjacent Pins Adjacent	-	-	-	0.47	-	-	-	pF	

Data labeled "Typ" is not to be used for design purposes, but is intended as an indication of the IC's potential performance.
For voltage drops across the switch (ΔV_{switch}) > 600 mV (> 300 mV at high temperature), excessive V_{DD} current may be drawn; i.e. the current out of the switch may contain both V_{DD} and switch input components. The reliability of the device will be unaffected unless the Maximum Ratings are exceeded. (See first page of this data sheet.)

ELECTRICAL CHARACTERISTICS (C_L = 50 pF, T_A = 25° C)

Characteristic	Symbol	V _{DD} – V _{SS} Vdc	Typ ⁽⁴⁾	Max	Unit
Propagation Delay Times Channel Input-to-Channel Output (R _L = 200 kΩ)	t _{PLH} , t _{PHL}				ns
MC14067B	(Figure 3)	5.0	35	90	
	,	10	15	40	
		15	12	30	
Propagation Delay Times Channel Input-to-Channel Output (R _L = 1.0 kΩ)	t _{PLH} , t _{PHL}				ns
MC14067B	(Figure 3)	5.0		50	
		10		30	
		15		20	
Control Input-to-Channel Output					ns
Channel Turn–On Time ($R_L = 10 \text{ k}\Omega$) MC14067B		5.0	240	600	
MOTOD		10	115	290	
	t _{PZH} , t _{PZL}	15	75	190	
Channel Turn–Off Time (R _L = 300 kΩ) MC14067B	(Figure 4)				ns
WO 14001 B		5.0	250	625	
		10	120	300	
	t_{PHZ}, t_{PLZ}	15	75	190	
Channel Turn-Off Time (R _L = 10 kΩ) MC14067B	(Figure 4)				ns
		5.0		625	
		10		450	
		15		350	
Any Pair of Address Inputs to Output MC14067B	t _{PLH} , t _{PHL}				ns
		5.0	280	700	
		10	115	290	
		15	85	215	
Second Harmonic Distortion (R _L = 10 kΩ, f = 1 kHz, V _{in} = 5 V _{p−p})	_	10	0.3	_	%
ON Channel Bandwidth	BW				MHz
	(Figure 5)	10	15	-	
Off Channel Feedthrough Attenuation	-	10	- 40	-	dB
$[\text{R}_{\text{L}} = 50 \ \Omega, \ \text{V}_{\text{in}} = 1/2 \ (\text{V}_{\text{DD}} - \text{V}_{\text{SS}})_{p-p} (\text{sine-wave})] \\ \text{f}_{\text{in}} = 20 \ \text{MHz} - \text{MC14067B}$	(Figure 5)				
Channel Separation [R _L = 1 kΩ, V _{in} = 1/2 (V _{DD} -V _{SS}) _{p-p} (sine-wave)]	-	10	- 40	_	dB
$[n_{L} = 1 \text{ ksz}, v_{in} = 1/2 (v_{DD} - v_{SS})_{p-p} (sine-wave)]$ $f_{in} = 20 \text{ MHz}$	(Figure 6)				
Crosstalk, Control Inputs-to-Common O/I (R1 = 1 k Ω , R _L = 10 k Ω ,	_	10	30	-	mV
Control $t_r = t_f = 20$ ns, Inhibit = V _{SS})	(Figure 7)				


4. Data labelled "Typ" is not to be used for design purposes but is intended as an indication of the IC's potential performance.

ORDERING INFORMATION

Device	Package	Shipping [†]		
MC14067BDWG	SOIC-24	30 Units / Rail		
NLV14067BDWG*	(Pb-Free)			
MC14067BDWR2G	SOIC-24	1000 Units / Tape & Reel		
NLV14067BDWR2G*	(Pb-Free)			

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.







Figure 1. ΔV Across Switch










Figure 4. Turn-On and Delay Turn-Off Test Circuit and Waveforms

A, B, and C inputs used to turn ON or OFF the switch under test.




Figure 5. Bandwidth and Off-Channel Feedthrough Attenuation




Figure 6. Channel Separation (Adjacent Channels Used for Setup)




Figure 7. Crosstalk, Control to Common O/I




Figure 8. Channel Resistance (R_{ON}) Test Circuit





Figure 9. Propagation Delay, Any Pair of Address Inputs to Output

TYPICAL RESISTANCE CHARACTERISTICS



APPLICATIONS INFORMATION

Figure A illustrates use of the Analog Multiplexer / Demultiplexer. The 0–to–5 V Digital Control signal is used to directly control a 5 V_{p-p} analog signal.

The digital control logic levels are determined by V_{DD} and V_{SS} . The V_{DD} voltage is the logic high voltage; the V_{SS} voltage is logic low. For the example. $V_{DD} = +5$ V = logic high at the control inputs; $V_{SS} = GND = 0$ V = logic low.

The maximum analog signal level is determined by V_{DD} and V_{SS} . The analog voltage must swing neither higher than V_{DD} nor lower than V_{SS} . The example shows a 5 V_{p-p} signal which allows no margin at either peak. If voltage transients above V_{DD} and/or below V_{SS} are anticipated on the analog channels, external diodes (D_x) are recommended as shown in Figure B. These diodes should be small signal types able to absorb the maximum anticipated current surges during clipping.

The absolute maximum potential difference between V_{DD} and V_{SS} is 18.0 volts. Most parameters are specified up to 15 V which is the recommended maximum difference between V_{DD} and V_{SS} .




Figure A. Application Example





Figure B. External Germanium or Schottky Clipping Diodes

PACKAGE DIMENSIONS

SOIC-24 WB CASE 751E-04 ISSUE F



Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and IIIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not overy any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirma

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative