

## Data sheet Product SL 6 237 36 G

PCB connectors>Male headers


□ 0.635 mm

- **"S" selective gold-plated up to 33 mm pin length**
- for interconnections of stacked PCBs
- within the total length of the pin the insulator position can be changed as required ... **Design specification-sheet**
- **separable!** any requested number of contact can be delivered

### Features

grid:	<b>2.54 mm</b>
no. of contacts:	<b>36</b>
contact material:	<b>CuSn alloy</b>
surface of contact:	<b>gold-plated</b>
surface contact / contact sleeve:	<ul style="list-style-type: none"> <li>• <b>Ni+≥0.2µm Au</b></li> <li>• <b>Ni+4...6µm Sn</b></li> </ul>
version:	<b>sandwich</b>
volume resistance:	<b>≤5 mΩ</b>
nominal current:	<b>3 A</b>
nominal voltage:	<b>250 V AC</b>
test voltage:	<b>2000 V</b>
insulating body material:	<b>PA 4.6. GF</b>
temperature range:	<ul style="list-style-type: none"> <li>• <b>-40°C... +163°C</b></li> <li>• <b>(260°C/10 s)</b></li> </ul>
class of inflammability:	<b>UL 94 V-0</b>
specific insulation resistance:	<b>&gt;10<sup>7</sup> Ω·m</b>
connection type:	<b>THT (soldering)</b>
reflow solderable:	<b>yes</b>

## Technical Drawing



A: 23.7 mm

L: 33 mm

S: 6.0 mm

Fischer Elektronik GmbH & Co. KG  
DEUTSCHLAND • GERMANY • ALLEMAGNE

Nottebohmstraße 28  
58511 Lüdenscheid

Telefon +49 2351 435-0  
Telefax +49 2351 45754

info@fischerelektronik.de  
www.fischerelektronik.de