

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010081041](#)
Status: **Active**
Overview: [KK 508 Connector System](#)
Description: KK Header, Vertical, Round Pin, 4 Circuits, Tin (Sn) Plating, Pin Length 19.05mm

Documents:

3D Model	Packaging Specification 30030001-PK-000 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-1008-1041-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-99020-0087-001 (PDF)	

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	3003
Application	Board-to-Board, Power, Wire-to-Board
Overview	KK 508 Connector System
Product Name	KK 508
UPC	800753612174

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.012/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.94mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	See Product Specification



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[3003](#) Series

Mates With

KK Crimp Housing [3001](#)
KK PCB
Receptacle [3002](#)

Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 7.0A

Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 010

Lead-free Process Capability WAVE

Process Temperature max. C 260

Material Info

Engineering Number 3003-04A

Reference - Drawing Numbers

Packaging Specification 30030001-PK-000

Product Specification PS-99020-0087-001

Sales Drawing SDAE-3003-NX-001

Symbol/Footprint Data SYM-1008-1041-001

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[10-08-1041](#)