www.vishay.com

Vishay Dale

Metal Film Resistors, Axial, Military / Established Reliability, MIL-PRF-39017 Qualified, Type RLR



FEATURES

- Meets requirements of MIL-PRF-39017
 Failure rate: Verified failure rate (contact factory for current
- · Epoxy coated construction provides superior moisture protection
- Traceability of materials and processing
 Monthly lot acceptance testing
 Very low noise (-40 dB)

- Extensive stocking program at distributors and factory in ± 1 % and ± 2 % tolerances
 Vishay Dale has complete capability to develop specific reliability programs designed to customer requirements

STANDARD ELECTRICAL SPECIFICATIONS								
VISHAY DALE MODEL	MIL-PRF-39017 STYLE	MIL SPEC. SHEET	POWER RATING 70 °C W	RESISTANCE RANGE (1) Ω	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C	MAXIMUM WORKING VOLTAGE ⁽⁴⁾ V	LIFE FAILURE RATE ⁽²⁾
ERL05, ERL0519 ⁽³⁾	RLR05	05	0.125	4.7 to 100K > 100K to 1M	1, 2	100	200	M, P, R, S M, P, R
ERL07, ERL0723 ⁽³⁾	RLR07	01	0.25	1 to 9.76 10 to 3.01M 3.02M to 10M	1, 2	100	250	M M, P, R, S M, P, R
ERL20, ERL2011 ⁽³⁾	RLR20	02	0.50	4.3 to 3.01M	1, 2	100	350	M, P, R, S
ERL32, ERL321 ⁽³⁾	RLR32	03	1.0	1 to 2.7M	1, 2	100	500	M, P, R

Extended resistance range: DSCC has created a series of drawings intended to support extended resistance ranges left otherwise void by the discontinuation of MIL-R-39008 RCR carbon composition resistors. Vishay Dale is listed as a resource on these drawings as follows:

DSCC DRAWING NUMBER	VISHAY DALE MODEL	POWER RATING P _{70 °C} W	$\begin{array}{c} \textbf{RESISTANCE} \\ \textbf{RANGE} \\ \Omega \end{array}$	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C	MAXIMUM WORKING VOLTAGE V (4)
98020	ERL0536, ERL0537 (3)	0.125	1.1M to 22M	2, 5, 10	350	200
99011	ERL07100, ERL07101 (3)	0.25	11M to 22M	2, 5, 10	350	250
98021	ERL2036, ERL2037 (3)	0.50	3.3M to 22M	2, 5, 10	350	350
98022	ERL3236, ERL3237 (3)	1.0	3M to 22M	2, 5, 10	350	350
97004	ERL621, ERL622 ⁽³⁾	2.0	10 to 2.7M 3M to 22M	1, 2, 5, 10	100 350	500

Low inductance: DSCC has created a drawing intended to support a resistor which exhibits low inductance over a frequency range of 1 MHz to 30 MHz. Vishay Dale is listed as a resource on these drawings as follows:

DSCC DRAWING NUMBER	VISHAY DALE MODEL	POWER RATING P _{70°C} W	$\begin{array}{c} \textbf{RESISTANCE} \\ \textbf{RANGE} \\ \Omega \end{array}$	MAXIMUM INDUCTANCE nH	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C	MAXIMUM WORKING VOLTAGE V ⁽⁴⁾
96002	ERL0762	ERL0762 0.25	1 to 10	10	1.0	100	250
90002 ERLU762		0.25	11 to 49.9	8	1, 2	100	230

These drawings can be viewed at: https://landandmaritimeapps.dla.mil/Downloads/MilSpec/DsccDwg/96002.pdf


- Consult factory for current QPL failure rates
- Hot solder dipped leads
- Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less

TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	CONDITION		
Voltage Coefficient, max.	ppm/V	5/V when measured between 10 % and full rated voltage		
Dielectric Strength	V _{AC}	RLR05 = 300; RLR07 and RLR20 = 500; RLR32 = 1000		
Insulation Resistance	Ω	≥ 10 ⁹ min. dry; ≥ 10 ¹¹ min. after moisture test		
Operating Temperature Range	°C	-65 to +150		
Terminal Strength	lb	2 lb pull test on RLR05; 5 lb pull test on all other sizes		
Solderability		Continuous satisfactory coverage when tested in accordance with MIL-STD-202, method 208		
Weight	g	RLR05 = 0.11; RLR07 = 0.35; RLR20 = 0.75; RLR32 = 1.05		

Revision: 25-Apr-2023 Document Number: 31023




www.vishay.com



Note

• For additional information on packaging, refer to the Through Hole Resistor Packaging document (www.vishay.com/doc?31544)

DIMENSIONS in inches (millimeters)



Note

(1) Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim

VISHAY DALE MODEL	Α	В	C (Max.)	D	E
ERL05	0.150 ± 0.020	0.066 ± 0.008	0.187	0.016 ± 0.002	1.25 ± 0.266
	(3.81 ± 0.51)	(1.68 ± 0.21)	(4.75)	(0.41 ± 0.05)	(31.75 ± 6.76)
ERL07	0.250 + 0.031 - 0.046	0.090 ± 0.008	0.300	0.025 ± 0.002	1.50 ± 0.125
	(6.35 + 0.79 - 1.17)	(2.29 ± 0.21)	(7.62)	(0.64 ± 0.05)	(38.10 ± 3.18)
ERL20	0.375 ± 0.041	0.138 ± 0.023	0.450	0.032 ± 0.002	1.50 ± 0.125
	(9.53 ± 1.04)	(3.51 ± 0.58)	(11.43)	(0.81 ± 0.05)	(38.10 ± 3.18)
ERL32	0.562 ± 0.031	0.190 ± 0.015	0.625	0.032 + 0.002 - 0.001	1.50 ± 0.125
	(14.27 ± 0.79)	(4.83 ± 0.38)	(15.87)	(0.81 + 0.05 - 0.03)	(38.10 ± 3.18)
ERL62	0.562 + 0.031 - 0.042	0.230 ± 0.015	0.650	0.032 + 0.002 - 0.001	1.50 ± 0.125
	(14.27 + 0.79 - 1.07)	(5.84 ± 0.38)	(16.51)	(0.81 + 0.05 - 0.03)	(38.10 ± 3.18)

MATERIAL SPECIFICATIONS			
Element Vacuum-deposited nickel-chrome			
Core	Fire-cleaned high purity ceramic		
Encapsulation	Specially formulated epoxy compound		
Termination	Standard lead material is solder-coated copper. Solderable and weldable per MIL-STD-1276, Type C.		

POWER RATING

Power ratings are based on the following two conditions:

- 1. \pm 2.0 % maximum ΔR in 2000 h load life
- 2. +150 °C maximum operating temperature

APPLICABLE MIL-SPECIFICATIONS

MIL-PRF-39017:

The ERL series meets the electrical, environmental and dimensional requirements of MIL-PRF-39017.

MIL-PRF-22684:

MIL-PRF-39017 supersedes MIL-PRF-22684 on new designs. The ERL series meet or exceed MIL-PRF-22684 requirements.

Documentation:

Qualification and failure rate verification test data is maintained by Vishay Dale and is available upon request. Lot traceability and identification data is maintained by Vishay Dale for five years.

CAGE CODE: 91637


Revision: 25-Apr-2023 2 Document Number: 31023






www.vishay.com

Vishay Dale





MARKING (per MIL-PRF-39017)

Tolerance: F = 1 %, G = 2 %

Value = three significant figures and multiplier J = JAN (Joint Army - Navy) brand

RLR07: (4 lines)

RLR05: (3 lines)

210A

214AJ 3-digit date code, lot code and JAN

1002 Value RLR7C Style ("0" omitted) and lead material

FSJD

3-digit date code and lot code

1300G Value and tolerance

Tolerance, failure rate, JAN and manufacturer's code

RD Failure rate and manufacturer's code

RLR20, RLR32: (4 lines)

91637 CAGE code

Style and lead material RLR20C

4993FR Value, tolerance and failure rate 1225AJ 4-digit date code, lot code and JAN

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.