

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1210500554](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** mPm DIN Valve Connector, Form A - 18mm, 2 Pole Plus Ground Position H6/H12 with C4 Circuit, to 1.0m (3.28') PVC Cable Pigtail, Yellow LED, Black Nitrile Gasket, 24V

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E218123

**General**

Product Family Industrial Cordsets  
 Series [121050](#)  
 Connector End A Brad mPm DIN A - 18mm  
 Connector End B Pigtail  
 IP Rating IP65  
 Material - Contact Brass  
 Overview [mPm DIN Valve Connectors](#)  
 Product Name mPm  
 Protocol N/A  
 Region America, Europe  
 Type Single Ended  
 UPC 883906589769

**Physical**

Cable Diameter 5.72mm (.225")  
 Cable Length 1.0m (3.28')  
 Color - Cable Jacket Black  
 Coupling Style Threaded  
 Gender Male-Pigtail  
 Keyway None  
 LED Indicator Yellow  
 Material - Cable Jacket PVC  
 Material - Connector Body Polypropylene  
 Material - Coupling Nut N/A  
 Material - Plating Mating Gold  
 Net Weight 90.014/g  
 Orientation 90° to Pigtail  
 Poles 2  
 Temperature Range - Operating -40° to +90°C  
 Wire Size AWG N/A  
 Wire/Cable Type N/A

**Electrical**

Current - Maximum per Contact 5.0A  
 Voltage - Maximum 24V

**Material Info**

Engineering Number E452N3N10011C4H

**Reference - Drawing Numbers**

Sales Drawing 1210502000-000, SD-121050-001-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2021)4569-DC (8  
 July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[121050 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1210500554](#)