


ALUMINUM ELECTROLYTIC CAPACITORS

LGZ Snap-in Terminal Type, 105°C Long Life Assurance



NEW



- Long life product of LGR series.
- Contribute to longer life of equipment.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).



Specifications

Item	Performance Characteristics		
Category Temperature Range	- 25 to +105°C		
Rated Voltage Range	450V		
Rated Capacitance Range	82 to 330μF		
Capacitance Tolerance	±20% at 120Hz, 20°C		
Leakage Current	After 5 minutes' application of rated voltage at 20°C, leakage current is not more than $3\sqrt{CV}$ (μA) or 5 mA, whichever is smaller (at 20°C) [C : Rated Capacitance (μF) , V : Voltage (V)]		
Tangent of loss angle (tan δ)	0.20MAX. 120Hz at 20°C		
Stability at Low Temperature	Rated voltage (V)	450	
	Impedance ratio ZT/Z20(MAX.)	Z - 25°C / Z+20°C 8	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 20000 hours at 105°C, the peak voltage shall not exceed the rated voltage.	Capacitance change	Within ±25% of the initial capacitance value
		tan δ	250% or less than the initial specified value
		Leakage current	Less than or equal to the initial specified value
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the characteristic requirements listed at right.	Capacitance change	Within ±15% of the initial capacitance value
		tan δ	150% or less than the initial specified value
		Leakage current	Less than or equal to the initial specified value
Marking	Printed with white color letter on black sleeve.		

Drawing




(PC board hole dimensions)

(Terminal dimensions)

※ The other terminal is also available upon request. Please refer page 346 for schematic of dimensions.

Type numbering system (Example : 450V 82μF)



Dimensions

450V (2W)				
Cap. (μF)	Size φD × L(mm)	Rated ripple (mArms)	Leakage Current (mA)	Code
82	30 × 25	560	0.57	LGZ2W820MELB25
100	30 × 30	640	0.63	LGZ2W101MELB30
120	30 × 35	720	0.69	LGZ2W121MELB35
	35 × 25	720	0.69	LGZ2W121MELC25
150	30 × 40	790	0.77	LGZ2W151MELB40
	35 × 30	790	0.77	LGZ2W151MELC30
180	30 × 45	870	0.85	LGZ2W181MELB45
	35 × 35	870	0.85	LGZ2W181MELC35
220	30 × 50	1000	0.94	LGZ2W221MELB50
	35 × 40	1000	0.94	LGZ2W221MELC40
270	35 × 45	1190	1.04	LGZ2W271MELC45
330	35 × 50	1380	1.15	LGZ2W331MELC50

Rated ripple current (mArms) at 105°C 120Hz

Frequency coefficient of rated ripple current

Frequency (Hz)	50	60	120	300	1 k	10k	50k or more
Coefficient	0.77	0.82	1.00	1.16	1.30	1.41	1.43

Minimum order quantity : 50pcs.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[LGZ2E151MHSB](#) [LGZ2W101MELB30](#) [LGZ2W121MELB35](#) [LGZ2W121MELC25](#) [LGZ2W151MELB40](#)
[LGZ2W331MELC50](#) [LGZ2W820MELB25](#) [LGZ2W151MELC30](#) [LGZ2W181MELB45](#) [LGZ2W181MELC35](#)
[LGZ2W221MELB50](#) [LGZ2W221MELC40](#) [LGZ2W271MELC45](#)