


650 V, 6 A high surge silicon carbide power Schottky diode



D²PAK

Features

- No reverse recovery charge in application current range
- · Switching behavior independent of temperature
- · High forward surge capability
- Insulated package TO-220AC Ins:
 - Insulated voltage: 2500 V_{RMS}
 - Typical package capacitance: 7 pF
- Power efficient product
- ECOPACK[®]2 compliant component

Applications

- Switch mode power supply
- PFC
- · DCDC converters
- · LLC topologies
- Boost diode

Description

This 6 A, 650 V SiC diode is an ultrahigh performance power Schottky diode. It is manufactured using a silicon carbide substrate. The wide band gap material allows the design of a Schottky diode structure with a 650 V rating. Due to the Schottky construction, no recovery is shown at turn-off and ringing patterns are negligible. The minimal capacitive turn-off behavior is independent of temperature.

This STPSC6H065 is especially suited for use in PFC applications. This ST SiC diode will boost the performance in hard switching conditions. Its high forward surge capability ensures a good robustness during transient phases.

Product status STPSC6H065

Product summary			
Symbol	Value		
I _{F(AV)}	6 A		
V _{RRM}	650 V		
T _{j(max.)}	175 °C		

SUSTAINABLE TECHNOLOGY



1 Characteristics

Table 1. Absolute ratings (limiting values at 25 °C unless otherwise specified)

Symbol		Parameter	Value	Unit	
V_{RRM}	Repetitive peak reverse voltage	650	V		
I _{F(RMS)}	Forward rms current		22	Α	
	Average forward average	TO-220AC, DPAK, D ² PAK, T _C = 135 °C ⁽¹⁾ , DC		_	
I _{F(AV)} Average forward current	TO-220AC Ins,T _c = 110 °C ⁽¹⁾	6	A		
		t_p = 10 ms sinusoidal, T_c = 25 °C	60		
I_{FSM}	Surge non repetitive forward current	t_p = 10 ms sinusoidal, T_c = 125 °C	52	Α	
		t_p = 10 µs square, T_c = 25 °C	400		
I	Depositive pools forward assessed	TO-220AC, DPAK, D ² PAK, T _c = 135 °C ⁽¹⁾ , T _j = 175 °C, δ = 0.1		_	
I _{FRM} Repetitive peak forward current	TO-220AC Ins,T _C = 95 °C	25	Α		
T _{stg}	Storage temperature range			°C	
Tj	Operating junction temperature ra	Operating junction temperature range ⁽²⁾			

^{1.} Value based on R_{th(j-c)} max.

Table 2. Thermal resistance parameters

Symbol		Parameter	Typ. value	Max. value	Unit
R _{th(j-c)}	Junction to case	TO-220AC, DPAK, D ² PAK	1.6	2.4	°C/W
· \tn(j-c)	Junction to case	TO-220AC Ins	2.9	4.2	C/VV

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
I _R ⁽¹⁾	L (1)		V _R = V _{RRM}	-	5	60	μA
IR ^(*)	Reverse leakage current	T _j = 150 °C	VR - VRRM	-	50	250	μΑ
V _F ⁽²⁾	Forward voltage drop	T _j = 25 °C	I _F = 6 A	-	1.56	1.75	V
VF ⁽²⁾ F	Forward voltage drop	T _j = 150 °C	IF - 0 A	-	1.98	2.50	V

^{1.} $t_p = 10 \text{ ms}, \ \delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 1.35 \times I_{F(AV)} + 0.192 \times I_{F^{2}(RMS)}$$

For more information, please refer to the following application notes related to the power losses:

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

DS9064 - Rev 9 page 2/16

^{2.} $(dP_{tot}/dT_i) < (1/R_{th(i-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

^{2.} $t_p = 500 \, \mu \text{s}, \, \delta < 2\%$



Table 4. Dynamic electrical characteristics

Symbol	Parameter	Test conditions	Тур.	Unit
Q _{cj} ⁽¹⁾	Total capacitive charge	V _R = 400 V	18	nC
C.	C _j Total capacitance	V _R = 0 V, T _c = 25 °C, F = 1 MHz	300 pF	
O _j		V _R = 400 V, T _c = 25 °C, F = 1 MHz	30	ÞΕ

1. Most accurate value for the capacitive charge: $Q_{Cj}(V_R) = \int\limits_0^{V_R} C_j(V) dV$



1.1 Characteristics (curves)

Figure 1. Forward voltage drop versus forward current (typical values, low level)




Figure 2. Forward voltage drop versus forward current (typical values, high level)




Figure 3. Reverse leakage current versus reverse voltage applied (typical values)





Figure 4. Peak forward current versus case temperature (TO-220AC, DPAK, D²PAK)



DS9064 - Rev 9 page 4/16



Figure 5. Peak forward current versus case temperature (TO-220AC Ins)




Figure 6. Junction capacitance versus reverse voltage applied (typical values)




Figure 7. Relative variation of thermal impedance junction to case versus pulse duration (TO-220AC, DPAK and D²PAK)




Figure 8. Relative variation of thermal impedance junction to case versus pulse duration (TO-220AC Ins)




Figure 9. Non-repetitive peak surge forward current versus pulse duration (sinusoidal waveform)





Figure 10. Total capacitive charges versus reverse voltage applied (typical values)



DS9064 - Rev 9 page 5/16



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 DPAK package information

Epoxy meets UL94, V0

Figure 11. DPAK package outline




Table 5. DPAK mechanical data

	Dimensions							
Dim.	Millimeters			Inches ⁽¹⁾				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
Α	2.20		2.40	0.087		0.094		
A1	0.90		1.10	0.035		0.043		
A2	0.03		0.23	0.001		0.009		
b	0.64		0.90	0.025		0.035		
b4	5.20		5.40	0.205		0.213		
С	0.45		0.60	0.018		0.024		
c2	0.48		0.60	0.019		0.024		
D	6.00		6.20	0.236		0.244		
D1	4.95	5.10	5.25	0.195	0.201	0.207		
E	6.40		6.60	0.252		0.260		
E1	4.60	4.70	4.80	0.181	0.185	0.189		
е	2.159	2.286	2.413	0.085	0.090	0.095		
e1	4.445	4.572	4.699	0.175	0.180	0.185		
Н	9.35		10.10	0.368		0.398		
L	1.00		1.50	0.039		0.059		
(L1)	2.60	2.80	3.00	0.102	0.110	0.118		
L2	0.65	0.80	0.95	0.026	0.031	0.037		
L4	0.60		1.00	0.024		0.039		
R		0.20			0.008			
V2	0°		8°	0°		8°		

^{1.} Inches dimensions given for reference only

Figure 12. DPAK recommended footprint (dimensions are in mm)



The device must be positioned within $\boxed{\oplus 0.05 \text{ A} \text{ B}}$

DS9064 - Rev 9 page 7/16



2.2 D²PAK package information

- Epoxy meets UL94, V0.
- Cooling method: by conduction (C)

THERMAL PAD

SEATING PLANE

COPLANARITY A1

COPLANARITY A1

CAUGE PLANE

V2

Figure 13. D²PAK package outline

Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.


DS9064 - Rev 9 page 8/16



Table 6. D²PAK package mechanical data

	Dimensions						
Ref.		Millimeters		Inches (for reference only)			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
A	4.40		4.60	0.173		0.181	
A1	0.03		0.23	0.001		0.009	
b	0.70		0.93	0.028		0.037	
b2	1.14		1.70	0.045		0.067	
С	0.45		0.60	0.018		0.024	
c2	1.23		1.36	0.048		0.053	
D	8.95		9.35	0.352		0.368	
D1	7.50	7.75	8.00	0.295	0.305	0.315	
D2	1.10	1.30	1.50	0.043	0.051	0.060	
Е	10.00		10.40	0.394		0.409	
E1	8.30	8.50	8.70	0.335	0.343	0.346	
E2	6.85	7.05	7.25	0.266	0.278	0.282	
е		2.54			0.100		
e1	4.88		5.28	0.190		0.205	
Н	15.00		15.85	0.591		0.624	
J1	2.49		2.69	0.097		0.106	
L	2.29		2.79	0.090		0.110	
L1	1.27		1.40	0.049		0.055	
L2	1.30		1.75	0.050		0.069	
R		0.40			0.015		
V2	0°		8°	0°		8°	

Figure 14. D²PAK recommended footprint (dimensions are in mm)



DS9064 - Rev 9 page 9/16



2.3 TO-220AC package information


Epoxy meets UL 94,V0

Cooling method: by conduction (C)

• Recommended torque value: 0.55 N·m

Maximum torque value: 0.70 N·m

Figure 15. TO-220AC package outline



- (1) :Max resin gate protusion 0.5 mm
- (2) :Resin gate position is accepted in each of the two positions shown on the drawings or their symmetrical

DS9064 - Rev 9 page 10/16



Table 7. TO-220AC package mechanical data

	Dimensions				
Ref.	Millin	neters	Inches (for reference only)		
	Min.	Max.	Min.	Max.	
A	4.40	4.60	0.173	0.181	
С	1.23	1.32	0.048	0.051	
D	2.40	2.72	0.094	0.107	
E	0.49	0.70	0.019	0.027	
F	0.61	0.88	0.024	0.034	
F1	1.14	1.70	0.044	0.066	
G	4.95	5.15	0.194	0.202	
H2	10.00	10.40	0.393	0.409	
L2	16.4	0 typ.	0.645 typ.		
L4	13.00	14.00	0.511	0.551	
L5	2.65	2.95	0.104	0.116	
L6	15.25	15.75	0.600	0.620	
L7	6.20	6.60	0.244	0.259	
L9	3.50	3.93	0.137	0.154	
M	2.60	typ.	0.102	2 typ.	
Diam	3.75	3.85	0.147	0.151	

DS9064 - Rev 9 page 11/16



2.4 TO-220AC Ins. package information


Epoxy meets UL 94,V0


Cooling method: by conduction (C)

• Recommended torque value: 0.55 N·m

Maximum torque value: 0.70 N·m

Figure 16. TO-220AC Ins. package outline





DS9064 - Rev 9 page 12/16



Table 8. TO-220AC Ins. package mechanical data

			Dime	nsions		
Ref.		Millimeters		Inch	es (for reference	only)
	Min.	Тур.	Max.	Min.	Тур.	Max.
А	15.20		15.90	0.598		0.625
a1		3.75			0.147	
a2	13.00		14.00	0.511		0.551
В	10.00		10.40	0.393		0.409
b1	0.61		0.88	0.024		0.034
b2	1.23		1.32	0.048		0.051
С	4.40		4.60	0.173		0.181
c1	0.49		0.70	0.019		0.027
c2	2.40		2.72	0.094		0.107
е	4.80		5.40	0.189		0.212
F	6.20		6.60	0.244		0.259
L	2.65		2.95	0.104		0.116
12	1.14		1.70	0.044		0.066
14	15.80	16.40	16.80	0.622	0.645	0.661
M		2.60			0.102	
ØI	3.75		3.85	0.147		0.151

DS9064 - Rev 9 page 13/16



3 Ordering Information

Table 9. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPSC6H065D	STPSC6H065D	TO-220AC	1.86 g	50	Tube
STPSC6H065DI	STPSC 6H065DI	TO-220AC Ins.	2.12 g	50	Tube
STPSC6H065G-TR	STPSC6H065G	D ² PAK	1.48 g	1000	Tape and reel
STPSC6H065B-TR	STPSC 6H065	DPAK	0.32 g	2500	Tape and reel

DS9064 - Rev 9 page 14/16



Revision history

Table 10. Document revision history

Date	Version	Changes
18-Jun-2012	1	First issue.
31-Aug-2012	2	Added diode configuration graphic on front page. Updated value of Q_{cj} and footnote equation in Table 5.
10-Oct-2012	3	Added Max. value in Table 3.
07-Nov-2013	4	Updated Figure 1, Figure 2, Figure 13, Figure 14, and Table 9.
07-Jan-2014	5	Added TO-220AC Ins package.
22-Jul-2015	6	Updated Table 10 and reformatted to current standard.
22-Feb-2016	7	Updated cover image.
25-Jan-2019	8	Updated D²PAK package information. Added Section Applications and Section Sustainable technology program.
09-Jan-2020	9	Updated Features.



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics - All rights reserved

DS9064 - Rev 9 page 16/16