


6 mm Square Long Travel
Light Touch Switches, Radial Taping

Japan

Type: **EVQPV**

Light Touch Switches with a long travel of 1.3 mm or 1.0 mm and a push plate, 5.0 mm in height




■ Features

- Excellent operation by a larger push plate (φ4.6 mm)
- High mountability, section terminals and radial taping package (2500 pcs./pack)
- Low contact resistance and steady contact characteristics

■ Recommended Applications

- Car audio equipment

■ Explanation of Part Numbers



■ Specifications


Type		Snap action/Push-on type SPST	
Electrical	Rating	50 mA 12 Vdc max. (Resistive load)	
	Contact Resistance	100 mΩ max.	
	Insulation Resistance	100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	2.2 N	2.0 N, 2.5 N, 3.5 N
	Travel	1.0 mm±0.2 mm	1.3 mm±0.2 mm
Endurance	Operating Life	100000 cycles min. (3.5 N type : 30000 cycles min.)	
	Operating Temperature	-30 °C to +85 °C (45 % to 85 % RH)	
	Storage Temperature	-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/Packing Unit		2500 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

EVQPV

(Radial Taping)



Part Numbers	Operating Force	Travel	H=Height	Push Plate Color	Operating Life
EVQPVA05K	2.2 N	1.0 mm	5.0 mm	Black	100000 cycles
EVQPVG05K	2.0 N	1.3 mm	5.0 mm	Black	100000 cycles
EVQPVF05K	2.5 N	1.3 mm	5.0 mm	Black	100000 cycles
EVQPVW05K	3.5 N	1.3 mm	5.0 mm	Black	30000 cycles