

DIN-Signal high current f, 40A press-in



Image is for illustration purposes only. Please refer to product description.

Part number	09 03 000 6250
Specification	DIN-Signal high current f, 40A press-in
HARTING eCatalogue	https://b2b.harting.com/09030006250

Identification

Category	Contacts
Type of contact	Press-in contact
Description of the contact	Straight
Contacts for	DIN 41612 Type M-flat

Version

Gender	Female contact for female connectors
Manufacturing process	Turned contacts
Performance level	1

Technical characteristics

Operating current	≤40 A
-------------------	-------

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances	Lead
-----------------------	------

Specifications and approvals

Specifications	DIN 41626
----------------	-----------

Commercial data

Packaging size	100
----------------	-----

Net weight	1.06 g
------------	--------

Country of origin	Czechia
-------------------	---------

European customs tariff number	85366990
--------------------------------	----------

eCl@ss	27440204 Contact for industrial connectors
--------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09030006250](#)