


Surface-Mount Glass Passivated Ultrafast Rectifier

Superectifier®


GL41 (DO-213AB)

FEATURES

- Superectifier structure for high reliability condition
- Cavity-free glass-passivated junction
- Ideal for automated placement
- Ultrafast reverse recovery time
- Low switching losses, high efficiency
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 250 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

TYPICAL APPLICATIONS

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, automotive and telecommunication.

MECHANICAL DATA

Case: GL41 (DO-213AB), molded epoxy over glass body
Molding compound meets UL 94 V-0 flammability rating
Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102
E3 suffix meets JESD 201 class 1A whisker test

Polarity: two bands indicate cathode end - 1st band denotes device type and 2nd band denotes repetitive peak reverse voltage rating

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	1.0 A
V_{RRM}	50 V to 400 V
I_{FSM}	30 A
t_{rr}	50 ns
V_F	1.0 V, 1.25 V
T_J max.	175 °C
Package	GL41 (DO-213AB)
Circuit configuration	Single

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)

PARAMETER	SYMBOL	BYM12-50	BYM12-100	BYM12-150	BYM12-200	BYM12-300	BYM12-400	UNIT
		EGL41A	EGL41B	EGL41C	EGL41D	EGL41F	EGL41G	
FAST EFFICIENT DEVICE: 1ST BAND IS GREEN								
Polarity color bands (2 nd band)		Gray	Red	Pink	Orange	Brown	Yellow	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	150	200	300	400	V
Maximum RMS voltage	V_{RMS}	35	70	105	140	210	280	V
Maximum DC blocking voltage	V_{DC}	50	100	150	200	300	400	V
Maximum average forward rectified current at $T_T = 75$ °C	$I_{F(AV)}$	1.0						A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	30						A
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +175						°C



ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	BYM12-50	BYM12-100	BYM12-150	BYM12-200	BYM12-300	BYM12-400	UNIT
			EGL41A	EGL41B	EGL41C	EGL41D	EGL41F	EGL41G	
Max. instantaneous forward voltage	1.0 A	$V_F^{(1)}$	1.0				1.25		V
Max. DC reverse current at rated DC blocking voltage	$T_A = 25\text{ }^\circ\text{C}$	$I_R^{(1)}$	5.0						μA
	$T_A = 125\text{ }^\circ\text{C}$		50						
Max. reverse recovery time	$I_F = 0.5\text{ A}$, $I_R = 1.0\text{ A}$, $t_{rr} = 0.25\text{ A}$	t_{rr}	50						ns
Typical junction capacitance	4.0 V, 1 MHz	C_J	20				14		pF

Note

(1) Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	BYM12-50	BYM12-100	BYM12-150	BYM12-200	BYM12-300	BYM12-400	UNIT
		EGL41A	EGL41B	EGL41C	EGL41D	EGL41F	EGL41G	
Maximum thermal resistance	$R_{\theta JA}^{(1)}$	60						$^\circ\text{C/W}$
	$R_{\theta JT}^{(2)}$	30						

Notes

- (1) Thermal resistance from junction to ambient, 0.24" x 0.24" (6.0 mm x 6.0 mm) copper pads to each terminal
- (2) Thermal resistance from junction to terminal, 0.24" x 0.24" (6.0 mm x 6.0 mm) copper pads to each terminal

ORDERING INFORMATION (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
EGL41D-E3/96	0.114	96	1500	7" diameter plastic tape and reel
EGL41D-E3/97	0.114	97	5000	13" diameter plastic tape and reel

RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Junction Capacitance




Fig. 4 - Typical Reverse Leakage Characteristics






Fig. 6 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[BYM12-100-E3/76](#) [BYM12-100HE3/96](#) [BYM12-100HE3/97](#) [BYM12-150-E3/75](#) [BYM12-150HE3/75](#) [BYM12-150HE3/96](#) [BYM12-150HE3/97](#) [BYM12-200-E3/75](#) [BYM12-200-E3/76](#) [BYM12-200HE3/76](#) [BYM12-200HE3/96](#) [BYM12-200HE3/97](#) [BYM12-300HE3/96](#) [BYM12-300HE3/97](#) [BYM12-400/76](#) [BYM12-400HE3/96](#) [BYM12-400HE3/97](#) [BYM12-50-E3/76](#) [BYM12-50HE3/96](#) [BYM12-50HE3/97](#) [EGL41A-E3/51](#) [EGL41A-E3/75](#) [EGL41AHE3/96](#) [EGL41AHE3/97](#) [EGL41BHE3/96](#) [EGL41BHE3/97](#) [EGL41CHE3/96](#) [EGL41CHE3/97](#) [EGL41D/46](#) [EGL41DHE3/96](#) [EGL41DHE3/97](#) [EGL41F-E3/75](#) [EGL41FHE3/96](#) [EGL41FHE3/97](#) [EGL41G/46](#) [EGL41G-E3/46](#) [EGL41G-E3/76](#) [EGL41GHE3/96](#) [EGL41GHE3/97](#) [BYM12-200](#) [EGL41F/46](#) [BYM12-150HE3_A/H](#) [BYM12-200HE3_A/H](#) [BYM12-300HE3_A/H](#) [BYM12-50HE3_A/H](#) [EGL41BHE3_A/H](#) [BYM12-100HE3_A/H](#) [EGL41DHE3_A/H](#) [EGL41AHE3_A/H](#) [EGL41FHE3_A/H](#) [EGL41CHE3_A/H](#) [EGL41GHE3_A/H](#)