



# 1N5817 THRU 1N5819

## 1.0 AMP. Schottky Barrier Rectifiers



Voltage Range  
20 to 40 Volts  
Current  
1.0 Ampere


### Features

- ✧ Low forward voltage drop
- ✧ High current capability
- ✧ High reliability
- ✧ High surge current capability

### Mechanical Data

- ✧ Cases: Molded plastic DO-41
- ✧ Epoxy: UL 94V-O rate flame retardant
- ✧ Lead: Axial leads, solderable per MIL-STD-202, Method 208 guaranteed
- ✧ Polarity: Color band denotes cathode end
- ✧ High temperature soldering guaranteed: 260°C/10 seconds/.375", (9.5mm) lead lengths at 5 lbs., (2.3kg) tension
- ✧ Weight: 0.33 gram

### DO-41



Dimensions in inches and (millimeters)

## Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	1N5817	1N5818	1N5819	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	20	30	40	V
Maximum RMS Voltage	$V_{RMS}$	14	21	28	V
Maximum DC Blocking Voltage	$V_{DC}$	20	30	40	V
Maximum Average Forward Rectified Current .375 (9.5mm) Lead Length @ $T_L = 90^\circ\text{C}$	$I_{(AV)}$	1.0			A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	25			A
Maximum Instantaneous Forward Voltage @ 1.0A	$V_F$	0.45	0.550	0.600	V
Maximum Instantaneous Forward Voltage @ 3.0A	$V_F$	0.750	0.875	0.900	V
Maximum DC Reverse Current @ $T_A=25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_A=100^\circ\text{C}$	$I_R$	1.0 10			mA mA
Typical Thermal Resistance (Note 1)	$R_{\theta JA}$ $R_{\theta JC}$	100 45			$^\circ\text{C/W}$
Typical Junction Capacitance (Note 2)	$C_j$	55			pF
Operating Temperature Range	$T_J$	-65 to +125			$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-65 to +125			$^\circ\text{C}$

Notes: 1. Mount on Cu-Pad Size 5mm x 5mm on P.C.B.

2. Measured at 1 MHz and Applied Reverse Voltage of 4.0 V D.C.

## RATINGS AND CHARACTERISTIC CURVES (1N5817 THRU 1N5819)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL JUNCTION CAPACITANCE




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT

