
A (ONS										
A (DESC	RIPTIO	N					DATE (YR-MO-DA)		A) APPROVED)			
	TABLE I. Output s subgroup 2, delete Changes in accord	0.4 V and	substitute	e 0.45 V	<i>'</i> .	ion I _{SIN}	IK = 8 r	nA,		94-12-13		M. A. FRYE					
C F	Drawing updated t	o reflect cu	reflect current requirements. Redrawn				- ro				00-0	07-24		R. MONNIN			
	Replace reference	to MIL-ST	o MIL-STD-973 with reference to MIL-F				RF-385	35 r	0		03-0)4-17		R. MONNIN			
D l	Update boilerplate	paragraph	s to curre	nt MIL-	PRF-38	3535 re	quirem	ents	ro		11-0	05-02		C. SAFFLE			
THE ORIGINAL FI	IRST SHEET OF	THIS DRA	WING HAS	S BEEN	I REPL	ACED.											
THE ORIGINAL FI	IRST SHEET OF	THIS DRA	WING HAS	S BEEN	I REPL	ACED.											
ľ	IRST SHEET OF	THIS DRA	WING HAS	S BEEN	I REPL	ACED.											
REV	IRST SHEET OF	THIS DRA	WING HAS	S BEEN	I REPL	ACED.											
REV SHEET	IRST SHEET OF	THIS DRA	WING HAS	S BEEN	I REPL	ACED.											
REV SHEET REV	IRST SHEET OF	THIS DRA	WING HA	S BEEN	I REPL	ACED.	D	D	D	D	D	D	D				
REV SHEET REV SHEET	IRST SHEET OF							D 5	D 6	D 7	D 8	D 9	D 10				
REV SHEET REV SHEET REV STATUS OF SHEETS PMIC N/A		REV SHEET PREPA		D	D	D	D		6	7 DLA	8 LANE	9 ANE	10 MAR				
REV SHEET REV SHEET REV STATUS OF SHEETS PMIC N/A STANE MICROC	DARD	REV SHEET PREPA RICK (RED BY OFFICER	D 1	D	D	D		6	7 DLA I	8 LANE	9 ANE, OHIO	10	218-39			
REV SHEET REV SHEET REV STATUS OF SHEETS PMIC N/A STANE MICROC DRAW THIS DRAWING	DARD CIRCUIT VING	REV SHEET PREPAI RICK (CHECK CHARI	RED BY DFFICER	D 1	D	D	D 4	5	G CC	7 DLA DLUM http	B LANE IBUS D://ww	9 ANE, OHIO	D MAR O 432 scc.dla	218-39 a.mil			
REV SHEET REV SHEET REV STATUS OF SHEETS PMIC N/A STANE MICROC DRAW	DARD CIRCUIT VING IS AVAILABLE E BY ALL MENTS IES OF THE	REV SHEET PREPAI RICK (CHECK CHARI APPRO MICHA	RED BY DFFICER ED BY LES E. BE VED BY SEL A. FR'	D 1	D 2	D	D 4	5 CROC	CCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCCC	DLA DLUM http	BLANE IBUS D://ww	9 ANE, OHIO	10 MAR O 432	218-39 a.mil AGE	990		

DSCC FORM 2233 APR 97

1. SCOPE

- 1.1 <u>Scope</u>. This drawing describes device requirements for MIL-STD-883 compliant, non-JAN class level B microcircuits in accordance with MIL-PRF-38535, appendix A.
 - 1.2 Part or Identifying Number (PIN). The complete PIN is as shown in the following example:



1.2.1 <u>Device type(s)</u>. The device type(s) identify the circuit function as follows:

Device type	Generic number	<u>Circuit function</u>
01	LT1011A	Voltage comparator
02	LT1011	Voltage comparator

1.2.2 <u>Case outline(s)</u>. The case outline(s) are as designated in MIL-STD-1835 and as follows:

Outline letter Descriptive designator		<u>Terminals</u>	Package style
G	MACY1-X8	8	Can
P	GDIP1-T8 or CDIP2-T8	8	Dual-in-line

- 1.2.3 Lead finish. The lead finish is as specified in MIL-PRF-38535, appendix A.
- 1.3 Absolute maximum ratings.

Positive supply voltage (+V _S)	+18 V dc	
Negative supply voltage (-V _S)	-18 V dc	
Supply voltage (+V _S to -V _S)	36 V dc	
Output to negative supply (OUTPUT to -V _S)	50 V dc	
Ground to negative supply (GROUND to -V _S)	30 V dc	
Differential input voltage	±36 V dc	
Voltage at strobe pin	5 V dc	
Power dissipation (P _D)	200 mW	
Input voltage (V _{IN})	Equal to supplies	<u>1</u> /
Output strobe current (I _{STR})	5 mA	
Output strobe current (ISINK)		
Output short circuit duration		
Storage temperature range	-65°C to +150°C	
Lead temperature (soldering, 10 seconds)		
Junction temperature (T _J)		

^{1/} Inputs may be clamped to supplies with diodes so that maximum input voltage actually exceeds supply voltage by one diode drop.

STANDARD MICROCIRCUIT DRAWING	SIZE A		5962-90627
DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990		REVISION LEVEL D	SHEET 2

1.3 Absolute maximum ratings -continued.

1.4 Recommended operating conditions.

2. APPLICABLE DOCUMENTS

2.1 <u>Government specification, standards, and handbooks</u>. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those cited in the solicitation or contract.

DEPARTMENT OF DEFENSE SPECIFICATION

MIL-PRF-38535 - Integrated Circuits, Manufacturing, General Specification for.

DEPARTMENT OF DEFENSE STANDARDS

MIL-STD-883 - Test Method Standard Microcircuits.

MIL-STD-1835 - Interface Standard Electronic Component Case Outlines.

DEPARTMENT OF DEFENSE HANDBOOKS

MIL-HDBK-103 - List of Standard Microcircuit Drawings.
MIL-HDBK-780 - Standard Microcircuit Drawings.

(Copies of these documents are available online at https://assist.daps.dla.mil/quicksearch/ or from the Standardization Document Order Desk, 700 Robbins Avenue, Building 4D, Philadelphia, PA 19111-5094.)

2.2 <u>Order of precedence</u>. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

3. REQUIREMENTS

3.1 Item requirements. The individual item requirements shall be in accordance with MIL-PRF-38535, appendix A for non-JAN class level B devices and as specified herein. Product built to this drawing that is produced by a Qualified Manufacturer Listing (QML) certified and qualified manufacturer or a manufacturer who has been granted transitional certification to MIL-PRF-38535 may be processed as QML product in accordance with the manufacturers approved program plan and qualifying activity approval in accordance with MIL-PRF-38535. This QML flow as documented in the Quality Management (QM) plan may make modifications to the requirements herein. These modifications shall not affect form, fit, or function of the device. These modifications shall not affect the PIN as described herein. A "Q" or "QML" certification mark in accordance with MIL-PRF-38535 is required to identify when the QML flow option is used.

STANDARD MICROCIRCUIT DRAWING	SIZE A		5962-90627
DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990		REVISION LEVEL D	SHEET 3

- 3.2 <u>Design, construction, and physical dimensions</u>. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38535, appendix A and herein.
 - 3.2.1 Case outlines. The case outlines shall be in accordance with 1.2.2 herein.
 - 3.2.2 <u>Terminal connections</u>. The terminal connections shall be as specified on figure 1.
- 3.3 <u>Electrical performance characteristics</u>. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full ambient operating temperature range.
- 3.4 <u>Electrical test requirements</u>. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are described in table I.
- 3.5 <u>Marking</u>. Marking shall be in accordance with MIL-PRF-38535, appendix A. The part shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's PIN may also be marked. For packages where marking of the entire SMD PIN number is not feasible due to space limitations, the manufacturer has the option of not marking the "5962-" on the device.
- 3.5.1 <u>Certification/compliance mark.</u> A compliance indicator "C" shall be marked on all non-JAN devices built in compliance to MIL-PRF-38535, appendix A. The compliance indicator "C" shall be replaced with a "Q" or "QML" certification mark in accordance with MIL-PRF-38535 to identify when the QML flow option is used.
- 3.6 <u>Certificate of compliance</u>. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in MIL-HDBK-103 (see 6.6 herein). The certificate of compliance submitted to DLA Land and Maritime -VA prior to listing as an approved source of supply shall affirm that the manufacturer's product meets the requirements of MIL-PRF-38535, appendix A and the requirements herein.
- 3.7 <u>Certificate of conformance</u>. A certificate of conformance as required in MIL-PRF-38535, appendix A shall be provided with each lot of microcircuits delivered to this drawing.
- 3.8 <u>Notification of change</u>. Notification of change to DLA Land and Maritime -VA shall be required for any change that affects this drawing.
- 3.9 <u>Verification and review</u>. DLA Land and Maritime, DLA Land and Maritime 's agent, and the acquiring activity retain the option to review the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.

STANDARD					
MICROCIRCUIT DRAWING					
DLA LAND AND MARITIME					
COLUMBUS, OHIO 43218-3990					

SIZE A		5962-90627
	REVISION LEVEL D	SHEET 4

T 4 D 1 E 1			
TABLE I.	Electrical	performance	characteristics.

Test	Symbol	Conditions $\underline{1}/$ -55°C \leq T _A \leq +125°C unless otherwise specified	Group A subgroups	Device type	Limits 2/		Unit
					Min	Max	
Input offset voltage	Vos	<u>3</u> /	1	01	-0.5	+0.5	mV
			2,3		-1.0	+1.0	
			1	02	-1.5	+1.5	
			2,3		-3.0	+3.0	
		$R_S \le 50 \text{ k}\Omega$ 4/	1	01	-0.75	+0.75	
			2,3		-1.5	+1.5	
			1	02	-2.0	+2.0	
			2,3		-3.0	+3.0	
Input offset current	los	<u>4</u> /	1	01	-3	+3	nA
			2,3		-5	+5	
			1	02	-4	+4	
			2,3		-6	+6	
Input bias current	IB	<u>3</u> /	1	01	-25	+25	nA
				02	-50	+50	
		<u>4</u> /	1	01	-35	+35	
			2,3		-50	+50	
			1	02	-65	+65	
			2,3		-80	+80	
Input offset voltage	ΔV _{OS} /	<u>5</u> / <u>6</u> /	2,3	01	-15	+15	μV/°C
drift	ΔΤ			02	-25	+25	
Common mode	CMRR	V _{CM} = -14.5 V and 13 V	1	01	94		dB
rejection ratio			2,3		88		
			1	02	90		
			2,3	1	84		1

See footnotes at end of table.

STANDARD MICROCIRCUIT DRAWING	SIZE A		5962-90627
DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990		REVISION LEVEL D	SHEET 5

TABLET	Flootrical	porformanco	characteristics -	Continued
LADLE I.	Electrical	benormance	characteristics -	· Conunuea.

Test	Symbol	Conditions $\underline{1}/$ -55°C \leq T _A \leq +125°C unless otherwise specified	Group A subgroups	Device type	Limi	its <u>2</u> /	Unit
					Min	Max	
Input voltage range	IVR	<u>6</u> /	1,2,3	All	-14.5	13	V
		+V _S = +5 V, -V _S = 0 V <u>6</u> /			0.5	3.0	
Output saturation voltage		$+V_S = +5 \text{ V}, V_{IN} = 5 \text{ mV},$ $I_{SINK} = 8 \text{ mA},$	1,3 All			0.4	V
		GROUND pin = 0 V	2			0.45	
		I _{SINK} = 50 mA, GROUND pin = 0 V	1,2,3			1.5	
Output leakage current	I _{LKG}	V _{IN} = 5 mV, V _{OUT} = 35 V,	1	All		10	nA
		GROUND pin = -15 V	2,3			500	
Positive supply current	+I _S	<u>7</u> /	1	All		4.0	mA
			2,3			9.0	
Negative supply current	-I _S	<u>7</u> /	1	All	-2.5		mA
			2,3		-6.5		
Strobe current	I _{STR}	T _A = +25°C, <u>6</u> / <u>7</u> / <u>8</u> / minimum to ensure output transistor is turned off	1	All	500		μА
Large signal voltage gain A _{VOL}		$R_L = 1 \text{ k}\Omega \text{ to +15 V},$ $-10 \text{ V} \leq \text{V}_{OUT} \leq 14.5 \text{ V},$ $T_A = +25^{\circ}\text{C}$	4	All	200		V/mV
		$R_L = 500 \ \Omega \text{ to } +5 \ V,$ $0.5 \ V \le V_{OUT} \le 4.5 \ V,$ $T_A = +25^{\circ}C$			50		
Response time	T _R	T _A = +25°C <u>6</u> / <u>9</u> /	9	All		250	ns

See footnotes at end of table.

A	
	REVIS

SIZE A		5962-90627
	REVISION LEVEL D	SHEET 6

TABLE I. Electrical performance characteristics - Continued.

- 1/ Unless otherwise specified, $\pm V_S = \pm 15 \text{ V}$, $V_{CM} = 0 \text{ V}$, and $R_S = 50 \Omega$.
- The algebraic convention, whereby the most negative value is a minimum and the most positive is a maximum, is used in this table.
- 3/ Output is sinking 1.5 mA with $V_{OUT} = 0 \text{ V}$.
- $\underline{4}$ / These specifications apply for all supply voltages from a single +5 V to ±15 V, the entire input voltage range, and for both high and low output states. The high state is I_{SINK} ≥ 100 μA, V_{OUT} ≥ (+V_S 1 V) and the low state is I_{SINK} ≤ 8 mA, V_{OUT} ≤ 0.8 V. Therefore, this specification defines a worst case error band that includes effects due to common mode signals, voltage gain, and output load.
- 5/ Drift is calculated by dividing the offset voltage difference measured at minimum and maximum temperatures by the temperature difference.
- 6/ Guaranteed by design, characterization, or correlation to other tested parameters.
- 7/ These specifications apply for all supply voltages from a single +5 V to ± 15 V.
- 8/ Do not short the strobe pin to ground. It should be current driven at 3 mA to 5 mA for the shortest strobe time. Currents as low as 500μ A will strobe the device if speed is not important. External leakage on the strobe pin in excess of 0.2μ A when the strobe is "off" can cause offset voltage shifts.
- 9/2 Response time is measured with a 100 mV step and 5 mV overdrive. The output load is a 500 Ω resistor tied to +5 V. Time measurement is taken when the output crosses 1.4 V.

STANDARD MICROCIRCUIT DRAWING	SIZE A		5962-90627
DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990		REVISION LEVEL D	SHEET 7

Device types	01 and 02	
Case outlines	G and P	
Terminal number	Terminal symbol	
1	GROUND	
2	+INPUT	
3	-INPUT	
4	-Vs	
5	BALANCE	
6	BALANCE / STROBE	
7	OUTPUT	
8	+VS	

FIGURE 1. <u>Terminal connections</u>.

STANDARD MICROCIRCUIT DRAWING

DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990

SIZE A		5962-90627
	REVISION LEVEL D	SHEET 8

4. VERIFICATION

- 4.1 <u>Sampling and inspection</u>. Sampling and inspection procedures shall be in accordance with MIL-PRF-38535, appendix A.
- 4.2 <u>Screening</u>. Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:
 - a. Burn-in test, method 1015 of MIL-STD-883.
 - (1) Test condition C. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1015 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}C$, minimum.
 - b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.
- 4.3 <u>Quality conformance inspection</u>. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.
 - 4.3.1 Group A inspection.
 - a. Tests shall be as specified in table II herein.
 - b. Subgroups 5, 6, 7, 8, 10, and 11 in table I, method 5005 of MIL-STD-883 shall be omitted.
 - 4.3.2 Groups C and D inspections.
 - a. End-point electrical parameters shall be as specified in table II herein.
 - b. Steady-state life test conditions, method 1005 of MIL-STD-883.
 - (1) Test condition C. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1005 of MIL-STD-883.
 - (2) $T_A = +125^{\circ}C$, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

STANDARD MICROCIRCUIT DRAWING	SIZE A		5962-90627
DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990		REVISION LEVEL D	SHEET 9

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (in accordance with MIL-STD-883, method 5005, table I)
Interim electrical parameters (method 5004)	
Final electrical test parameters (method 5004)	1*,2,3,4
Group A test requirements (method 5005)	1,2,3,4,9
Groups C and D end-point electrical parameters (method 5005)	1

^{*} PDA applies to subgroup 1.

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38535, appendix A.

6. NOTES

- 6.1 <u>Intended use</u>. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.
- 6.2 <u>Replaceability</u>. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.
- 6.3 <u>Configuration control of SMD's</u>. All proposed changes to existing SMD's will be coordinated with the users of record for the individual documents. This coordination will be accomplished using DD Form 1692, Engineering Change Proposal.
- 6.4 <u>Record of users</u>. Military and industrial users shall inform DLA Land and Maritime when a system application requires configuration control and the applicable SMD to that system. DLA Land and Maritime will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronics devices (FSC 5962) should contact DLA Land and Maritime -VA, telephone (614) 692-0544.
- 6.5 <u>Comments</u>. Comments on this drawing should be directed to DLA Land and Maritime -VA, Columbus, Ohio 43218-3990, or telephone (614) 692-0540.
- 6.6 <u>Approved sources of supply</u>. Approved sources of supply are listed in MIL-HDBK-103. The vendors listed in MIL-HDBK-103 have agreed to this drawing and a certificate of compliance (see 3.6 herein) has been submitted to and accepted by DLA Land and Maritime -VA.

STANDARD MICROCIRCUIT DRAWING	SIZE A		5962-90627
DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990		REVISION LEVEL D	SHEET 10

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 11-05-02

Approved sources of supply for SMD 5962-90627 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML-38535 during the next revision. MIL-HDBK-103 and QML-38535 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DLA Land and Maritime -VA. This information bulletin is superseded by the next dated revision of MIL-HDBK-103 and QML-38535. DLA Land and Maritime maintains an online database of all current sources of supply at http://www.dscc.dla.mil/Programs/Smcr/.

i e e e e e e e e e e e e e e e e e e e	t	
Standard	Vendor	Vendor
microcircuit drawing	CAGE	similar
PIN <u>1</u> /	number	PIN <u>2</u> /
5962-9062701GA	60264	MTLT1011AQH
	<u>3</u> /	MTL1011AMH
	<u>3</u> /	LT1011AMH/883
5962-9062701PA	60264	MTLT1011AQD8
	<u>3</u> /	MTL1011AMD8
	<u>3</u> /	LT1011AMJ8/883
5962-9062702GA	60264	MTLT1011QH
	<u>3</u> /	MTL1011MH
	<u>3</u> /	LT1011MH/883
5962-9062702PA	60264	MTLT1011QD8
	<u>3</u> /	MTL1011MD8
	<u>3</u> /	LT1011MJ8/883

- 1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the vendor to determine its availability.
- 2/ <u>Caution</u>. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.
- 3/ Not available from an approved source of supply.

 Vendor CAGE
 Vendor name

 number
 and address

60264 Minco Technology Labs, Inc. 1805 Rutherford Lane

1805 Rutherford Lane Austin, TX 78754-5101

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.