

BATTU Heat-shrink Tubing



TABLE 1

DIMENSIONS: Millimeters (*Inches*)

Description	As Supplied		As Recovered			
	Expanded I.D. (D)	Expanded Wall W3	Recovered I.D. (d)	Recovered Wall W (Total)	Recovered Wall W1 (Core)	Recovered Wall W2 (Jacket)
BATTU-12.7 / 6.1	12.70 (0.500) Min.	0.56 (0.022) ±0.18 (0.007)	6.10 (0.240) Max	1.09 (0.043) ±0.28 (0.011)	0.51 (0.020) ±0.15 (0.006)	0.58 (0.023) ±0.13 (0.005)
BATTU-20.1 / 8.9	20.07 (0.790) Min.	0.66 (0.026) ±0.18 (0.007)	8.90 (0.350) Max	1.45 (0.057) ±0.30 (0.012)	0.74 (0.029) ±0.15 (0.006)	0.71 (0.028) ±0.15 (0.006)
BATTU-25.4 / 12.7	25.40 (1.000) Min.	1.02 (0.040) ±0.25 (0.010)	12.70 (0.500) Max	1.91 (0.075) ±0.30 (0.012)	1.07 (0.042) ±0.15 (0.006)	0.84 (0.033) ±0.15 (0.006)


For More Details See BATTU Heat-shrink Tubing Specification, TEC-108-120006

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2017 TE Connectivity Corporation

THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm	DWN J. Bitter	06JUN2017	 TE Connectivity 305 Constitution Drive Menlo Park, CA 94025 USA			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK —				
0 PLC ± -	PRODUCT SPEC —	NAME BATTU TUBING DUAL WALL HEAT SHRINK TUBING	SIZE A4	CAGE CODE 06090	DRAWING NO BATTU_TUBING	RESTRICTED TO —
1 PLC ± -	APPLICATION SPEC —	WEIGHT 0	SCALE NTS		SHEET 1 OF 1	REV A
2 PLC ± -		CUSTOMER DRAWING				
3 PLC ± -						
4 PLC ± -						
ANGLES ± -						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[BATTU12.7/6.1A1032MM](#)