

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Sensor/actuator cable, 3-position halogen-free, Plug straight M8, coding: A, on Socket straight M8, cable length: 1.5 m

Your advantages

- Easy and safe: 100% electrically tested plug-in components

Commercial Data

Item number	1681923
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	BF01
Product Key	BF1BBA
Catalog Page	Page 188 (C-2-2019)
GTIN	4017918158583
Weight per Piece (including packing)	36.4 g
Weight per Piece (excluding packing)	35 g
Customs tariff number	85444290
Country of origin	DE

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Technical Data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
Application	Standard
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A
Protective circuit	unwired

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Signaling

Status display	No
Status display present	No

Connection data

Conductor connection

Tightening torque	0.2 Nm (M8 connectors)
-------------------	------------------------

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Connector

Connection 1

Type	Plug straight M8
Number of positions	3
Coding type	A
Number of positions	3


Connection 2

Type	Socket straight M8
Number of positions	3
	3

Cable/line

Cable length	1.5 m
--------------	-------

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	18 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	3x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm
External cable diameter	3.6 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation)
Thickness, outer sheath	approx. 0.5 mm
Overall twist	3 wires, twisted
Length of twist, overall twist	40 mm

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Max. conductor resistance	≤ 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	18 mm
Smallest bending radius, movable installation	36 mm
Max. bending cycles	10000000
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	hydrolysis and microbe resistant Highly resistant to acids, alkaline solutions and solvents Resistant to salt water partly UV-resistant in accordance with DIN EN ISO 4892-2-A
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

Standards/specifications	IEC 61076-2-104
--------------------------	-----------------

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable




1681923

<https://www.phoenixcontact.com/us/products/1681923>


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Circuit diagram




SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable

1681923


<https://www.phoenixcontact.com/us/products/1681923>

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

Dimensional drawing




Socket M8 x 1, straight

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable

1681923

<https://www.phoenixcontact.com/us/products/1681923>

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable




1681923


<https://www.phoenixcontact.com/us/products/1681923>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1681923>

 UL Listed Approval ID: FILE E 221474				
	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	60 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal Voltage U_N	Nominal Current I_N	Cross Section AWG	Cross Section mm^2
	60 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387	
---	--

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

Accessories

PROT-M 8 FS-PA-CHAIN - Sealing cap

1430857

<https://www.phoenixcontact.com/us/products/1430857>

M8 sealing cap made of plastic with fixing band for sensor cables, for M8 plugs



PABA WH/23 - Insert label

1013779

<https://www.phoenixcontact.com/us/products/1013779>

Insert label, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, lettering field size: 23 x 4 mm, Number of individual labels: 20



SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

PABA YE/23 - Insert label

1013782

<https://www.phoenixcontact.com/us/products/1013782>



Insert label, Strip, yellow, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 35 mm, lettering field size: 23 x 4 mm, Number of individual labels: 20

B-STIFT - Marker pen

1051993

<https://www.phoenixcontact.com/us/products/1051993>



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

PROT-M 8 MS-PA-CHAIN - Screw plug

1430860

<https://www.phoenixcontact.com/us/products/1430860>

M8 sealing cap made of plastic with fixing band for sensor cables, for M8 sockets



TSD 02 SAC - Torque screwdriver

1208487

<https://www.phoenixcontact.com/us/products/1208487>

Torque screwdriver, with preset torque of 0.2 Nm and 4 mm hexagonal drive for M8 connectors



SAC-3P-M 8MS/ 1,5-PUR/M 8FS - Sensor/actuator cable



1681923

<https://www.phoenixcontact.com/us/products/1681923>

SAC BIT M8-D10 - Tool

1208461

<https://www.phoenixcontact.com/us/products/1208461>



Nut for assembling M8 connectors with longitudinal knurl and a knurl diameter of 10 mm, for 4 mm hexagonal drive

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com