

# NOTES: UNLESS OTHERWISE SPECIFIED

# 1. PLUG MATERIAL:


SHELL: ZINC ALLOY, NICKEL PLATED COUPLING RING: ALUMINUM ALLOY, NICKEL PLATED INSERT AND RETAINING RING: THERMOPLASTIC SEAL: SILICONE RUBBER

# 2. BACKSHELL MATERIAL:


SHELL: ALUMINIUM ALLOY, NICKEL PLATED; LATCH SEGMENT: ALUMINIUM ALLOY, NICKEL PLATED; SCREW AND LOCK WASHER: STAINLESS STEEL; BUSHING: EPDM.

### 3. SPECIFICATIONS:

- 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
- 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
- 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
- 3.4 MOISTURE RESISTANCE: IP67 & IP69K (MATED CONDITION).
- 3.5 MATING CYCLE DURABILITY: 100 CYCLES
- 3.6 RoHS COMPLIANT
- 4. APPLY TO CABLE OD SIZE: Ø11.20-Ø24.08 . CAN BE USED:
- 4.1. WITH LARGE AND SMALL BUSHINGS IN PLACE.
- 4.2. WITH ONLY LARGE BUSHING IN PLACE.
- 4.3. WITH BOTH BUSHINGS REMOVED.
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 6. SEE SPECIFIC PLUG DRAWING FOR:
  - 6.1 CONTACT SIZE AND WIRE RANGE.
  - 6.2 RETAINING RING COLOR.
  - 6.3 MATING PART(S).
  - 6.4 CONTACT LAYOUT AND ALL OTHER SPECIFICATIONS.







			_							
	AHDM06-24-21SR-059		HDS	36-24-21SE-059	-21SE-069					
	PART NUMBER					DE	SCRIPTION			ITEM
QUANTITY		MA	TI	ERI	٩LS	S LI	ST			
UNLESS OTHER			DATE	1 Amphanal						
2) Tolerances are a		DRAWN: J. HEAD		16MAR2020	Amphenol					
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:				Sin	e Systems - www.a	mphenol-sine	.com	
3) Note reference	= <u>x</u>	ENGINEER:			44724 Morley Drive					
MATERIAL SPECIFICA	TIONS:	APPROVAL:			Clinton Township, MI 48036					
		CUSTOMER:			DUI		ΓΕ AHDM PLU	- /	,	ΓHD,
INFORMATION ONLY D		THIS DRAWING IS SUPPL INFORMATION ONLY, DES				KIT W	V/ CABLE CLA	MP BACK	SHELL	
PROCESS SPECIFICATIONS:  SPECIFICATIONS AND PERFORMANCE SHOWN HEREON ARE THE PROPERTY THE AMPHIENDL CORPORATION NO RI OF REPRODUCTION ARE MIPLED. ALL DIMENSIONS ARE SUBJECT TO NORMA		DPERTY OF	SIZE	TYPE	DWG NO:	04.0400	٥٥٥	REVISION		
				В	C-	AHDM06-	24-21SR	-059	A1	
NEXT ASS'Y:		MANUFACTURING VARIA			SCALE: N	ONE		SHEET	1 or	1

DWG NO: AHDM06-24-21SR-059

KIT,PLUG AND BACKSHELL,SZ 24

REV: A1 SH:

# **AT Series™** - Contact Size 16 Options

Machined Contacts, Sockets & Pins						
Part Number Description		Size	AWG	Туре		
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined		
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined		
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined		
AT62-209-16141	Female Contact - Socket, Nickel-plated	16	14	Machined		
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined		
AT62-201-1631	Female Contact - Socket, Gold-plated	16	16-20	Machined		
AT60-202-16141	Male Contact - Pin, Nickel-plated	16	16-20	Machined		
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined		
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined		
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined		
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined		
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined		

Tooling - Machined Contacts				
Part	Part Number	Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

	Contact Removal Tools				
Part	Part Number	Description			
3	ATRT-100	Used for removal of contacts for A Series™ products			
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16			
	A114017	Sealing Plug, Size 16, White			

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Type		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		

	Tooling - Stamped & Formed Contacts				
Part	Part Number	Description			
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)			
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)			
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)			
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)			
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)			
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)			
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021

# **ATP Series™** - Contact Size 12 Options

Machined Contacts, Sockets & Pins						
Part Number	Size	AWG	Туре			
AT60-204-12141-10	Male Contact - Pin, Nickel-plated		10-12	Machined		
AT62-203-12141-10	Female Contact - Socket, Nickel-plated 12 10-1		10-12	Machined		
AT60-220-1231	Male Contact - Pin, Gold-plated 12 12		12-14	Machined		
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined		
AT60-204-12141 Male Contact - Pin, Nickel-plated		12	12-14	Machined		
AT62-203-12141	Female Contact - Socket, Nickel-plated 12 12-14 Mach		Machined			

Smaller AWG for	DiagnosticGrade™ Machined Contacts, Sockets & Pins  • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective						
Part Number	Description	Size	AWG	Туре			
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined			
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined			

Tooling - Machined Contacts				
Part	Part Number	Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

Contact Removal Tools				
Part	Part Number	Description		
refer turbs	ATRT-100	Used for removal of contacts for A Series™ products		
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12		
	A114017	Sealing Plug, Size 12, White		

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed		
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed		
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed		
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed		
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed		
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed		
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed		
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed		

	Tooling - Stamped & Formed Contacts					
Part	Part Number	Description				
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)				
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series				
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)				

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021