

US-WML 36 (25X25) - Cable marker label



0800474

<https://www.phoenixcontact.com/us/products/0800474>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Cable marker label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: without print, mounting type: adhesive, cable diameter range: 14 ... 36 mm, cable diameter: \leq 36 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Your advantages

- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- Quick and easy handling
- Resistant to solvents
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- US-WML ... cable marker labels consist of a labeling field and a transparent protective foil

Commercial Data

Item number	0800474
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	BG09
Product Key	BG2319
Catalog Page	Page 215 (C-3-2019)
GTIN	4046356607063
Weight per Piece (including packing)	6.4 g
Weight per Piece (excluding packing)	5 g
Customs tariff number	39199080
Country of origin	DE

US-WML 36 (25X25) - Cable marker label



0800474

<https://www.phoenixcontact.com/us/products/0800474>

Technical Data

Product properties

Product type	Conductor marking
Type	Label

Marking

Number of individual labels	4
Number of individual labels per row	4
Printing	without print

Dimensions

Width	129.5 mm
Length	25.4 mm

External dimensions

Outside diameter	11 mm ... 36 mm
------------------	-----------------

Material specifications

Foil strength	0.06 mm
Adhesive	Acrylic
Color	white
Material	PVC
Base element material	Vinyl film
Components	Silicone-free

Cable/line

External cable diameter	≤ 36 mm
	14 mm ... 36 mm

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

US-WML 36 (25X25) - Cable marker label



0800474

<https://www.phoenixcontact.com/us/products/0800474>

Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (assembly)	> 0 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

US-WML 36 (25X25) - Cable marker label



0800474

<https://www.phoenixcontact.com/us/products/0800474>

Classifications

ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-WML 36 (25X25) - Cable marker label



0800474

<https://www.phoenixcontact.com/us/products/0800474>

Accessories

BLUEMARK ID - Printer

1003334

<https://www.phoenixcontact.com/us/products/1003334>



Monochrome printer with UV LED technology, with integrated "MARKING SYSTEM APP" marking software on board. 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal plates.

BLUEMARK ID COLOR - Printer

1002329

<https://www.phoenixcontact.com/us/products/1002329>



CMYK multicolor printer with UV LED technology, with integrated "MARKING SYSTEM APP" marking software on board, 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal plates.

US-WML 36 (25X25) - Cable marker label

0800474

<https://www.phoenixcontact.com/us/products/0800474>



BLUEMARK CLED - Printer

5147999

<https://www.phoenixcontact.com/us/products/5147999>



Printers with LED-UV technology for printing plastic labels in UniCard format.

THERMOMARK PRIME - Thermal transfer printer

5148888

<https://www.phoenixcontact.com/us/products/5148888>



Mobile thermal transfer printer for card materials, including power supply unit, Euro/US power cable, and USB cable. User manual printed in German and English. Magazine for UCT-TM... sheets and magazine for US-... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon cartridge = 70 m

US-WML 36 (25X25) - Cable marker label



0800474

<https://www.phoenixcontact.com/us/products/0800474>

THERMOMARK CARD 2.0 - Thermal transfer printer

1085267

<https://www.phoenixcontact.com/us/products/1085267>



Thermal transfer printer for card materials, including Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. User manual printed in German and English. Magazine for UCT-TM... sheets and magazines for US... cards. One Pcs./Pkt. each UCT-TM 6, US-EMLP (85,6x54), ink ribbon = 50 m

THERMOMARK CARD - Thermal transfer printer

5146464

<https://www.phoenixcontact.com/us/products/5146464>



Thermal transfer printer for cards

US-WML 36 (25X25) - Cable marker label

0800474

<https://www.phoenixcontact.com/us/products/0800474>



BM ID-CARTR. YE - Ink cartridge

1044348

<https://www.phoenixcontact.com/us/products/1044348>

Replacement UV fluid, 23 ml, color: yellow



BM ID-ADAPTER PLATE-US - Magazine

1044355

<https://www.phoenixcontact.com/us/products/1044355>

Adapter plate for accommodating US sheets



US-WML 36 (25X25) - Cable marker label

0800474

<https://www.phoenixcontact.com/us/products/0800474>



THERMOMARK CARD-US-MAG1 - Magazine

5146451

<https://www.phoenixcontact.com/us/products/5146451>

Magazine for the THERMOMARK CARD printer, for accommodating US cards



TMP-US-MAG1 - Magazine

0803341

<https://www.phoenixcontact.com/us/products/0803341>

Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards



US-WML 36 (25X25) - Cable marker label

0800474

<https://www.phoenixcontact.com/us/products/0800474>



THERMOMARK-RIBBON 110/50-TC - Ink ribbon

0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110-TC - Ink ribbon

0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

US-WML 36 (25X25) - Cable marker label

0800474

<https://www.phoenixcontact.com/us/products/0800474>



TMP-RIBBON 110 BK 100 - Ink ribbon cartridge

0803374

<https://www.phoenixcontact.com/us/products/0803374>

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., roll length: 70 m, width: 110 mm, color: black



BM ID-CARTR. BK - Ink cartridge

1044345

<https://www.phoenixcontact.com/us/products/1044345>

Replacement UV fluid, 23 ml, color: black



US-WML 36 (25X25) - Cable marker label

0800474

<https://www.phoenixcontact.com/us/products/0800474>



BM ID-CARTR. CY - Ink cartridge

1044346

<https://www.phoenixcontact.com/us/products/1044346>

Replacement UV fluid, 23 ml, color: cyan



Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com