




326005 Product Details

[Share](#) | [Print](#) | [Email](#)


326005
(AMPS-0-0326005-0)
TE Internal Number: 326005

Active

View 3D PDF

AMPOWER Terminals

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Product Classification = Connectors - Terminals and Splices
- Power Generation and Distribution Application
- Wire Size (AWG/CM) = 400,000 CM
- Wire/Cable Size = 375,000 - 450,000 CMA
- Terminal Configuration = Standard

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [TERMINAL, AMPOWER, WIRE SIZE: 400 MCM](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version AD)
- [3D Model](#) (IGES, Version AD)
- [3D Model](#) (STEP, Version AD)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Classification = Connectors - Terminals and Splices
- Terminal Configuration = Standard
- [Stud Size](#) = 1/2 [M12]
- [Stud Diameter \(mm \[in\]\)](#) = 12.70 [0.500]
- Material = Copper (Annealed) per ASTM B-75
- Body Style = Straight
- Finish = Tin

Termination Features:

- [Wire/Cable Size \(CMA\)](#) = 375,000 - 450,000

Body Features:

- [Wire Size \(AWG/CM\)](#) = 400,000 CM
- [Stud Hole Diameter \(mm \[in\]\)](#) = 13.08 [0.515]
- [Number of Holes](#) = 1
- [Barrel I.D. Min. \(mm \[in\]\)](#) = 22.25 [0.876]
- [Barrel Length](#) = Standard
- [Inspection Slot](#) = With
- [Tongue Material Thickness \(mm \[in\]\)](#) = 4.57 [0.180]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = Power Generation and Distribution

Packaging Features:

- Packaging Quantity = 25

Other:

- Brand = AMP
- Comment = Electrodeposited Tin Plate per MIL-T-10727.

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

