

BFU580Q NPN wideband silicon RF transistor Rev. 1 – 28 April 2014

Product data sheet

1. Product profile

1.1 General description

NPN silicon microwave transistor for high speed, medium power applications in a plastic, 3-pin SOT89 package.

The BFU580Q is part of the BFU5 family of transistors, suitable for small signal to medium power applications up to 2 GHz.

1.2 Features and benefits

- Low noise, high linearity, high breakdown RF transistor
- AEC-Q101 qualified
- Minimum noise figure (NF_{min}) = 0.75 dB at 900 MHz
- Maximum stable gain 14 dB at 900 MHz
- 11 GHz f_T silicon technology

1.3 Applications

- Applications requiring high supply voltages and high breakdown voltages
- Broadband amplifiers up to 2 GHz
- Low noise, high linearity amplifiers for ISM applications
- Automotive applications (e.g., antenna amplifiers)

1.4 Quick reference data

Table 1. Quick reference data

$T_{amb} = 25 \ ^{\circ}C$ unless otherwise specified

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V _{CB}	collector-base voltage	open emitter		-	-	24	V
V _{CE}	collector-emitter voltage	open base		-	-	12	V
		shorted base		-	-	24	V
V _{EB}	emitter-base voltage	open collector		-	-	2	V
I _C	collector current			-	30	60	mA
P _{tot}	total power dissipation	$T_{sp} \le 120 \ ^{\circ}C$	<u>[1]</u>	-	-	1000	mW
h _{FE}	DC current gain	I _C = 30 mA; V _{CE} = 8 V		60	95	130	
C _c	collector capacitance	V _{CB} = 8 V; f = 1 MHz		-	1.1	-	pF
f _T	transition frequency	I _C = 30 mA; V _{CE} = 8 V; f = 900 MHz		-	10.5	-	GHz



NPN wideband silicon RF transistor

$T_{amb} = 25 \ ^{\circ}C$ unless otherwise specified									
Symbol	Parameter	Conditions		Min	Тур	Max	Unit		
G _{p(max)}	maximum power gain	I _C = 30 mA; V _{CE} = 8 V; f = 900 MHz	<u>2]</u>	-	14	-	dB		
NF _{min}	minimum noise figure	I_C = 5 mA; V_{CE} = 8 V; f = 900 MHz; Γ_S = Γ_{opt}		-	0.75	-	dB		
P _{L(1dB)}	output power at 1 dB gain compression	I _C = 30 mA; V _{CE} = 8 V; Z _S = Z _L = 50 Ω ; f = 900 MHz		-	13	-	dBm		

Table 1. Quick reference data ...continued

[1] T_{sp} is the temperature at the solder point of the collector lead.

[2] If K > 1 then $G_{p(max)}$ is the maximum power gain. If K < 1 then $G_{p(max)}$ = MSG.

2. Pinning information

Pin	Description	Simplified outline	Graphic symbol
1	emitter		
2	collector		2
3	base		3-
		5 2 1	aaa-011580

3. Ordering information

Table 3.Ordering information

Type number	Packag	je	
	Name	Description	Version
BFU580Q	-	plastic surface-mounted package; exposed die pad with good heat transfer; 3 leads	SOT89
OM7965	-	Customer evaluation kit for BFU580Q and BFU590Q [1]	-

[1] The customer evaluation kit contains the following:

- a) Unpopulated RF amplifier Printed-Circuit Board (PCB)
- b) Unpopulated RF amplifier Printed-Circuit Board (PCB) with emitter degeneration
- c) Four SMA connectors for fitting unpopulated Printed-Circuit Board (PCB)
- d) BFU580Q and BFU590Q samples
- e) USB stick with data sheets, application notes, models, S-parameter and noise files

4. Marking

Table 4. Marking	
Type number	Marking
BFU580Q	S58

BFU580Q

5. Design support

Table 5. Available design support

Download from the BFU580Q product information page on http://www.nxp.com.

Support item	Available	Remarks
Device models for Agilent EEsof EDA ADS	yes	Based on Mextram device model.
SPICE model	yes	Based on Gummel-Poon device model.
S-parameters	yes	
Noise parameters	yes	
Customer evaluation kit	yes	See Section 3 and Section 10.
Solder pattern	yes	
Application notes	yes	See Section 10.1

6. Limiting values

Table 6.Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CB}	collector-base voltage	open emitter	-	30	V
V _{CE}	collector-emitter voltage	open base	-	16	V
		shorted base	-	30	V
V _{EB}	emitter-base voltage	open collector	-	3	V
I _C	collector current		-	100	mA
T _{stg}	storage temperature		-65	+150	°C
V _{ESD}	electrostatic discharge voltage	Human Body Model (HBM) According to JEDEC standard 22-A114E	-	±150	V
		Charged Device Model (CDM) According to JEDEC standard 22-C101B	-	±2	kV

7. Recommended operating conditions

Table 7. Characteristics								
Symbol	Parameter	Conditions	Min	Тур	Max	Unit		
V _{CB}	collector-base voltage	open emitter	-	-	24	V		
V _{CE}	collector-emitter voltage	open base	-	-	12	V		
		shorted base	-	-	24	V		
V _{EB}	emitter-base voltage	open collector	-	-	2	V		
l _C	collector current		-	-	60	mA		
Pi	input power	Z _S = 50 Ω	-	-	10	dBm		
Tj	junction temperature		-40	-	+150	°C		
P _{tot}	total power dissipation	$T_{sp} \le 120 \ ^{\circ}C$	<u>[1]</u> _	-	1000	mW		

[1] T_{sp} is the temperature at the solder point of the collector lead.

BFU580Q Product data sheet

Downloaded from Arrow.com.

8. Thermal characteristics

Table 8.	Thermal characteristics			
Symbol	Parameter	Conditions	Тур	Unit
R _{th(j-sp)}	thermal resistance from junction to solder point	[1]	30	K/W


[1] T_{sp} is the temperature at the solder point of the collector lead.

 T_{sp} has the following relation to the ambient temperature T_{amb} :

 $T_{sp} = T_{amb} + P \times R_{th(sp-a)}$

With P being the power dissipation and $R_{th(sp-a)}$ being the thermal resistance between the solder point and ambient. $R_{th(sp-a)}$ is determined by the heat transfer properties in the application.

The heat transfer properties are set by the application board materials, the board layout and the environment e.g. housing.



9. Characteristics

Table 9. Characteristics

 $T_{amb} = 25 \ ^{\circ}C$ unless otherwise specified

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _{(BR)CBO}	collector-base breakdown voltage	I _C = 100 nA; I _E = 0 mA	24	-	-	V
V _{(BR)CEO}	collector-emitter breakdown voltage	I _C = 150 nA; I _B = 0 mA	12	-	-	V
I _C	collector current		-	30	60	mA
I _{CBO}	collector-base cut-off current	I _E = 0 mA; V _{CB} = 8 V	-	<1	-	nA
h _{FE}	DC current gain	I _C = 30 mA; V _{CE} = 8 V	60	95	130	
C _e	emitter capacitance	V _{EB} = 0.5 V; f = 1 MHz	-	1.3	-	pF
C _{re}	feedback capacitance	V _{CE} = 8 V; f = 1 MHz	-	0.71	-	pF
C _c	collector capacitance	V _{CB} = 8 V; f = 1 MHz	-	1.1	-	pF
f _T	transition frequency	I _C = 30 mA; V _{CE} = 8 V; f = 900 MHz	-	10.5	-	GHz

BFU580Q Product data sheet

NPN wideband silicon RF transistor

Table 9. Characteristics ...continued

 $T_{amb} = 25 \ ^{\circ}C$ unless otherwise specified

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
G _{p(max)}	maximum power gain	f = 433 MHz; V _{CE} = 8 V	[1]			
		I _C = 5 mA	-	18.5	-	dB
		I _C = 20 mA	-	20	-	dB
		I _C = 30 mA	-	20	-	dB
		f = 900 MHz; V _{CE} = 8 V	[1]			
		I _C = 5 mA	-	14	-	dB
		I _C = 20 mA	-	14	-	dB
		I _C = 30 mA	-	14	-	dB
		f = 1800 MHz; V _{CE} = 8 V	[1]			
		I _C = 5 mA	-	8.5	-	dB
		I _C = 20 mA	-	8.5	-	dB
		I _C = 30 mA	-	8.5	-	dB
s ₂₁ ²	insertion power gain	f = 433 MHz; V _{CE} = 8 V				
		I _C = 5 mA	-	16.5	-	dB
		I _C = 20 mA	-	18.5	-	dB
		I _C = 30 mA	-	18.5	-	dB
		f = 900 MHz; V _{CE} = 8 V				
		I _C = 5 mA	-	11	-	dB
		I _C = 20 mA	-	12.5	-	dB
		I _C = 30 mA	-	12.5	-	dB
		f = 1800 MHz; V _{CE} = 8 V				
		I _C = 5 mA	-	6	-	dB
		I _C = 20 mA	-	7	-	dB
		I _C = 30 mA	-	7	-	dB
NF _{min}	minimum noise figure	f = 433 MHz; V_{CE} = 8 V; Γ_{S} = Γ_{opt}				
		I _C = 5 mA	-	0.7	-	dB
		I _C = 20 mA	-	1.05	-	dB
		I _C = 30 mA	-	1.2	-	dB
		f = 900 MHz; V_{CE} = 8 V; Γ_{S} = Γ_{opt}				
		I _C = 5 mA	-	0.75	-	dB
		I _C = 20 mA	-	1.05	-	dB
		I _C = 30 mA	-	1.25	-	dB
		f = 1800 MHz; V_{CE} = 8 V; Γ_{S} = Γ_{opt}				1
		$I_{\rm C} = 5 \mathrm{mA}$	-	0.85	-	dB
		I _C = 20 mA	-	1.1	-	dB
		I _C = 30 mA	-	1.3	-	dB

NPN wideband silicon RF transistor

Table 9. Characteristics ...continued


 $T_{amb} = 25 \ ^{\circ}C$ unless otherwise specified

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
G _{ass}	associated gain	f = 433 MHz; V_{CE} = 8 V; Γ_{S} = Γ_{opt}				
		I _C = 5 mA	-	18	-	dB
		I _C = 20 mA	-	18.5	-	dB
		I _C = 30 mA	-	18.5	-	dB
		f = 900 MHz; V_{CE} = 8 V; Γ_{S} = Γ_{opt}				
		I _C = 5 mA	-	12	-	dB
		I _C = 20 mA	-	12.5	-	dB
		I _C = 30 mA	-	12.5	-	dB
		f = 1800 MHz; V_{CE} = 8 V; Γ_{S} = Γ_{opt}				
		I _C = 5 mA	-	6.5	-	dB
		I _C = 20 mA	-	7	-	dB
		I _C = 30 mA	-	7	-	dB
P _{L(1dB)}	output power at 1 dB gain compression	f = 433 MHz; V_{CE} = 8 V; Z_{S} = Z_{L} = 50 Ω				
		I _C = 20 mA	-	13	-	dBm
		I _C = 30 mA	-	16	-	dBm
		f = 900 MHz; V_{CE} = 8 V; Z_{S} = Z_{L} = 50 Ω				
		I _C = 20 mA	-	13	-	dBm
		I _C = 30 mA	-	15	-	dBm
		f = 1800 MHz; V_{CE} = 8 V; Z_S = Z_L = 50 Ω				
		I _C = 20 mA	-	13.5	-	dBm
		I _C = 30 mA	-	15	-	dBm
IP3 _o	output third-order intercept point	f_1 = 433 MHz; f_2 = 434 MHz; V_{CE} = 8 V; Z_S = Z_L = 50 Ω				
		I _C = 20 mA	-	22.5	-	dBm
		I _C = 30 mA	-	25.5	-	dBm
		$ f_1 = 900 \text{ MHz}; f_2 = 901 \text{ MHz}; \text{V}_{\text{CE}} = 8 \text{ V}; \\ Z_{\text{S}} = Z_{\text{L}} = 50 \ \Omega $				
		I _C = 20 mA	-	22.5	-	dBm
		I _C = 30 mA	-	24.5	-	dBm
		f_1 = 1800 MHz; f_2 = 1801 MHz; V _{CE} = 8 V; Z _S = Z _L = 50 Ω				
		I _C = 20 mA	-	23	-	dBm
		I _C = 30 mA	-	24.5	-	dBm

[1] If K > 1 then $G_{p(max)}$ is the maximum power gain. If K < 1 then $G_{p(max)}$ = MSG.

NPN wideband silicon RF transistor






Downloaded from Arrow.com.

BFU580Q


NPN wideband silicon RF transistor



BFU580Q


BFU580Q

NPN wideband silicon RF transistor




BFU580Q

NPN wideband silicon RF transistor




BFU580Q

NPN wideband silicon RF transistor




NPN wideband silicon RF transistor



Product data sheet

BFU580Q


NPN wideband silicon RF transistor




BFU580Q

BFU580Q

NPN wideband silicon RF transistor



NPN wideband silicon RF transistor



10. Application information

More information about the following application example can be found in the application notes. See <u>Section 5 "Design support</u>".

The following application example can be implemented using the evaluation kit. See <u>Section 3 "Ordering information"</u> for the order type number.


The following application example can be simulated using the simulation package. See <u>Section 5 "Design support</u>".

BFU580Q

10.1 Application example: FM LNA

FM LNA, optimized for low noise.

More detailed information of the application example can be found in the application note: *AN11499.*



Remark: fine tuning of components maybe required depending on PCB parasitics.

Table 10. Application performance data at 98 MHz

$I_{CC} = 25 \text{ mA}; V_{CC} = 5 \text{ V}$						
Symbol	Parameter	Conditions	Min	Тур	Max	Unit
$ s_{21} ^2$	insertion power gain		-	22	-	dB
NF	noise figure		-	1.6	-	dB
IP3 _o	output third-order intercept point	f = 88 MHz to 108 MHz; carrier spacing = 100 kHz	-	15	-	dBm

NPN wideband silicon RF transistor

11. Package outline




Fig 26. Package outline SOT89

BFU580Q

12. Handling information

CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Observe precautions for handling electrostatic sensitive devices.

Such precautions are described in the ANSI/ESD S20.20, IEC/ST 61340-5, JESD625-A or equivalent standards.

13. Abbreviations

Acronym	Description
AEC	Automotive Electronics Council
FM	Frequency Modulation
ISM	Industrial, Scientific and Medical
LNA	Low-Noise Amplifier
MSG	Maximum Stable Gain
NPN	Negative-Positive-Negative
SMA	SubMiniature version A

14. Revision history

Table 12.Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BFU580Q v.1	20140428	Product data sheet	-	-

15. Legal information

15.1 Data sheet status

Document status[1][2]	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications - This NXP

Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

NPN wideband silicon RF transistor

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

16. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NPN wideband silicon RF transistor

17. Contents

1	Product profile	1
1.1	General description	1
1.2	Features and benefits	1
1.3	Applications	1
1.4	Quick reference data	1
2	Pinning information	2
3	Ordering information	2
4	Marking	2
5	Design support	3
6	Limiting values	3
7	Recommended operating conditions	3
8	Thermal characteristics	4
9	Characteristics	4
9.1	Graphs	7
10	Application information	15
10.1	Application example: FM LNA	16
11	Package outline	17
12	Handling information	18
13	Abbreviations	18
14	Revision history	18
15	Legal information	19
15.1	Data sheet status	19
15.2	Definitions	19
15.3		19
15.4	Trademarks	20
16	Contact information	20
17	Contents	21

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP Semiconductors N.V. 2014.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 28 April 2014 Document identifier: BFU580Q