



DATE	DESCRIPTION	REV.
5.23.11	CHANGE AS PER ECN 11-067	A



SB3.0 'B' RECEPTACLE FOOTPRINT

TOLERANCE ±.002 [±0.05]

SOCKET SPECIFICATIONS:

- SHELL: MAT'L- BRASS, NICKEL PLATE
- CONTACT: MAT'L- PHOSPHOR BRONZE AND BRASS
- INSULATION: MAT'L- THERMOPLASTIC (COLOR- BLUE), UL 94V-0
- FINISH- GOLD FLASH OVER NICKEL ON CONTACT AREA
- TIN OVER NICKEL ON SOLDER TAILS

ELECTRICAL CHARACTERISTICS:

- CONTACT RESISTANCE: 30m Ω max.
- INSULATION RESISTANCE: 1000 mega Ω min.
- DIELECTRIC VOLTAGE : 1.8 Amp AT 250 V AC MIN.

MECHANICAL CHARACTERISTICS:

- OPERATING TEMPERATURE: -13°F (-25°C) TO 176°F (+80°C)
- INSERTION FORCE: 35N MAX.

KEYSTONE ELECTRONICS CORP.

www.keystone.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

PART NAME

USB 3.0 TYPE B

MATERIAL

AS NOTED

FINISH

AS NOTED

TOLERANCES	INCH	[MM]	CODE	DWG NO.
DECIMAL	± .010	[± 0.25]	C	950
ANGULAR	± 1°			

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.

DRN BY NT DATE 4.09.10

App'D LN SCALE 2X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[950](#)