

Standard Recovery Diodes, (Stud Version), 300 A



DO-9 (DO-205AB)


RoHS
COMPLIANT

FEATURES

- Alloy diode
- Popular series for rough service
- Stud cathode and stud anode version
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

- Welders
- Power supplies
- Motor controls
- Battery chargers
- General industrial current rectification

PRIMARY CHARACTERISTICS

$I_{F(AV)}$	300 A
Package	DO-9 (DO-205AB)
Circuit configuration	Single

MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{F(AV)}$		300	A
	T_C	150	°C
I_{FSM}	50 Hz	6550	A
	60 Hz	6850	
I^2t	50 Hz	214	kA ² s
	60 Hz	195	
V_{RRM}	Range	400	V
T_J		-65 to +200	°C

ELECTRICAL SPECIFICATIONS
VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT $T_J = 175\text{ °C}$ mA
VS-300U(R)..	10	100	200	40
	20	200	300	
	30	300	400	
	40	400	500	
	60	600	700	



FORWARD CONDUCTION						
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS	
Maximum average forward current at case temperature	$I_{F(AV)}$	180° conduction, half sine wave		300	A	
				130	°C	
Maximum peak, one cycle forward, non-repetitive surge current	I_{FSM}	t = 10 ms	No voltage reapplied	6550	A	
		t = 8.3 ms		Sinusoidal half wave, initial $T_J = T_J$ maximum		6850
		t = 10 ms	100 % V_{RRM} reapplied			5500
		t = 8.3 ms				5750
Maximum I^2t for fusing	I^2t	t = 10 ms	No voltage reapplied		214	kA ² s
		t = 8.3 ms		100 % V_{RRM} reapplied	195	
		t = 10 ms	151			
		t = 8.3 ms	138			
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	t = 0.1 to 10 ms, no voltage reapplied			2140	kA ² √s
Maximum value of threshold voltage	$V_{F(TO)}$	$T_J = 200$ °C		0.610	V	
Maximum value of forward slope resistance	r_f			0.751	mΩ	
Maximum forward voltage drop	V_{FM}	$I_{pk} = 942$ A, $T_J = 25$ °C		1.40	V	

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating and storage temperature range	T_J, T_{Stg}		-65 to +200	°C
Maximum thermal resistance, junction to case	R_{thJC}	DC operation	0.18	K/W
Maximum thermal resistance, case to heatsink	R_{thCS}	Mounting surface, smooth, flat and greased	0.08	
Maximum allowed mounting torque +0 -20 %		Not lubricated threads	37	Nm
		Lubricated threads	28	
Approximate weight			250	g
Case style		(JEDEC®) see dimensions - link at the end of datasheet	DO-9 (DO-205AB) ⁽¹⁾	

Note

⁽¹⁾ 302U-A uses case style B-26

ΔR_{thJC} CONDUCTION				
CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.020	0.015	$T_J = T_J$ maximum	K/W
120°	0.024	0.025		
90°	0.031	0.034		
60°	0.045	0.047		
30°	0.077	0.077		

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics





Fig. 8 - Thermal Impedance Z_{thJC} Characteristic



ORDERING INFORMATION TABLE




- 1** - Vishay Semiconductors product
- 2** - 30 = essential part number
- 3** - 0 = standard device
2 = 300U top threaded version
- 4** - • U = stud normal polarity (cathode to stud)
• UR = stud reverse polarity (anode to stud)
- 5** - Voltage code x 10 = V_{RRM} (see Voltage Ratings table)
- 6** - A = essential part number
- 7** - None = stud base DO-9 (DO-205AB) 3/4" 16UNF-2A
M20 = Metric device M20 x 1.5 (available with standard device only)

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95340




DO-9 (DO-205AB) and B-26 for 300U(R) Series

DIMENSIONS FOR 300U(R)-A SERIES - DO-9 (DO-205AB) in millimeters (inches)



DIMENSIONS FOR 302U(R)-A SERIES - B-26 in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.