



CT203

Article number: 132-20360



Cable Ties for single hole application (Chassis Tie) CT-Series with square head, 700 N loop tensile strength

The ties have serrations on both sides of the strap allowing for quick and easy installation, even where the access or visibility is poor.

The B and DE ranges offer a rounded head for applications where a good aesthetic appearance is required. The CT, LHT and SHT ranges have a square head which allows for optimum use in areas with restricted space. Prior to final tensioning these ties can be used as 'releasable' ties for the addition of extra cables. Once the cable runs are complete the final tensioning (by use of a suitable HellermannTyton tensioning tool) locks the tie in place.

Using a single hole these 'chassis ties' are widely used in the automotive, truck and heavy equipment markets. Ideal for applications which have access to both sides of the hole - for example truck frames.

Base Data

Application Tool	MK6, MK6PN, MK9, MK9HT, MK21
Colour	Black (BK)
EDP Text 1 Germany	Befestigungsbinder 200x7,6
EDP Text 2 Germany	CT203 Schwarz 50 ST ME
Fixation Method (FF)	Connector Clip
Product Headline 1	Cable Ties for single hole application (Chassis Tie)
Product Headline 2	CT-Series with square head, 700 N loop tensile strength
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Type	CT203.HB2P
Variant	Outside Serrated

Product Dimensions

Bundle \varnothing max.	50 mm
Cable Tie Head Height (Metric)	12 mm
Cable Tie Head Length (metric)	7.5 mm
Cable Tie Head Width (metric)	15 mm
Fixing Hole \varnothing (FH)	8.5 mm
Fixing Hole \varnothing (FH) min.	9.5 mm
Height (H)	1.5 mm
Height (H2)	7.5 mm
Hole \varnothing	10.5 mm
Length (L)	200 mm
Min. Tensile Strength (N)	700 N
Thickness (T)	1.5 mm
Width (W)	7.6 mm

Logistic and Packaging

Carton Quantity	2000 pcs.
EAN code	4031026115795
Pack Cont.	50
Quantity of Europallet	48000 pcs.
Quantity per	Bag
Weight (Kg)	2.21 kg

Material and Specifications

Cable Tie	Polyamide 6.6 Heat Stabilised (PA66HS)
Flammability	UL94 V2
Material	Polyamide 6.6 Heat Stabilised (PA66HS)
Material	PA66HS
Material Head	Polyamide 6.6 Heat Stabilised (PA66HS)
Operating Temperature	-40 °C to +105 °C, intermittent +145 °C (for 500 h)

© HellermannTyton 2012