

T4142012121-000 ✓ ACTIVE




## M12 Connector

TE Internal #: T4142012121-000

Standard Circular Connectors, Wire-to-Panel, 12 Position, Sealable, Signal, Panel Mount, Reverse Gender, Nickel, Brass, M12 Connector

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Panel Mount PCB



Connector System: **Wire-to-Panel**

Number of Positions: **12**

Sealable: **Yes**

Contact Current Rating (Max): **1.5 A**

Circuit Application: **Signal**

[All M12 Panel Mount PCB \(111\)](#)

## Features

### Product Type Features

Product Type	Connector Assembly
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Panel
Sealable	Yes
Circular Connector Type	Plug
Shell Type	Metal

### Configuration Features

Keying & Polarized Position Locations	A
Factory Installed Backshell	No
Keying	A
Number of Positions	12
Number of Power Positions	0



Number of Signal Positions	12
----------------------------	----

Contacts Preloaded	Yes
--------------------	-----

### Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

### Body Features

Peripheral Seal Material	Silicone
--------------------------	----------

Environmental Protection	IP67
--------------------------	------

O-Ring Material	Silicone
-----------------	----------

Environmental Protection Type	Elastomer Sealed
-------------------------------	------------------

Shell Plating Material	Nickel
------------------------	--------

Shell Base Material	Brass
---------------------	-------

Circular Connector Insulation Material Type	Polyamide 66 GF25
---	-------------------

### Contact Features

Contact Current Rating (Max)	1.5 A
------------------------------	-------

Reverse Gender	Yes
----------------	-----

Circular Connector Contact Type	Pin
---------------------------------	-----

### Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Polarization Code	A
-------------------	---

Mating Alignment Type	Keyed
-----------------------	-------

Mating Retention	With
------------------	------

### Housing Features

Circular Connector Shell Size	18
-------------------------------	----

### Usage Conditions

IP Water Sealing Level	IP67
------------------------	------

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

### Operation/Application

Circuit Application	Signal
---------------------	--------

Shielded	No
----------	----

### Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

### Packaging Features



Packaging Quantity	1
--------------------	---

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (4% in Component) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Also in the Series | M12 Connector



M8/M12 Cable Assemblies(230)



Standard Circular Connectors(519)

## Customers Also Bought



TE Part #T4111502051-000  
M12,MALE,STRAIGHT,D CODE,5P, PG9,GOLD



TE Part #T4111012081-000  
M12 M, 8P GOLD A\_CODE S SHIELDED PG9



TE Part #3-2198618-7  
Ni Pltd Plstic Backshell, 37 Way, 45 Deg



TE Part #2198618-9  
Ni Pltd Plastic Backshell, 9 Way, 45 Deg



TE Part #3-2198617-7  
Ni Plated Plastic Backshell, 37 Way, Str



TE Part #2-2176094-6  
RP 2A 0.25W 221K 0.1% 25PPM 1K RL



TE Part #2-2176094-8  
RP 2A 0.25W 232K 0.1% 25PPM 1K RL



TE Part #6-2271129-2  
M12,FEMALE,A CODE,R/A,12P,PG9, SHIELD(AU)



TE Part #1-2176094-6  
RP 2A 0.25W 169K 0.1% 25PPM 1K RL

## Documents

### Product Drawings

M12,FRONT MOUNT,MALE, A,12P,SOLDER PCB

English

### CAD Files

Customer View Model

ENG\_CVM\_CVM\_T4142012121-000\_B.3d\_igs.zip



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_T4142012121-000\\_B.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_T4142012121-000\\_B.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

[M12 PCB/Panel Connectors 8/12Pin](#)

English

---

### Product Specifications

[Application Specification](#)

English