

Specification Sheet

Part Number: IMP2.510C2

Identification Marker Plates can be marked with a permanent pen, printed labels or hot stamped for a wide variety of labeling options.

Any size bundle diameter can be marked because it is only dependent upon the length of the cable tie selected, provided the cable tie width does not exceed .29".



The marker plates are stamped from nylon, making them a durable and long term method of identification.

The mounting holes are positioned to allow the marker to be mounted as a flag, tag or wrapped around the cable or bundle for a wide variety of installed positions.

Identification Marker Plate, 2.5" x .75", Nylon, White, 100/pkg

Article Number 151-42259

Type IMP2.5

Color White (WH)

Quantity Per bag

Product Description Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.

Short Description	Identification Marker Plate, 2.5" x .75", Nylon, White, 100/pkg
Global Part Name	IMP2.5-PA66-WH
Length L (Imperial)	2.5
Length L (Metric)	63.5
Fixation Method	Others
Identification Plate Position	attached to bundle
Variant	Other
Width W (Imperial)	2.5
Width W (Metric)	19.3
Thickness T (Imperial)	0.016
Thickness T (Metric)	0.4
Height H (Imperial)	0.75
Height H (Metric)	19.05
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.80

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Weight (Metric)	0.06
Weight (Imperial)	0.132

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[IMP2.510C2](#)