

1

2







3

4

5


6

REV.	ECN NO OR DESCRIPTION	REVISED	DATE
▽	PROPOSE ONLY	ALLEN	2011.04.08



-NOTE-

- *Electrical Characteristics:
Contact Current Rating:0.5 Amperes.
Dielectric Withstanding Voltage:AC500V r.m.s.
Insulation Resistance:1000 MΩ Minimum.
Contact Resistance:40 mΩ Maximum.
- *Environmental:
Operating Temperature:-25°C+90°C.
- *Environmental:
Mating Cycles:3,000 Insertions.
- *Mechanical Characteristics:
Card Push Insertion/Out Force:0.7N±0.20kgf.
Contact Separation Force:0.20kgf Minimum.
- *Material:
Insulator:HI-Temp Plastic UL 94V-0 Rated.
Contact:Copper Alloy(t=0.15mm).
Shell:Stainless Steel(t=0.15mm).



RECOMMENDED P.C.BOARD LAYOUT(TOP VIEW)
GENERAL TOLERANCE:±0.05

3	TERMINAL	6	COPOER ALLOY	CONTACT Au OVER ALL:
2	SHELL	1	STAILESS STELL	
1	HOUSING	1	THERMOPLASTIC	UL 94V-0
NO.	DESCRIPTION	QT'Y	MATERIAL	NOTE
UNLESS OTHERWISE SPECIFIED TOLERANCES				
DECIMALS: X :±0.5 X.X :±0.20 X.XX :±0.10		TITLE 1.8H HINGE MICRO SIM CARD CONN		
ANGLES: X :±2° X.X :±1°		DWN ALLEN PART NO. AMT-USIM-1.8J		
		CHKD KEVIN	SCALE:1:1	UNIT: mm
		APVD ERIC.W	SIZE: A3	SHEET:10F 1
		REV: A1		
CUSTOMER COPY				

1

2

3

4

5

6