

MG series

T1 3/4 Midget groove based LED's •
single or multichip LED illumination



DISTINCTIVE FEATURES

T1 3/4 Midget groove based LED for bulb replacement

Operating & Storage Temperature Range: -20 °C to +70 °C
(-4 °F to +158 °F)

12 VDC to 28 VAC/DC 14 mA, mcd range from 490 to 2,070
dependent on version



MATERIALS

- Body : Polycarbonate
- Base : Nickel plated brass



BUILD YOUR PART NUMBER



For other voltage options please contact APEM

LUMINOUS INTENSITY

	Voltage
Color	12 V, 24 V & 28 V
R - Red	1,750 mcd
G - Green	1,610 mcd
Y - Yellow	630 mcd
B - Blue	490 mcd
W - White	2,070 mcd

The company reserves the right to change specifications without notice.

MG series

T1 3/4 Midget groove based LED's •
single or multichip LED illumination



BUILD YOUR PART NUMBER

MG MULTI CHIP

MG

SERIES

TYPE

M Multi Chip

COLOR

R Red
G Green
Y Yellow

VOLTAGE & CURRENT AC/DC

12 12 V - 30 mA
24 24 V - 14 mA
28 28 V - 14 mA

OPTIONS


A AC/DC version

For other voltage options please contact APEM

LUMINOUS INTENSITY

	Voltage
Color	12 V, 24 V & 28 V
R - Red	40 mcd
G - Green	35 mcd
Y - Yellow	45 mcd

MG - MULTI CHIP RED



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[MGSG28](#) [MGSR28](#) [MGSW24](#) [MGSG12](#) [MGSY24](#) [MGSR12](#) [MGSY28](#) [MGSW12](#) [MGSG24](#) [MGSW28](#) [MGSR24](#)
[MGSB28](#)