

Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of http://www.nxp.com, http://www.nxp.com, http://www.nexperia.com, http://www.nexperia.com)

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.


If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

DISCRETE SEMICONDUCTORS

DATA SHEET



BCX71 seriesPNP general purpose transistors

Product data sheet Supersedes data of 1999 Apr 20



NXP Semiconductors Product data sheet

PNP general purpose transistors

BCX71 series

FEATURES

• Low current (max. 100 mA)

• Low voltage (max. 45 V)

• Low noise.

APPLICATIONS

- Low level, low noise, low frequency applications in hybrid circuits
- · General purpose switching and amplification.

DESCRIPTION

PNP transistor in a plastic SOT23 package. NPN complements: BCX70 series.

MARKING

TYPE NUMBER	MARKING CODE ⁽¹⁾
BCX71H	BH*
BCX71J	BJ*
BCX71K	BK*

Note


1. * = p : Made in Hong Kong.

* = t : Made in Malaysia.

* = W : Made in China.

PINNING

PIN	DESCRIPTION
1	base
2	emitter
3	collector



ORDERING INFORMATION

TYPE	PACKAGE					
NUMBER	NAME	VERSION				
BCX71H	_	plastic surface mounted package; 3 leads	SOT23			
BCX71J						
BCX71K						

NXP Semiconductors Product data sheet

PNP general purpose transistors

BCX71 series

LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V _{CBO}	collector-base voltage	open emitter	_	-45	V
V _{CEO}	collector-emitter voltage	open base	_	-45	V
V _{EBO}	emitter-base voltage	open collector	_	-5	V
I _C	collector current (DC)		_	-100	mA
I _{CM}	peak collector current		_	-200	mA
I _{BM}	peak base current		_	-200	mA
P _{tot}	total power dissipation	T _{amb} ≤ 25 °C	_	250	mW
T _{stg}	storage temperature		-65	+150	°C
Tj	junction temperature		_	150	°C
T _{amb}	operating ambient temperature		-65	+150	°C

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R _{th(j-a)}	thermal resistance from junction to ambient	note 1	500	K/W

Note

1. Transistor mounted on an FR4 printed-circuit board.

2004 Feb 16 3

NXP Semiconductors Product data sheet

PNP general purpose transistors

BCX71 series

CHARACTERISTICS

 T_{amb} = 25 °C unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
I _{CBO}	collector-base cut-off current	I _E = 0; V _{CB} = -45 V	_	-	-20	nA
		I _E = 0; V _{CB} = -45 V; T _{amb} = 150 °C	_	_	-20	μΑ
I _{EBO}	emitter-base cut-off current	$I_C = 0; V_{EB} = -4 V$	_	_	-20	nA
h _{FE}	DC current gain	$I_C = -10 \mu A; V_{CE} = -5 V$				
	BCX71H		30	_	_	
	BCX71J		40	_	_	
	BCX71K		100	_	_	
	DC current gain	$I_C = -2 \text{ mA}; V_{CE} = -5 \text{ V}$				
	BCX71H		180	_	310	
	BCX71J		250	_	460	
	BCX71K		380	_	630	
	DC current gain	$I_C = -50 \text{ mA}$; $V_{CE} = -1 \text{ V}$; note 1				
	BCX71H		80	_	_	
	BCX71J		100	_	_	
	BCX71K		110	_	_	
V _{CEsat}	collector-emitter saturation	$I_C = -10 \text{ mA}; I_B = -0.25 \text{ mA}$	-60	_	-250	mV
	voltage	$I_C = -50 \text{ mA}$; $I_B = -1.25 \text{ mA}$; note 1	-120	_	-550	mV
V _{BEsat}	base-emitter saturation	$I_C = -10 \text{ mA}; I_B = -0.25 \text{ mA}$	-600	_	-850	mV
	voltage	$I_C = -50 \text{ mA}$; $I_B = -1.25 \text{ mA}$; note 1	-680	_	-1050	mV
V_{BE}	base-emitter voltage	$I_C = -2 \text{ mA}; V_{CE} = -5 \text{ V}$	-600	-650	-750	mV
		$I_C = -10 \mu A; V_{CE} = -5 V$	_	-550	_	mV
		$I_C = -50 \text{ mA}; V_{CE} = -1 \text{ V}; \text{ note 1}$	_	-720	_	mV
C _c	collector capacitance	$I_E = I_e = 0$; $V_{CB} = -10 \text{ V}$; $f = 1 \text{ MHz}$	_	4.5	_	pF
C _e	emitter capacitance	$I_C = I_c = 0$; $V_{EB} = -0.5 \text{ V}$; $f = 1 \text{ MHz}$	_	11	_	pF
f _T	transition frequency	$I_C = -10 \text{ mA}$; $V_{CE} = -5 \text{ V}$; $f = 100 \text{ MHz}$	100	-	_	MHz
F	noise figure	$I_C = -200 \ \mu A; \ V_{CE} = -5 \ V; \ R_S = 2 \ k\Omega; \ f = 1 \ kHz; \ B = 200 \ Hz$	_	2	6	dB

Note

1. Pulse test: $t_p \leq 300~\mu s;~\delta \leq 0.02.$

NXP Semiconductors Product data sheet


PNP general purpose transistors

BCX71 series

SOT23

PACKAGE OUTLINE

Plastic surface-mounted package; 3 leads



ι	JNIT	Α	A ₁ max.	bp	С	D	E	е	e ₁	HE	Lp	Q	v	w
	mm	1.1 0.9	0.1	0.48 0.38	0.15 0.09	3.0 2.8	1.4 1.2	1.9	0.95	2.5 2.1	0.45 0.15	0.55 0.45	0.2	0.1

OUTLINE REFERENCES					EUROPEAN	ISSUE DATE
VERSION	IEC	JEDEC	EDEC JEITA PROJECTION		ISSUE DATE	
SOT23		TO-236AB				-04-11-04 06-03-16

NXP Semiconductors Product data sheet

PNP general purpose transistors

BCX71 series

DATA SHEET STATUS

DOCUMENT STATUS ⁽¹⁾	PRODUCT STATUS ⁽²⁾	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

Notes

- 1. Please consult the most recently issued document before initiating or completing a design.
- 2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

DISCLAIMERS

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

2004 Feb 16 6

NXP Semiconductors

Customer notification

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

Contact information

For additional information please visit: http://www.nxp.com
For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands R75/04/pp7 Date of release: 2004 Feb 16 Document order number: 9397 750 12409



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nexperia:

BCX71H,235 BCX71H,215 BCX71J,235 BCX71J,215 BCX71K,235 BCX71K,215