









Typical Specifications
 1. Rating : DC 12V 50mA
 2. Contact Resistance: $\leq 100m\Omega$
 3. Travel: $0.2 \pm 0.05mm$
 4. Life : 100,000 Cycles



Circuit Diagram



PCB Layout(Pattern side)

NO.1	
PART NO	vigor
3	180±30
4	250±30

NO.2	
PART NO	MATERIAL/QTY
D	SUS/2PC

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑥	Dust cover	---	2	---	Yellow	---
⑤	Terminal	---	4	Kapton film	Plating silver	---
④	Contact	---	2	SUS	Plating silver	---
③	Base	---	1	LCP	White	---
②	Cover	---	1	Brass	Plating silver	---
①	Knob	---	1	PA46	Black	---

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhong	2018/8/1	TACT SWITCHS

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---	A	---	NEW	---	---	---

APPROVALS	DATE	TITLE:
CHECKED	---	TACT SWITCHS
APPROVALS	---	---

TOLERANCES ARE	ANGLE	UNIT:	SCALE:	DRAWING NO.	SHEET
30~0.1±	±0.30	mm	1:1	---	1 OF 1
10~30	±0.20	---	---	---	---
5~10	±0.15	---	---	---	---
~5	±0.10	---	---	---	---

PROJ: