# 0402 SMD TYPE LED

OPTOELECTRONICS



VAOL-S4WR4


### Features

- Fit automatic placement equipment.
- Fit Compatible with infrared and vapor phase reflow solder process.
- Pb-free.
- RoHS compliant.

### Descriptions

- For higher packing density .
- For minature applications .
- Yellow Diffusion Lens .
- Chip material : InGaN.
- Emitting color : White .

### **Package Outline Dimensions**



**Note:** The tolerances unless mentioned is  $\pm 0.1$  mm, Unit = mm





OPTOELECTRONICS



	(10 20 0)		
Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	IF	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	Ifp	100	mA
Power Dissipation	Pd	110	mW
Electrostatic Discharge(HBM)	ESD	150	V
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	$-40 \sim +90$	°C
Soldering Temperature	Tsol	Reflow Soldering : $260$ °CHand Soldering : $350$ °C	for 10 sec. for 3 sec.

# Absolute Maximum Ratings (Ta=25°C)







Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	57		112	mcd	
Viewing Angle	2 <del>0</del> 1/2		130		deg	IF=5mA
Forward Voltage	Vf	2.6		3.0	V	
Reverse Current	Ir			50	$\mu A$	V <sub>R</sub> =5V

# **Electro-Optical Characteristics (Ta=25°C)**

### Bin Range Of Luminous Intensity & Forward Voltage

		·	C	,	1
Symbol	Bin Code	Min.	Max.	Unit	Condition
Iv	P2	57	72		
	Q1	72	90	mcd	IF=5mA
	Q2	90	112		
VF	28	2.6	2.7	V	IF=5mA
	29	2.7	2.8		
	30	2.8	2.9		
	31	2.9	3.0		

Specific binning requirements- please contact our home office

### Notes:

1.Tolerance of Luminous Intensity ±10% 2.Tolerance of Forward Voltage ±0.05V









Group	Bin Code	CIE_x	CIE_y	Condition
C	1 -	0.274	0.226	
		0.274	0.258	
		0.294	0.286	
		0.294	0.254	
	2	0.274	0.258	
		0.274	0.291	
		0.294	0.319	
		0.294	0.286	$I_{F}=5mA$
	3	0.294	0.254	
		0.294	0.286	
		0.314	0.315	
		0.314	0.282	
	4	0.294	0.286	
		0.294	0.319	
		0.314	0.347	
		0.314	0.315	

## **Chromaticity Coordinates Specifications for Bin Grading**

#### Notes:

1. The C.I.E. 1931 chromaticity diagram ( Tolerance  $\pm 0.01$  ).

2. The products are sensitive to static electricity and care must be fully taken when handling products.






OPTOELECTRONICS



# **CIE** Chromaticity Diagram








OPTOELECTRONICS

VGG OP




# **Typical Electro-Optical Characteristics Curves**








### **Reel Dimensions**















# Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel

**Note:** The tolerances unless mentioned is  $\pm 0.1$  mm ,Unit = mm

### **Moisture Resistant Packaging**










### Soldering Condition

1.Pb-free solder temperature profile



- 2.Reflow soldering should not be done more than two times.
- 3 When soldering, do not put stress on the LEDs during heating.
- 4 After soldering, do not warp the circuit board.

Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than  $350^{\circ}$ C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.







# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC: VAOL-S4WR4