

CERAMIC SURFACE MOUNT LOW PROFILE QUARTZ CRYSTALS

ABMM2

 RoHS/RoHS II Compliant

ABMM2



6.0 x 3.6 x 1.2 mm

FEATURES:

- Suitable for RoHS compliant reflow
- Low height 1.2 mm max
- Seam sealed ceramic package assures high reliability
- Available tight tolerance and stability

APPLICATIONS:

- Computers, Modems, Microprocessors
- Communication, Test equipment
- PCMCIA

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		7.3728		110.00	MHz	
Operation Mode	7.3728 – 30.00MHz	Fundamental				Standard
	30.01 – 100.00MHz	3 rd Overtone				Standard
	100.01 – 110.00MHz	5 th Overtone				Standard
	30.01 – 50.00MHz	Fundamental				See options
Operating Temperature		-10		+60	°C	See options
Storage Temperature		-40		+85	°C	
Frequency Tolerance @+25°C		-20		+20	ppm	See options
Frequency Stability over the Operating Temperature (ref. to +25°C)		-20		+20	ppm	See options
Equivalent series resistance (R1)		See table 1 below			Ω	
Shunt capacitance (C0)				7.0	pF	
Load capacitance (CL)			18.0		pF	Standard (See options if other than STD)
Drive Level			100	500	μW	
Aging		-2		+2	ppm	@25°C±3°C First year
Insulation Resistance		500			MΩ	@ 100Vdc ± 15V

TABLE 1- Standard ESR

Frequency (MHz)	ESR(Ω) max
7.3728 -7.999999 (Fund)	150
8.000 -9.999999 (Fund)	72
10.000 -50.000 (Fund)	50
30.000 – 100.000 (3 rd OT)	60
100.001 – 110.000 (5 th OT)	80

CERAMIC SURFACE MOUNT LOW PROFILE QUARTZ CRYSTALS

ABMM2

 RoHS/RoHS II Compliant

ABMM2



6.0 x 3.6 x 1.2 mm

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)

ABMM2 - MHz - - - - -

Frequency in MHz

Please specify the frequency in MHz.
e.g. 16.000MHz

Packaging

Blank: Bulk
T: 1000pcs / reel
T2: 250pcs / reel

Load Capacitance (pF)

Please specify CL in pF
(8 to 33pF) or S for series
Please contact Abracon
for other values

Freq. Stability

Blank: Standard
F; fund. AT for
F>30MHz

Custom ESR if other than standard

R□
□: Specify a value in
Ω (e.g.: R40)

Freq. Tolerance

1: ± 10 ppm
7: ± 15 ppm

Frequency Stability (ppm)

Operating Temp.	±10	±20	±30	±50	±100
0°C ~ +50° C	A3	A4	A6	-----	-----
-10°C ~ +50°C	B3	B4	B6	-----	-----
-10°C ~ +60°C	C1	Std	C6	-----	-----
-20°C ~ +70°C	E1	E2	E6	-----	-----
-40°C ~ +85°C	-----	D1	D6	D5	-----
-40°C ~ +1 05°C	-----	-----	-----	J5	J10
-40°C ~ +1 25°C	-----	-----	-----	K5	K10



CERAMIC SURFACE MOUNT LOW PROFILE QUARTZ CRYSTALS



ABMM2

 RoHS/RoHS II Compliant

ABMM2

6.0 x 3.6 x 1.2 mm


OUTLINE DRAWING:



Dimensions: inches (mm)


Note 1: A chamfer of 0.3mm may appear on pad 1 or 4
Note 2: A rounded pad may appear on pad 1
Note 3: Pin 2 and 4 are connected to the metal lid.
 Please connect to GND

TAPE & REEL:



Dimensions: mm

REFLOW PROFILE



ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED

ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale
 30332 Esperanza, Rancho Santa Margarita, California 92688
 tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 01.18.13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ABMM2-12.000MHZ-B2-T](#) [ABMM2-27.000MHZ-E2-T](#) [ABMM2-8.000MHZ-E2-T](#) [ABMM2-19.6608MHZ-E2-T](#) [ABMM2-14.31818MHZ-E2-T](#) [ABMM2-24.000MHZ-B2-T](#) [ABMM2-10.000MHZ-B2-T](#) [ABMM2-20.000MHZ-B2-T](#) [ABMM2-16.000MHZ-E2-T](#) [ABMM2-16.000MHZ-B2-T](#) [ABMM2-11.0592MHZ-E2-T](#) [ABMM2-12.000MHZ-E2-T](#) [ABMM2-20.000MHZ-E2-T](#) [ABMM2-11.0592MHZ-B2-T](#) [ABMM2-32.000MHZ-2BF-T](#) [ABMM2-27.000MHZ-B2-T](#) [ABMM2-25.000MHZ-B2-T](#) [ABMM2-16.9344MHZ-E2-T](#) [ABMM2-19.6608MHZ-B2-T](#) [ABMM2-24.000MHZ-E2-T](#) [ABMM2-14.31818MHZ-B2-T](#) [ABMM2-10.000MHZ-E2-T](#) [ABMM2-14.7456MHZ-B2-T](#) [ABMM2-25.000MHZ-E2-T](#) [ABMM2-16.9344MHZ-B2-T](#) [ABMM2-8.000MHZ-B2-T](#) [ABMM2-14.7456MHZ-E2-T](#) [ABMM2-24.576MHZ-B2-T](#) [ABMM2-24.576MHZ-E2-T](#) [ABMM2-32.000MHZ-E2-T](#) [ABMM2-32.000MHZ-E2F-T](#) [ABMM2-8.0000MHZ-E1-T](#) [ABMM2-25.000MHZ-D1-T](#) [ABMM2-40.000MHZ-E2F-T](#) [ABMM2-7.3728MHZ-E2-T](#) [ABMM2-12.9000MHZ-E2-T](#) [ABMM2-14.7456MHZ-D1-T](#) [ABMM2-32.00MHZ-E2-FT](#) [ABMM2-48.000MHZ-E2F-T](#) [ABMM2-50.000MHZ-E2F-T](#) [ABMM2-32.768MHZ-E2F-T](#) [ABMM2-8.000MHZ-D1-T](#) [ABMM2-10.000MHZ-D1-T](#) [ABMM2-8.000MHZ-D6-T](#) [ABMM2-7.3728MHZ-D1-T](#) [ABMM2-25.000MHZ-T](#) [ABMM2-16.000MHZ-D1-T](#)