







DATE	DESCRIPTION	REV.
5.31.11	CHANGE AS PER ECN 11-075	A
3.21.16	CHANGE AS PER ECN 16-039	B



Notes:

- Shell: Mat'l: Brass, Finish: Nickel Plate
- Insulator: Mat'l: LCP
- Contacts: Mat'l: Phosphor Bronze Finish: Gold Plate over Nickel on contact area. Tin Plate over nickel on solder Tail.

Electrical Specifications

- Contact Resistance: 50 milliohms Max.
- Insulation Resistance: 500 Mega Ohm.
- Dielectric Voltage: 100V AC max. current : 1 Amp



ACTUAL SIZE

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.

KEYSTONE ELECTRONICS CORP.			
www.kevelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
USB MINI TYPE HORIZONTAL SOCKET			
MATERIAL			
AS NOTED			
FINISH			
AS NOTED			
TOLERANCES		INCH	[MM]
DECIMAL	± .010	[± 0.25]	
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED		CODE	DWG NO.
		C	934
DRN BY	DATE	SCALE	
NT	12.17.08	5X	
APP'D			
LN			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[934](#)