		TEST CONDITIONS	OPERATING CHARACTERISTICS AT 25°C AMBIENT								
DIALIGHT PART NUMBER	LED & LENS COLOR		LUMINOUS INTENSITY (mcd)		FORWARD VOLTAGE		FORWARD CURRENT		DOMINANT WAVELENGTH (nm)		VIEWING ANGLE (DEG)
			MIN	TYP	TYP	MAX	MIN	MAX	TYP	TYP	TYP
555-4001F	RED, TINTED, DIFFUSED	Ir = IOmA	0.4	0.6	1.6	2.0			640	655	35
555-4003F	RED, TINTED, DIFFUSED, INT RES, 5V	Vf = 5V	1.0	2.5			3.7	8.70	640	655	35
555-4007F	RED, TINTED, DIFFUSED, INT RES, 5V	Vf = 5V	0.4	0.6			2.2	4.3	640	655	35
555-4008F	RED, TINTED, DIFFUSED, INT RES, 24V	Vr = 24V	0.4	0.6			2.3	4. I	640	655	35
555-4009F	RED, TINTED, DIFFUSED, INT RES, 5V	Vf = 5V	0.4	0.6				2.6	640	655	35
555-4301F	HI. PERF. GREEN, TINTED, DIFFUSED	IF = IOmA	6.3	25	2.1	2.7			569	565	35
555-4303F	HI. PERF. GREEN, TINTED, DIFF, INT RES, 5V	Vf = 5V	1.0	2.0			3.3	13.0	569	565	35
555-4401F	YELLOW, TINTED, DIFFUSED	IF = IOmA	16	50	2.0	2.4			585	583	35
555-4403F	YELLOW, TINTED, DIFFUSED, INT RES, 5V	Vr = 5V	1.6	5.0			3.5	5.3	585	583	35

SOLDERING

260 °C

260 °C

260 °C

260 °C

260 °C

STORAGE

TEMPERATURE TEMPERATURE TEMPERATURE (°C) (°C) (FOR 5 SEC)

-55 TO +100

-55 TO +100

-55 to +100 -55 TO +100

-40 to +100 -55 TO +100

-20 to +85 | -55 TO +100

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT

OPERATING

-40 to +85

-40 to +85

REVERSE

VOLTAGE

(| R = | 0 0 m A)

5 V

5 V

5 V

5 V

5 V

DC

FORWARD

VOLTAGE

6 V

24 V

6 V

FORWARD

CURRENT

50 mA

30 mA

LED COLOR

RED

RED, INT RES, 5V

RED, INT RES, 24V

GREEN

GREEN, INT RES, 5V


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A		NEW RELEASE	AJF	KLJ	NO	7-30-09

RoHS Compliant 555-4X0XF


Part Numbers with the "F" suffix ending are RoHS Compliant. Example: 555-4003F Packaging is marked with "RoHS Compliant" label or equivalent markings. Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp. for 5 sec.


NOTES:


- I. PIN MUMBERS FOR REFERENCE ONLY. DESIGNATION NON-EXISTENT ON PART.
- 2. DIALIGHT PART NUMBERS: 555-4X0XF.
 3. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS), MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.
- 4. LED LEAD DIMENSIONS SHOWN ARE MEASURED AT HOUSING EXIT.
- 5. LEADS TO FIT INTO HOLES SPACED AS PER PATTERN.
- 6. LED LEADS PURE Sn PLATING OVER OLIN 194 COPPER ALLOY BASE METAL.



NOM. TYP.







Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

555-4303F 555-4001F 555-4301F 555-4007F 555-4403F 555-4401F 555-4003F 555-4008F 555-4009F