


## GLASS PASSIVATED BRIDGE RECTIFIERS

REVERSE VOLTAGE - 50 to 1000Volts  
FORWARD CURRENT - 15.0 Amperes

### FEATURES

- Surge overload rating -240 amperes peak
- Ideal for printed circuit board
- Reliable low cost construction utilizing molded plastic technique
- Plastic material has U/L flammability classification 94V-0
- Mounting position: Any

### GBU



Dimensions in inches and (millimeters)

### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	GBU 15005	GBU 1501	GBU 1502	GBU 1504	GBU 1506	GBU 1508	GBU 1510	UNIT	
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V	
Maximum RMS Voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	V	
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	V	
Maximum Average Forward (with heatsink Note 2) Rectified Current @ T <sub>c</sub> =100°C (without heatsink)	I <sub(av)< sub=""></sub(av)<>					15.0				A
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	I <sub>FSM</sub>					240				A
Maximum Forward Voltage at 7.5A DC	V <sub>F</sub>					1.0				V
Maximum DC Reverse Current @ T <sub>J</sub> =25°C at Rated DC Blocking Voltage @ T <sub>J</sub> =125°C	I <sub>R</sub>					10.0				μA
I <sup>2</sup> t Rating for Fusing (t<8.3ms)	I <sup>2</sup> t					239				A <sup>2</sup> s
Typical Junction Capacitance Per Element (Note1)	C <sub>J</sub>					70				pF
Typical Thermal Resistance	R <sub>θJC</sub>					2.2				°C/W
Operating Temperature Range	T <sub>J</sub>					-55 to +150				°C
Storage Temperature Range	T <sub>STG</sub>					-55 to +150				°C

NOTES: 1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

2. Device mounted on 100mm\*100mm\*1.6mm Cu plate heatsink.

3. The typical data above is for reference only (典型值仅供参考).

FIG.1-MAXIMUM FORWARD SURGE CURRENT




FIG.2- DERATING CURVE  
 OUTPUT RECTIFIED CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS





FIG.4-TYPICAL REVERSE CHARACTERISTICS



The cruve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!