





SPECIFICATIONS

Current Rating: 3AMP
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstand Voltage: 1000V AC/minute
 Operation Temperature: -40 degree up +105 degree

Contact: Brass
 plating: Au or Sn Over 50u" Ni
 Insulator: High Temperature Thermoplastic
 UL94V-0 Rated
 Standard: PBT+30%G.F



Recommended PCB Layout

T821 X XX XX S1 00 C EU

Box Header:
2.54mm Pitch

Housing Color
0: Grey
1: Black

No of Positions:
06: 6 positions
:
:
64: 64 positions

Plating Options:
A1: Flash Gold
A2: 15u"/0,4um Gold
A3: 30u"/0,8um Gold
SN: Tin

EU: RoHS
Compliant

C: Fixed Index

Variation Code:
00: Standard
(No Latch)

Termination:
S1: Straight THT
R1: Right Angled THT



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL Amphenol European Design Center	
X. ±0.3	DRAWN Roger	12/Jun/2006	Box header 2.54pitch DIP	Scale N.A.	Sheet 1 of 1
XX ±0.2	CHECKED Rob K.	13/Jun/2006			
XXX ±0.15	APPROVED Rob K.	14/Jun/2006			
UNLESS OTHERWISE SPECIFIED	UNLESS OTHERWISE SPECIFIED	UNIT: mm	SIZE: A4	DRAWING N° T821XxxXXS100CEU	
					REV. A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[T821120A1S100CEU](#)