Radial, Molded, COG Dielectric, 50 – 200 VDC (Commercial Grade)



Overview

KEMET's epoxy molded radial through-hole ceramic capacitors in COG dielectric feature a 125°C maximum operating temperature. The Electronics Industries Alliance (EIA) characterizes COG dielectric as a Class I "stable" material. Components of this classification are temperature compensating and are suited for resonant circuit applications or those where Q and stability of capacitance characteristics are required. COG exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to ±30 ppm/°C from -55°C to +125°C. These devices meet the flame test requirements outlined in UL Standard 94 V-0.

Applications

Typical applications include critical timing, tuning, circuits requiring low loss, circuits with pulse, high current, decoupling, bypass, filtering, transient voltage suppression, blocking and energy storage.

Benefits

- · Radial through-hole form factor
- · Molded case
- -55°C to +125°C operating temperature range
- DC voltage ratings of 50 V, 100 V and 200 V
- Capacitance offerings ranging from 1.0 pF up to 0.18 μF
- Available capacitance tolerances of ±0.5 pF, ±1%, ±2%, ±5%, and ±10%
- No piezoelectric noise
- Extremely low ESR and ESL
- · High thermal stability
- · High ripple current capability
- No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- · No capacitance decay with time
- · Non-polar device, minimizing installation concerns
- SnPb-plated lead finish (60/40)
- 100% pure matte tin-plated lead finish option available upon request (RoHS)
- Encapsulation meets flammability standard UL 94 V-0





Ordering Information

С	052	С	272	F	2	G	5	Т	Α	7303
Ceramic	Style/ Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance ¹	Rated Voltage (VDC)	Dielectric	Design	Lead Finish ²	Failure Rate	Packaging/ Grade (C-Spec) ³
	052 062 512 522	C = Standard	Two significant digits and number of zeros Use 9 for 1.0 - 9.9 pF Use 8 for 0.599 pF ex. 2.2 pF = 229 ex. 0.5 pF = 508	D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10%	1 = 100 2 = 200	G = COG	5 = Multilayer	T = 100% Matte Sn C = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

¹ Additional capacitance tolerance offerings may be available. Contact KEMET for details.

Standard: 60% tin (Sn)/40% lead (Pb) finish with 100% copper core ("C" designation).


Optional (C052 and C062 only): 100% matte tin (Sn) with nickel (Ni) underplate and steel core ("T" designation).

Alternative lead materials and finishes may be available. Contact KEMET for details.

C-Spec 7301: Recommended for straight lead configuration part types.

C-Spec 7301: Recommended for formed (bent) lead configuration part types.

Dimensions - Inches (Millimeters)



Series	Style/ Size	S Lead Spacing	L Length	H Height	T Thickness	LD Lead Diameter	LL Lead Length Minimum
C05X	052/056	0.20±0.015	0.19±0.01 (4.83±0.25)	0.19±0.01 (4.83±0.25)	0.09±0.01 (2.29±0.25)		
C06X	062/066	(5.08±0.38)	0.29±0.01 (7.37±0.25)	0.29±0.01 (7.37±0.25)	0.09±0.01 (2.29±0.25)	0.025+0.004/-0.002	1.05 (01.75)
OFVV	512	0.40±0.02	0.48±0.02 (12.19±0.51)	0.48±0.02 (12.19±0.51)	0.14±0.01 (3.56±0.25)	(0.635+0.102/-0.051)	1.25 (31.75)
C5XX	522	(10.16±0.51)	0.48±0.02 (12.19±0 .51)	0.48±0.02 (12.19±0.51)	0.24±0.01 (6.10±0.25)		

² Lead materials and finishes:

³ Reeling options:



Application Notes

These devices are not recommended for use in overmold applications and/or processes

Qualification/Certification

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 2, Performance & Reliability.

Environmental Compliance

Devices with standard lead finish option of 60% tin (Sn)/40% lead (Pb) do not meet RoHS criteria. Devices with 100% matte tin (Sn) lead finish option are RoHS Compliant (C052 & C062 only).

Electrical Parameters/Characteristics

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +125°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±30 ppm/°C
Aging Rate (Maximum % Cap Loss/Decade Hour)	0%
Dielectric Withstanding Voltage	250% of rated voltage (5±1 seconds and charge/discharge not exceeding 50 mA)
Dissipation Factor (DF) Maximum Limit at 25°C	0.1%
Insulation Resistance (IR) Limit at 25°C	1,000 megohm microfarads or 100 GΩ (Rated voltage applied for 120±5 seconds at 25°C)

To obtain IR limit, divide $M\Omega$ - μ F value by the capacitance and compare to $G\Omega$ limit. Select the lower of the two limits. Capacitance and dissipation factor (DF) measured under the following conditions:

1 MHz ± 100 kHz and 1.0 $V_{rms} \pm 0.2$ V if capacitance $\leq 1,000$ pF

1 kHz ± 50 Hz and 1.0 V $_{rms}$ ± 0.2 V if capacitance > 1,000 pF

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

Post Environmental Limits

High Temperature Life, Biased Humidity, Moisture Resistance						
Dielectric	Dielectric Rated DC Voltage Capacitance Value DF (%) Capacitance Shift					
COG	All	All	0.5	0.3% or ±0.25 pF		



Table 1A - C052 Style/Size (0.20" Lead Spacing), Capacitance Range Waterfall

	C052 Style	e/Size (0.20" Lead S	pacing)	
Rated Volt	tage (VDC)	50	100	200
Voltag	e Code	5	1	2
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)		
1pF		109	109	109
1.5pF		159	159	159
2.2pF	D = ±0.5 pF	229	229	229
2.7pF		279	279	279
3.3pF		339	339	339
3.9pF 4.7pF		399 479	399 479	399 479
4.7pF 5.6pF		569	569	569
6.8pF		689	689	689
8.2pF		829	829	829
10pF		100	100	100
12pF		120	120	120
15pF	J = ±5% K = ±10%	150	150	150
18pF		180	180	180
22pF		220	220	220
27pF	G = ±2%	270	270	270
33pF	G = ±2% J = ±5% K = ±10%	330	330	330
39pF		390	390	390
47pF		470	470	470
56pF		560	560	560
68pF		680	680	680
82pF		820 101	820 101	820
100pF 120pF		121	121	101 121
150pF		151	151	151
180pF		181	181	181
220pF	l l	221	221	221
270pF		271	271	271
330pF		331	331	331
390pF		391	391	391
470pF	F = ±1%	471	471	471
560pF	G = ±2%	561	561	561
680pF	J = ±5%	681	681	681
820pF	K = ±10%	821	821	821
1000pF		102	102	102
1200pF		122	122	122
1500pF		152 182	152 182	152 182
1800pF 2200pF		222	222	222
2700pF		272	272	272
3300pF		332	332	LIL
2700pF		272	272	
3300pF		332	332	
3900pF		392	392	
4700pF		472	472	
Rated Volt	tage (VDC)	50	100	200
Voltag	e Code	5	1	2



Table 1B - C062 Style/Size (0.20" Lead Spacing), Capacitance Range Waterfall

	C062 Style	/Size (0.20" Lead S	pacing)	
Rated Vol	tage (VDC)	50	100	200
Voltag	e Code	5	1	2
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)		
3300pF		332	332	332
3900pF		392	392	392
4700pF		472	472	472
5600pF	5 .40	562	562	562
6800pF	F = ±1%	682	682	682
8200pF	G = ±2% J = ±5%	822	822	822
0.01µF	J = ±5% K = ±10%	103	103	103
0.012μF	K - 110%	123	123	
0.015µF		153	153	
0.018µF		183	183	
0.022µF		223	223	
Rated Voltage (VDC)		50	100	200
Voltage Code		5	1	2

Table 1C - C512 Style/Size (0.40" Lead Spacing), Capacitance Range Waterfall

C512 Style/Size (0.40" Lead Spacing)						
Rated Volt	age (VDC)	50	100	200		
Voltag	e Code	5	1	2		
Capacitance	Capacitance Capacitance Tolerance		Capacitance Code (Available Capacitance)			
0.012µF		123	123	123		
0.015μF		153	153	153		
0.018µF		183	183	183		
0.022µF		223	223	223		
0.027μF	F = ±1%	273	273	273		
0.033µF	G = ±2%	333	333	333		
0.039µF	J = ±5%	393	393	393		
0.047µF	K = ±10%	473	473	473		
0.056µF		563	563	563		
0.068µF		683	683	683		
0.082µF		823	823			
0.1µF		104	104			
Rated Volt	Rated Voltage (VDC)		100	200		
Voltag	e Code	5	1	2		



Table 1D - C522 Style/Size (0.40" Lead Spacing), Capacitance Range Waterfall

C522 Style/Size (0.40" Lead Spacing)					
Rated Vo	ltage (VDC)	50	100	200	
Volta	Voltage Code		1	2	
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)			
0.082μF 0.1μF 0.12μF 0.15μF 0.18μF	F = ±1% G = ±2% J = ±5% K = ±10%	823 104 124 154 184	823 104 124 154 184	823 104	
Rated Vo	Rated Voltage (VDC)		100	200	
Volta	Voltage Code		1	2	




Soldering Process

Recommended Soldering Technique:

- · Solder Wave
- Hand Soldering (Manual)


Recommended Soldering Profile:

· Optimum Wave Solder Profile



Hand Soldering (Manual)

Manual Solder Profile with Pre-heating



KEMET recommends following the guidelines and techniques outlined in technical bulletins F2103 and F9207.



Table 2 - Performance & Reliability: Test Methods and Conditions

Stress	Reference	Test or Inspection Method
		Magnification 50 X. Conditions:
Soldorahility	L OTD OOG	a) Method B, 4 hours at 155°C, dry heat at 235°C
Solderability	J-STD-002	b) Method B at 215°C category 3
		c) Method D, category 3 at 260°C
Temperature Cycling	JESD22 Method JA-104	1,000 cycles (-55°C to +125°C), Measurement at 24 hours. +/-2 hours after test conclusion.
5: 111 :15	MIL-STD-202 Method	Load Humidity: 1,000 hours 85°C/85% RH and Rated Voltage. Add 100 K ohm resistor. Measurement at 24 hours. +/-2 hours after test conclusion.
Biased Humidity	103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours. +/-2 hours after test conclusion.
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Unpowered. Measurement at 24 hours. +/-2 hours after test conclusion.
Thermal Shock	MIL-STD-202 Method 107	-55°C/+125°C. Note: Number of cycles required – 300. Maximum transfer time – 20 seconds. Dwell time – 15 minutes. Air – Air.
High Temperature Life	MIL-STD-202 Method 108 /EIA-198	1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 2 X rated voltage applied.
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC, for 1,000 hours.
Vibration	MIL-STD-202 Method 204	5 g for 20 minutes, 12 cycles each of 3 orientations. Note: Use 8"X5" PCB .031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz.
Resistance to Soldering Heat	MIL-STD-202 Method 210	Condition B. No pre-heat of samples. Note: single wave solder – procedure 2.
Terminal Strength	MIL-STD-202 Method 211	Conditions A (2.3 kg or 5 lbs)
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.

Storage & Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature—reels may soften or warp, and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C, and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts, and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability, chip stock should be used promptly, preferably within 1.5 years of receipt.



Packaging Details

Lead Spacing	Component Pitch (P1)
0.100 (2.54)	5.08
0.200 (5.08)	3.81
0.400 (10.16)	7.62
0.170 (4.32)	
0.220 (5.59)	
0.275 (6.98)	
0.300 (7.62)	
0.375 (9.52)	
0.475 (12.06)	
0.575 (14.60)	
0.675 (17.14)	

Packaging Quantities

Style/ Size	Standard Bulk Quantity	Ammo Pack Quantity Maximum	Reel Quantity Maximum (12" Reel)
052	100/Bag	2000	2000
062	100/Bag	1500	1500
512	Can Natal	NI/A	NI/A
522	See Note ¹	N/A	N/A

¹ Quantity varies. For further details, please contact KEMET.

Marking

C052C & C062C STANDARD MARKING

	FRONT	BACK	
Style-	C062	100V	Voltage
Temperature Characteristic	X7B	К —	KEMET
Capacitance, Capacitance Tolerance	104K	0811	Date Code
	100		

C512 & C522 STANDARD MARKING

KEMET C512X7B	KEMET SIZE and Temperature Characteristic
105K 50V 0832	Capacitance, Capacitance Tolerance, Voltage Date Code



KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KEMET:

```
C052C270K2G5CA C052C821F1G5CA C052C820K2G5CA C052C271J2G5CA C062C392F2G5CA
C052C561F1G5CA C052C471J1G5CA C052C272F2G5CA C052C181F2G5CA C052C390J2G5CA
C052C272K1G5CA C052C121F2G5CA C052C821J1G5CA C052C122J1G5CA C052C472G1G5CA
C062C562K2G5CA C052C272F1G5CA C052C151G2G5CA C052C150K2G5CA C052C121G2G5CA
C052C391J1G5CA C052C560J2G5CA C052C180J2G5CA C052C689D2G5CA C062C153J1G5CA7301
C052C390K2G5CA C052C560F2G5CA C052C120J2G5CA C052C182J1G5CA C062C682J1G5CA7301
C062C223F1G5CA7301 C052C270G2G5CA C062C562J1G5CA7301 C052C391F1G5CA C062C103J2G5CA7301
C052C681F1G5CA C062C103J1G5CA7301 C052C820G2G5CA C052C272F5G5CA C052C181J2G5CA
C052C101K1G5CA7301 C052C100K1G5CA7301 C052C102K1G5CA7301 C052C150K1G5CA
C052C150K1G5CA7301 C052C339D2G5CA7301 C052C221J2G5CA C052C820J2G5CA7301
C052C821J2G5CA7301 C052C689D2G5CA7301 C052C391K2G5CA C052C472K1G5CA7301
C052C470K1G5CA7301 C052C470J1G5CA C052C270G2G5CA7301 C052C561K1G5CA C052C681K2G5CA
C052C330G2G5CA7301 C052C561G1G5CA C052C470K1G5CA C052C189D2G5CA C052C829D2G5CA
C052C220K1G5CA C052C150J2G5CA C052C220K2G5CA C052C331K2G5CA C052C391J2G5CA
C052C472J5G5CA7301 C052C560J5G5CA7301 C052C100J1G5CA7301 C052C101J1G5CA7301
C052C102J1G5CA7301 C052C152J1G5CA7301 C052C222G5G5CA C052C460J2G5CA C052C511F1G5CA
C052C100J5G5CA C052C680G2G5CA7301 C052C100J1G5CA C052C471J2G5CA7301 C052C182F1G5CA
C052C470J2G5CA7301 C052C122K2G5CA C052C332K1G5CA C052C510J2G5CA C052C101F2G5CA
C052C100K2G5CA7301 C052C121K2G5CA7301 C052C101K2G5CA7301 C052C181K2G5CA7301
C052C102K2G5CA7301 C052C181K2G5CA C052C470K2G5CA7301 C052C471K2G5CA7301
C052C680F2G5CA7301 C052C560K2G5CA7301 C052C680J1G5CA C052C680J2G5CA C052C560J1G5CA
C052C102K1G5CA
```