G3VM-101BR/ER

MOS FET Relays

Compact, General-purpose, **Analog-switching MOS FET Relays,** with 2-A Switching.

- Continuous load current of 2 A. (Connection C: 4 A)
- Switches minute analog signals.
- Dielectric strength of 2,500 Vrms between I/O.


RoHS compliant

■Application Examples

- Communication equipment
- Test & Measurement equipment
- Security equipment
- Factory Automation equipment
- Power circuit

Note: The actual product is marked differently from the

■ Terminal Arrangement/Internal Connections



Note: The actual product is marked differently from the image shown here.

■List of Models

Package type	Contact form	Terminals	Load voltage (peak value) *	Model	Minimum package quantity	
	Contact form		Load voitage (peak value)	Model	Number per stick	Number per tape and reel
DIP6	1a (SPST-NO)	PCB terminals		G3VM-101BR	50	
		Surface-mounting terminals	100 V	G3VM-101ER	50	
	(31 31-110)			G3VM-101ER (TR)		1,500

^{*} The AC peak and DC value are given for the load voltage.

■ Absolute Maximum Ratings (Ta = 25°C)

Item		Symbol	Rating	Unit	Measurement conditions		
	LED forward current		lF	30	mA		
=	Repetitive peak LED forward current		IFP	1	Α	100 μs pulses, 100 pps	
Input	LED forward current reduction rate		∆IF/°C	-0.3	mA/°C	Ta ≥ 25°C	
=	LED reverse voltage		VR	5	V		
	Connection temp	onnection temperature		125	°C		
	Load voltage (AC peak/DC)		Voff	100	V		
	Continuous load current	Connection A		2	Α	Connection A: AC neels/DC	
		Connection B	lo	2		Connection A: AC peak/DC Connection B and C: DC	
O		Connection C		4		Connection B and O. BO	
Output	ON current reduction rate	Connection A		-20	mA/°C	Ta ≥ 25°C	
₽		Connection B	∆lo/°C	-20			
		Connection C		-40			
	Pulse ON current		lop	6	Α	t = 100 ms, Duty = 1/10	
	Connection temp	erature	TJ	125	°C		
Dielectric strength between I/O (See note 1.)			V _I -O	2500	Vrms	AC for 1 min	
Operating temperature			Ta	-40 to +85	°C	With no icing or condensation	
Storage temperature			Tstg	-55 to +125	°C	With no icing or condensation	
Soldering temperature				260	°C	10 s	

1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.


Connection Diagram

Connection A	1 6 Load 2 5 or AC
Connection B	1 6 Load DC T
Connection C	1 6 Load DC 7

■ Electrical Characteristics (Ta = 25°C)

Item			Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions	l
LED forward voltage		VF	1.18	1.33	1.48	٧	IF = 10 mA	Ī	
Reverse current Capacity between terminals		IR			10	μА	V _R = 5 V	Ī	
Capacity between terminals		Ст		70		pF	V = 0, f = 1 MHz	ı	
Trigger LED forward current		IFT		0.5	3	mΑ	lo = 1 A		
	Maximum	Connection A			100	200	$m\Omega$	$I_F = 5 \text{ mA}, I_O = 2 \text{ A}, t < 1 \text{ s}$	
O	resistance with	Connection B	Ron		50		$m\Omega$	$I_F = 5 \text{ mA}, I_O = 2 \text{ A}, t < 1 \text{ s}$	
Output	output ON	Connection C			25		$m\Omega$	$I_F = 5 \text{ mA}, I_O = 4 \text{ A}, t < 1s$	
두	Current leakage when the relay is open		ILEAK			1.0	μΑ	Voff = 100 V	
	Capacity between terminals		Coff		1000		pF	V = 0, f = 1 MHz	
Capacity between I/O terminals			C _{I-O}		0.8		pF	f = 1 MHz, Vs = 0 V	
Insulation resistance between I/O terminals			Rı-o	1000			$M\Omega$	V _{I-O} = 500 VDC, RoH ≤ 60%	
Turn-ON time			ton		2	5	ms	IF = 5 mA, RL = 200 Ω ,	Ī
Turn-OFF time			toff		0.1	1	ms	V _{DD} = 20 V (See note 2.)	

Note: 2. Turn-ON and Turn-OFF Times




■Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V _{DD}			80	V
Operating LED forward current	lF	5	10	25	mA
Continuous load current (AC peak/DC)	lo			2	Α
Operating temperature	Та	-20		65	ô

■ Engineering Data


LED forward current vs. **Ambient temperature**




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage




On-state resistance vs. Ambient temperature




Trigger LED forward current vs. **Ambient temperature**




Turn ON, Turn OFF time vs. **LED forward current**



Turn ON, Turn OFF time vs. **Ambient temperature**



Current leakage vs. **Ambient temperature**



■Safety Precautions

• Refer to "Common Precautions" for all G3VM models.

■ Appearance


DIP6

DIP (Dual Inline Package)


Ħ OMRON logo **OMRON** -101BR Model name 0 Pin 1 mark 932 Lot No.

Note: The actual product is marked differently from the image shown here.

■ Dimensions (Unit: mm)




PCB Terminals




Note: The actual product is marked differently from the image shown here.

Surface-mounting Terminals Weight: 0.4 g




PCB Dimensions (Bottom View)



Actual Mounting Pad Dimensions

(Recommended Value, Top View)



Note: Do not use this document to operate the Unit.

Contact: www.omron.com/ecb

Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
 Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad

systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

G3VM-101BR G3VM-101ER G3VM-101ER (TR) G3VM-101ER(TR)