


PART NUMBER		IFL-LX161F	REV	B
REV	E.C.N. NUMBER AND REVISION COMMENTS		DATE	
A	E.C.N. #11148		12.27.06	
B	ECN-Lumex202000041		04.30.20	




ELECTRO-OPTICAL SPECIFICATIONS

PARAMETER	VALUE	UNITS
OPERATING VOLTAGE	12~16	V
DESIGN VOLTAGE	14	V
CURRENT DRAW @ DESIGN VOLTS	190	mA
M.S.C.P.@ DESIGN VOLTS	1.0	-
AVERAGE LIFE@ DESIGN VOLTS	4000	HR

MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION
BULB SIZE AND SHAPE	T-10 TUBULAR
LENS	CLEAR GLASS
BASE OR LEAD FINISH	WEDGE
FILAMENT SHAPE	C-2F

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= ^{+DECIMAL PRECISION}/_{-0.00} MAX.= ^{+0.00}/_{-DECIMAL PRECISION}

 <p>425 N. GARY AVE. CAROL STREAM, IL 60188 PHONE : 800-278-5666 FAX : 630-315-2150 WEB : WWW.LUMEX.COM</p>	T-3 1/4(T10*27mm) ALL GLASS WEDGE BASE LAMP, CLEAR GLASS LENS.		DATE : 2020.04.30	DRAWN BY : E.C.
	THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE.		PAGE : 1 OF 1	CHKD BY : E.C.
	CONFIDENTIAL INFORMATION THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.		SCALE : NTF	APRVD BY : G.Y.
			UNIT : mm [INCH]	(No)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumex:](#)

[IFL-LX161F](#)