


DC Film Capacitors MKT Radial Potted Type



FEATURES

15 mm to 27.5 mm lead pitch.
 Supplied loose in box and taped on reel





ROHS COMPLIANT HALOGEN FREE


APPLICATIONS

Blocking and coupling, bypass and energy reservoir

QUICK REFERENCE DATA	
Capacitance tolerance	± 10 %, ± 5 %
Capacitance range (E12 series)	0.047 μF to 15 μF
Rated DC voltage	100 V, 250 V, 400 V, 630 V
Rated AC voltage	63 V, 160 V, 220 V, 250 V
Climatic testing class (according to IEC 60068-1)	55/105/56
Rated temperature	85 °C
Maximum application temperature	105 °C
Performance grade	Grade 1 (long life)
Leads	Tinned wire
Reference standards	IEC 60384-2
Dielectric	Polyester film
Electrodes	Metallized
	Mono construction
Construction	
Encapsulation	Flame retardant plastic case and epoxy resin (UL-class 94 V-0)
Marking C-value; tolerance; rated voltage; manufacturer's symbol; year and week of manufacturer; manufacturer's type	

Note

For more detailed data and test requirements, contact <u>dc-film@vishay.com</u>





55

56

45

46

COMPOSITION OF CATALOG NUMBER

Taped on reel (1)

TY	PE AND	PITCHES				ACITANCE merically)				MULTIF (nF	
		15.0 mr	n		(IIu	inerically)				· ·	<u>* </u>
373		22.5 mr	n							0.1	2
		27.5 mr	n							1	3
	<u> </u>		'							10	4
									[100	5
								ample: 1 = 10 x 10	= 100 nF	,	
		BFC	2	373	×	X	Y	Υ	Υ		
		2222	(*)	373	X	X	Y	Υ	Υ		
		(*) Old orde	ering nun	nber							
TYPE	РΔ	CKAGING	ΙFAD	CONFIGURA	TION				EFERRED T		
=					_	C-TOL.		100 V	250 V	400 V	630 V
	Lo	ose in box	5.0	Lead length $0 \text{ mm} \pm 1.0 \text{ m}$	m	± 10 %		23 24	43 44	53 54	63 64
373				l ⁽¹⁾ = 18.5 mm		± 10 %		27	47	57	67
compact	Таре	ed on reel (1)	F	P ₀ = 12.7 mm diameter = 356		± 10 %		28	48	58	68
	1 .			Lead length		± 10 %		21	41	51	
373	Lo	ose in box	5.0	0 mm ± 1.0 m	m	± 5 %		22	42	52	
	1			(1)	_	· · · · · · · · · · · · · · · · · · ·	1		1		-

± 10 %

±5%

25

26

Note

standard

 $H^{(1)} = 18.5 \text{ mm}$

 $P_0 = 12.7 \text{ mm}$ Reel diameter = 356 mm

SPECIFIC REFERENCE DATA				
DESCRIPTION				
Tangent of loss angle:	at 1 kHz	at	10 kHz	at 100 kHz
C ≤ 0.1 µF	≤ 75 x 10 ⁻⁴	≤1	30 x 10 ⁻⁴	≤ 250 x 10 ⁻⁴
0.1 μF < C ≤ 0.47 μF	≤ 75 x 10 ⁻⁴	≤ 1	30 x 10 ⁻⁴	≤ 300 x 10 ⁻⁴
0.47 μF < C ≤ 1.0 μF	≤ 75 x 10 ⁻⁴	≤ 1	30 x 10 ⁻⁴	=
1.0 μF < C ≤ 10 μF	$\leq 75 \times 10^{-4}$	≤ 1	50 x 10 ⁻⁴	-
C > 10 µF	≤ 75 x 10 ⁻⁴		-	
Rated voltage pulse slope (dU/dt) _R at	100 V _{DC}	250 V _{DC}	400 V _{DC}	630 V _{DC}
P = 15 mm	14 V/μs	16 V/μs	34 V/µs	90 V/μs
P = 22.5 mm	5 V/μs	7 V/µs	14 V/µs	35 V/µs
P = 27.5 mm	4 V/μs	6 V/μs	12 V/µs	30 V/µs
R between leads, for C ≤ 0.33 µF				
at 100 V; 1 min	$>$ 15 000 M Ω	$>$ 15 000 M Ω	> 30 000 MΩ	
at 500 V; 1 min				> 30 000 MΩ
RC between leads, for C > 0.33 µF				
at 100 V; 1 min	> 5000 s	> 10 000 s	> 10 000 s	
at 500 V; 1 min				> 10 000 s
R between interconnecting leads and case (foil method)		> 30	Ω 000 ΜΩ	
Withstanding (DC) voltage (cut off current 10 mA) ⁽¹⁾ ; rise time ≤ 1000 V/s	160 V; 1 min	400 V; 1 min	640 V; 1 min	1008 V; 1 min
Withstanding (DC) voltage between leads and case	200 V; 1 min	500 V; 1 min	800 V; 1 min	1260 V; 1 min
Maximum application temperature			105 °C	

Note

⁽¹⁾ For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139

⁽¹⁾ See "Voltage Proof Test for Metallized Film Capacitors": www.vishay.com/doc?28169



				CA.	TALOG NUMBER B	FC2 373 XXYYY ANI	D PACKAGING	
				LOOSE	IN BOX	REEL	(1)(2)	C-VALUE
U _{RDC}	CAP.	Wynyi	MASS	I _t = 5.0 mm	n ± 1.0 mm	H = 18.5 mm;	P ₀ = 12.7 mm	
(V)	(μ F)		(g) ⁽³⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	Ī
				XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	YYY
			U _{RAC} =	63 V; PITCH = 15.0	mm ± 0.4 mm; d _t =	0.60 mm ± 0.06 mm	1	
	0.33							334
	0.39							394
	0.47							474
	0.56							564
	0.68	F 0 v 11 0 v 17 F	4.4	23	24	27	28	684
	0.82	5.0 x 11.0 x 17.5	1.1	(1000)	(1000)	(1100)	(1100)	824
	1.0							105
100	1.2							125
100	1.5							155
	1.8							185
	2.2	6.0 x 12.0 x 17.5	1.5	23 (1000)	24 (1000)	27 (900)	28 (900)	225
			U _{RAC} =	63 V; PITCH = 15.0	mm ± 0.4 mm; d _t =	0.80 mm ± 0.08 mm	1	
	2.7	70105175	0.0	23	24	27	28	275
-	3.3	7.0 x 13.5 x 17.5	2.0	(1000)	(1000)	(800)	(800)	335
	3.9	85 v 15 0 v 17 5	0.7	23	24	27	28	395
	4.7	8.5 x 15.0 x 17.5	2.7	(1000)	(1000)	(650)	(650)	475
			U _{RAC} =	160 V; PITCH = 15.0	mm ± 0.40 mm; d _t	= 0.60 mm ± 0.06 m	m	
	0.15							154
	0.18	0.22 5.0 x 11.0 x 17.5 1.1		43 (1000)			48 (1100)	184
	0.22		1.1		44 (1000)	47 (1100)		224
	0.27							274
	0.32							334
	0.39	6 0 v 10 0 v 17 5	1 5	43	44	47	48	394
	0.47	6.0 x 12.0 x 17.5	1.5	(1000)	(1000)	(900)	(900)	474
			U _{RAC} =	160 V; PITCH = 15.0	mm ± 0.40 mm; d _t	= 0.80 mm ± 0.08 m	m	
	0.56	7.0 x 13.5 x 17.5	2.0	43	44	47	48	564
	0.68	7.0 × 10.5 × 17.5	2.0	(1000)	(1000)	(800)	(800)	684
	0.82	8.5 x 15.0 x 17.5	2.7	43	44	47	48	824
250	1.0	0.0 x 10.0 x 17.5	۷.1	(1000)	(1000)	(650)	(650)	105
	1.2	10.0 x 16.5 x 17.5	3.5	43	44	47	48	125
				(500)	(500)	(600)	(600)	
	1 5	1	URAC =			= 0.80 mm ± 0.08 mr		155
	1.5	8.5 x 18.0 x 26.0	4.5	43 (200)	44 (200)	47 (450)	48 (450)	155
	1.8			· , ,	` ,	` ,	. ,	185
	2.2	10.0 x 19.5 x 26.0	5.7	43 (200)	44 (200)	47 (350)	48 (350)	225
	2.7		Unia -	` ,	` '	= 0.80 mm ± 0.08 mr		275
				43	44	- 5.55 mm ± 6.66 mm	••	
	3.3	11.0 x 21.0 x 31.0	8.2	(100)	(100)	-	<u>-</u>	335
	3.9	13.0 x 23.0 x 31.0	10.2	43	44			395
	4.7	10.0 A 20.0 A 01.0	10.2	(100)	(100)] -	-	475



ELEC	TRICA	L DATA - COM	IPACT	SIZE				
				CA ⁻	TALOG NUMBER B	FC2 373 XXYYY ANI	D PACKAGING	
				LOOSE	IN BOX	REEL	(1)(2)	
U _{RDC}	CAP.	DIMENSIONS wxhxl	MASS	l _t = 5.0 mm	n ± 1.0 mm	H = 18.5 mm;	P ₀ = 12.7 mm	C-VALUE
(V)	(μ F)	(mm)	(g) ⁽³⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	
				XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	YYY
			U _{RAC} =	220 V; PITCH = 15.0	0 mm ± 0.4 mm; d _t :	= 0.60 mm ± 0.06 mr	n	
	0.047 0.056 0.068 0.082 0.10 0.12 0.15	5.0 x 11.0 x 17.5	1.1	53 (1000)	54 (1000)	57 (1100)	58 (1100)	473 563 683 823 104 124 154
	0.18	6.0 x 12.0 x 17.5	1.5	53	54	57	58	184
	0.22	0.0 X 12.0 X 17.0		(1000)	(1000)	(900)	(900)	224
	0.27		U _{RAC} =	220 V; PITCH = 15.0	0 mm ± 0.4 mm; d _t :	= 0.80 mm ± 0.08 mr 57	n 58	274
	0.27	7.0 x 13.5 x 17.5	2.0	(1000)	(1000)	(800)	(800)	334
400	0.39	8.5 x 15.0 x 17.5	2.7	53	54	57	58	394
	0.47	0.5 X 15.0 X 17.5	2.1	(1000)	(1000)	(650)	(650)	474
	0.56	10.0 x 16.5 x 17.5	3.5	53 (500)	54 (500)	57 (600)	58 (600)	564
	0.68	-	U _{RAC} =			= 0.80 mm ± 0.08 mr		684
	0.82	8.5 x 18.0 x 26.0	4.5	53 (200)	54 (200)	57 (450)	58 (450)	824
	1.0	10.0 10.5 00.0	F 7	53	54	57	58	105
	1.2	10.0 x 19.5 x 26.0	5.7	(200)	(200)	(350)	(350)	125
		_	U _{RAC} =			= 0.80 mm ± 0.08 mr	n	1
	1.5	11.0 x 21.0 x 31.0	8.2	53 (100)	54 (100)	-	-	155
	1.8 2.2	13.0 x 23.0 x 31.0	10.2	53 (100)	54 (100)	-	-	185 225
			U _{RAC} =	250 V; PITCH = 15.0	0 mm ± 0.4 mm; d _t :	= 0.60 mm ± 0.06 mr	n	
	0.047 0.056	5.0 x 11.0 x 17.5	1.1	63 (1000)	64 (1000)	67 (1100)	68 (1100)	473 563
	0.068 0.082	6.0 x 12.0 x 17.5	1.5	63 (1000)	64 (1000)	67 (900)	68 (900)	683 823
			U _{RAC} =	250 V; PITCH = 15.0	0 mm ± 0.4 mm; d _t :	= 0.80 mm ± 0.08 mr	n	
	0.10	7.0 x 13.5 x 17.5	2.0	63	64	67	68	104
	0.12 0.15			(1000) 63	(1000) 64	(800) 67	(800) 68	124 154
	0.13	8.5 x 15.0 x 17.5	2.7	(1000)	(1000)	(650)	(650)	184
630	0.22	10.0 x 16.5 x 17.5	3.5	63 (500)	64 (500)	67 (600)	68 (600)	224
	0.07	_	U _{RAC} =			= 0.80 mm ± 0.08 mr		074
	0.27 0.33	8.5 x 18.0 x 26.0	4.5	63 (200)	64 (200)	67 (450)	68 (450)	274 334
	0.39 0.47	10.0 x 19.5 x 26.0	5.7	63 (200)	64 (200)	67 (350)	68 (350)	394 474
	5.71	1	U _{RAC} =			= 0.80 mm ± 0.08 mr		1 717
	0.56	11.0 x 21.0 x 31.0	8.2	63 (100)	64 (100)	-	-	564
	0.68 0.82	13.0 x 23.0 x 31.0	10.2	63 (100)	64 (100)	-	-	684 824
	1.00	15.0 x 25.0 x 31.5	13.4	63 (100)	64 (100)			105

Notes

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139

(3) Weight for short lead product only

Revision: 08-Sep-16 4 Document Number: 28193



		AL DATA - STA			TALOG NUMBER R	FC2 373 XXYYY AN	D BVCKVGING	
				LOOSE		REEL		<u> </u>
U _{RDC}	С	DIMENSIONS	MASS	I _t = 5.0 mm			P ₀ = 12.7 mm	C-VALUE
(V)	(μF)	w x h x l	(g) ⁽³⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-VALUE
		(mm)		XX	XX	XX	XX XX	
				(SPQ)	(SPQ)	(SPQ)	(SPQ)	YYY
		•	U _{RAC} =	63 V; PITCH = 15.0	mm ± 0.4 mm; d _t =	0.60 mm ± 0.06 mm	n	II.
	0.33							334
	0.39			21	22	25	26	394
	0.47	5.0 x 11.0 x 17.5	1.1	(1000)	(1000)	(1100)	(1100)	474
	0.56				, ,	,	,	564
	0.68							684
	0.82	6.0 x 12.0 x 17.5	1.5	21 (1000)	22 (1000)	25 (900)	26 (900)	824
	1.00			(1000) : 63 V; PITCH = 15.0	. ,	` ,	` '	105
	1.2		URAC =	21	22	25	26	125
	1.5	7.0 x 13.5 x 17.5	2.0	(1000)	(1000)	(800)	(800)	155
	1.8			21	22	25	26	185
100	2.2	8.5 x 15.0 x 17.5	2.7	(1000)	(1000)	(650)	(650)	225
		1	U _{RAC} =	63 V; PITCH = 22.5	mm ± 0.4 mm; d _t =	0.80 mm ± 0.08 mm	n	1
	2.7	8.5 x 18.0 x 26.0	4.5	21	22	25	26	275
	3.3	6.5 X 16.0 X 26.0	4.5	(200)	(200)	(450)	(450)	335
	3.9	10.0 x 19.5 x 26.0	5.7	21	22	25	26	395
	4.7	10.0 X 10.0 X 20.0		(200)	(200)	(350)	(350)	475
		T	U _{RAC} =	63 V; PITCH = 27.5	mm ± 0.4 mm; d _t =	: 0.80 mm ± 0.08 mn	n	_
	5.6	11.0 x 21.0 x 31.0	8.2	21	22	-	-	565
	6.8			(100)	(100)			685
	8.2	13.0 x 23.0 x 31.0	10.2	21 (100)	22 (100)	-	-	825
	10 12			` ′				106 126
	15	18.0 x 28.0 x 31.5	18.4	21 (100)	22 (100)	-	-	156
	10		Upac =	160 V; PITCH = 15.0	, ,	= 0.60 mm ± 0.06 m	m	100
	0.15		- NAC					154
	0.18	5.0 x 11.0 x 17.5	1.1	41	42	45	46	184
	0.22			(1000)	(1000)	(1100)	(1100)	224
	0.27							274
	0.33	6.0 x 12.0 x 17.5	1.5	41	42	45	46	334
	0.39	0.0 x 12.0 x 17.5	1.5	(1000)	(1000)	(900)	(900)	394
	0.47							474
	0.50	 	U _{RAC} =	160 V; PITCH = 15.0				F0.4
	0.56	7.0 x 13.5 x 17.5	2.0	41 (1000)	42 (1000)	45 (800)	46	564
250	0.68			(1000)	(1000)	` ,	(800)	684
250	0.82 1.0	8.5 x 15.0 x 17.5	2.7	41 (1000)	42 (1000)	45 (650)	46 (650)	824 105
	1.0		Upac =	160 V; PITCH = 22.5	, ,	` ,	, ,	100
	1.2			41	42	45	46	125
	1.5	1 8 5 x 18 0 x 26 0	4.5	(200)	(200)	(450)	(450)	155
	1.8	100 105 000		41	42	45	46	185
	2.2	10.0 x 19.5 x 26.0	5.7	(200)	(200)	(350)	(350)	225
			U _{RAC} =	160 V; PITCH = 27.5	5 mm ± 0.4 mm; d _t :	= 0.80 mm ± 0.08 m	m	•
	2.7	13.0 x 23.0 x 31.0	10.2	41	42	-	_	275
	3.3	10.0 A 20.0 X 31.0	10.2	(100)	(100)	-	-	335
	3.9	15.0 x 28.0 x 31.5	13.4	41	42			395
	4.7	10.0 1 20.0 101.0	10.4	(100)	(100)			475

Revision: 08-Sep-16 5 Document Number: 28193



Vishay BCcomponents

						FC2 373 XXYYY AN	D PACKAGING					
		DIMENSIONS wxhxl		LOOSE		REEL						
U _{RDC}	C (v.E)		MASS	l _t = 5.0 mm		H = 18.5 mm;		C-VALUE				
(V)	(μ F)	(mm)	(g) ⁽³⁾	C-TOL. = ± 10 %	C-TOL. = ± 5 %	C-TOL. = ± 10 %	C-TOL. = ± 5 %					
				XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	YYY				
			U _{RAC} =	220 V; PITCH = 15.0	0 mm ± 0.4 mm; d _t :	= 0.60 mm ± 0.06 mi	m					
	0.047							473				
	0.056							563				
	0.068	5.0 x 11.0 x 17.5	1.1	51 (1000)	52 (1000)	55 (1100)	56 (1100)	683				
	0.082			(1000)	(1000)	(1100)		823				
	0.10							104				
Ī	0.12	6.0 x 12.0 x 17.5 1.5	0.0 40.0 47.5	0.010.017.5	00 100 175	0.0 10.0 17.5	4.5	51	52	55	56	124
	0.15		1.5	(1000)	(1000)	(900)	(900)	154				
			U _{RAC} =	220 V; PITCH = 15.0	0 mm ± 0.4 mm; d _t :	= 0.80 mm ± 0.08 mi	m					
Ī	0.18	70 105 175	10.517.5	51	52	55	56	184				
	0.22	7.0 x 13.5 x 17.5	2.0	(1000)	(1000)	(800)	(800)	224				
400	0.27	05 450 475		51	52	55	56	274				
	0.33	8.5 x 15.0 x 17.5	2.7	(1000) (1000)		(650)	(650)	334				
			U _{RAC} =	220 V; PITCH = 22.	5 mm ± 0.4 mm; d _t :	= 0.80 mm ± 0.08 mi	n					
Ī	0.39	0.510.000.0	4.5	51	52	55	56	394				
	0.47	8.5 x 18.0 x 26.0	4.5	(200)	(200)	(450)	(450)	474				
Ī	0.56	100 105 000		51	52	55	56	564				
	0.68	8 10.0 x 19.5 x 26.0 5.7	(200)	(200)	(350)	(350)	684					
			U _{RAC} =	220 V; PITCH = 27.	5 mm ± 0.4 mm; d _t :	= 0.80 mm ± 0.08 mi	m					
ļ	0.82	10.0 00.0 01.0	40.0	51	52			824				
	1.0 13.0 x 23.0 x 31.0 10.2	10.2	(100)	(100)	-	-	105					
Ţ	1.2	15.0 × 05.0 × 01.5	10.4	51	52			125				
	1.5	15.0 x 25.0 x 31.5	13.4	(100)	(100)	-	-	125				

Notes

SPQ = Standard Packing Quantity

⁽¹⁾ Reel diameter = 356 mm is available on request

⁽²⁾ H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to packaging information: <u>www.vishay.com/doc?28139</u>

⁽³⁾ Weight for short lead product only



Vishay BCcomponents

ELEC	ELECTRICAL DATA - AVAILABLE ON REQUEST									
				C	ATALOG NUMBEI	R BFC2 3	373 XXYYY AND PA	ACKAGING		
U _{RDC}	С	DIMENSIONS wxhxl	MASS	LO	OSE IN BOX		REEL (1)(2)			
(V)	(μ F)	(mm)	(g) ⁽³⁾	I _t = 5.0	mm ± 1.0 mm		Н	= 18.5 mm		
				C-TOL. = ± 10 %	C-TOL. = ± 5 %	SPQ	C-TOL. = ± 10 %	C-TOL. = ± 5 %	SPQ	
			U _{RAC} =	63 V; PITCH = 22	.5 mm ± 0.4 mm;	$d_t = 0.80$	mm ± 0.08 mm			
	1.5	6.0 x 15.5 x 26.0	2.7	90012	90013	300	90018	90019	600	
100	1.8	7.0 x 16.5 x 26.0	3.3	90022	90023	200	90028	90029	550	
100	2.2	7.0 X 10.5 X 20.0	3.3	90002	90003	200	90008	90009	550	
			U _{RAC} =	63 V; PITCH = 27	.5 mm ± 0.4 mm;	$d_t = 0.80$	mm ± 0.08 mm			
	4.7	9.0 x 19.0 x 31.0	6.1	90032	90033	100		-		
	U _{RAC} = 160 V; PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm									
	0.47			90042	90046		90048	90049		
	0.56	6.0 x 15.5 x 26.0	2.7	90052	90053	300	90058	90059	600	
	0.68			90062	90063		90068	90069		
	0.82	7.0 x 16.5 x 26.0	3.3	90072	90073	200	90078	90079	EEO	
250	1.0	7.0 X 16.5 X 26.0	3.3	90082	90083	200	90088	90089	550	
			U _{RAC} =	160 V; PITCH = 27	'.5 mm ± 0.4 mm;	$d_t = 0.80$	mm ± 0.08 mm			
	1.2	9.0 x 19.0 x 31.5	6.1	90172	90173	100				
	1.5	9.0 X 19.0 X 31.5	6.1	90092	90093	100		-		
	1.8	0.0 01.0 01.0	0.0	90102	90103	100				
	2.2	9.0 x 21.0 x 31.0	8.2	90112	90113	100		-		
		-	U _{RAC} =	220 V; PITCH = 22	2.5 mm ± 0.4 mm;	d _t = 0.80	mm ± 0.08 mm			
	0.22	6.0 x 15.5 x 26.0	2.7	90122	90123	300	90128	90129	600	
400	0.27	70 405 600	0.0	90132	90133	000	90138	90139	550	
400	0.33	7.0 x 16.5 x 26.0	3.3	90142	90143	200	90148	90149	550	
			U _{RAC} =	220 V; PITCH = 27	.5 mm ± 0.4 mm;	d _t = 0.80	mm ± 0.08 mm	'		
	0.68	9.0 x 19.0 x 31.5	6.1	90152	90153	100		-		

Notes

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- $^{(2)}$ H = in-tape height; P_0 = sprocket hole distance; for detailed specifications refer to packaging information: $\underline{www.vishay.com/doc?28139}$
- (3) Weight for short lead product only

MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139

Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that stand-off pips are in good contact with the printed-circuit board:


- For pitches ≤ 15 mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

Space Requirements On Printed-Circuit Board

The maximum space for length ($I_{max.}$), width ($w_{max.}$) and height ($h_{max.}$) of film capacitors to take in account on the printed-circuit board is shown in the drawing:

- For products with pitch \leq 15 mm, $\Delta w = \Delta l = 0.3$ mm and $\Delta h = 0.1$ mm
- For products with 15 mm < pitch \leq 27.5 mm, $\Delta w = \Delta l = 0.5$ mm and $\Delta h = 0.1$ mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



SOLDERING

For general soldering conditions and wave soldering profile, we refer to the application note:

"Soldering Guidelines for Film Capacitors": www.vishay.com/doc?28171

Storage Temperature


 T_{stg} = -25 °C to +35 °C with RH maximum 75 % without condensation

Ratings and Characteristics Reference Conditions


Unless otherwise specified, all electrical values apply to an ambient free air temperature of 23 °C \pm 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % \pm 2 %.

For reference testing, a conditioning period shall be applied over 96 h \pm 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.


CHARACTERISTICS




Capacitance as a function of frequency




Capacitance as a function of ambient temperature




Max. DC and AC voltage as a function of temperature



Impedance as a function of frequency







Revision: 08-Sep-16 9 Document Number: 28193




Vishay BCcomponents




Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency





Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency

Compact size





Max. AC voltage as a function of frequency


10⁵

10³


AC Voltage (V)

10²







Max. AC voltage as a function of frequency




Max. AC voltage as a function of frequency




Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency



Max. AC voltage as a function of frequency





Max. AC voltage as a function of frequency



Maximum RMS current (sinewave) as a function of frequency


U_{AC} is the maximum AC voltage depending on the ambient temperature in the curves "Max. RMS voltage and AC current as a function of frequency".





Tangent of loss angle as a function of frequency

Insulation resistance as a function of the ambient temperature (typical curve)



Maximum allowed component temperature rise (ΔT) as a function of the ambient temperature T_{amb} (°C)

	CONDUCTIVITY (G) AS A FUNCTION OF (ORIGINAL) PITCH AND CAPACITOR BODY KNESS IN mW/°C						
W _{MAX.}		HEAT CONDUCTIVITY (mW/°C)					
(mm)	PITCH 15.0 mm	PITCH 22.5 mm	PITCH 27.5 mm				
5.0	10	-	-				
6.0	11	19	-				
7.0	12	21	-				
8.5	16	25	-				
10.0	18	28	-				
11.0	-	-	36				
13.0	-	-	42				
15.0	-	-	48				
18.0	-	-	57				

POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free ambient temperature.


The power dissipation can be calculated according type detail specification "HQN-384-01/101: Technical Information Film Capacitors", www.vishay.com/doc?28147.

The component temperature rise (ΔT) can be measured (see section "Measuring the component temperature" for more details) or calculated by $\Delta T = P/G$:

- ΔT = component temperature rise (°C)
- P = power dissipation of the component (mW)
- G = heat conductivity of the component (mW/°C)

MEASURING THE COMPONENT TEMPERATURE

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded (T_{amb}) and maximum loaded condition (T_C).

The temperature rise is given by $\Delta T = T_C - T_{amb}$.

To avoid radiation or convection, the capacitor should be tested in a wind-free box.

APPLICATION NOTE AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection, as described hereunder. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact: dc-film@vishay.com

To select the capacitor for a certain application, the following conditions must be checked:

- 1. The peak voltage (U_P) shall not be greater than the rated DC voltage (U_{RDC})
- 2. The peak-to-peak voltage (U_{P-P}) shall not be greater than 2√2 x U_{RAC} to avoid the ionization inception level
- The voltage peak slope (dU/dt) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by U_{RDC} and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_{0}^{T} \left(\frac{dU}{dt}\right)^{2} \times \left(dt < U_{RDC} \times \left(\frac{dU}{dt}\right)_{rated}\right)$$

T is the pulse duration.

- 4. The maximum component surface temperature rise must be lower than the limits (see graph "Max. allowed component temperature rise").
- 5. Since in circuits used at voltages over 280 V peak-to-peak the risk for an intrinsically active flammability after a capacitor breakdown (short circuit) increases, it is recommended that the power to the component is limited to 100 times the values mentioned in the table: "Heat Conductivity"
- 6. When using these capacitors as across-the-line capacitor in the input filter for mains applications or as series connected with an impedance to the mains the applicant must guarantee that the following conditions are fulfilled in any case (spikes and surge voltages from the mains included).



Vishay BCcomponents

VOLTAGE CONDITIONS FOR 6 ABOVE					
ALLOWED VOLTAGES	T _{amb} ≤ 85 °C	85 °C < T _{amb} ≤ 105 °C			
Maximum continuous RMS voltage	U _{RAC}	See "Max. AC voltage as function of temperature" per characteristics			
Maximum temperature RMS-overvoltage (< 24 h)	1.25 x U _{RAC}	U _{RAC}			
Maximum peak voltage (V _{O-P}) (< 2 s)	1.6 x U _{RDC}	1.3 x U _{RDC}			

Example


C = 330 nF - 63 V used for the voltage signal shown in next drawing. $U_{P\text{-}P}$ = 40 V; U_P = 35 V; T_1 = 100 μs ; T_2 = 200 μs

The ambient temperature is 35 °C

Checking conditions:

- 1. The peak voltage $U_P = 35 \text{ V}$ is lower than 63 V_{DC}
- 2. The peak-to-peak voltage 40 V is lower than $2\sqrt{2}$ x 40 V_{AC} = 113 U_{P-P}
- 3. The voltage pulse slope (dU/dt) = 40 V/100 μ s = 0.4 V/ μ s This is lower than 60 V/ μ s (see specific reference data for each version)
- 4. The dissipated power is 16.2 mW as calculated with fourier terms The temperature rise for $W_{max.} = 3.5$ mm and pitch = 5 mm will be 16.2 mW/3.0 mW/°C = 5.4 °C This is lower than 15 °C temperature rise at 35 °C, according figure "Max. allowed component temperature rise"
- 5. Not applicable
- 6. Not applicable

Voltage Signal



INSPECTION REQUIREMENTS

General Notes

Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-2 and Specific Reference Data".

GROUP C INSPECTION REQUI	GROUP C INSPECTION REQUIREMENTS							
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS						
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1								
4.1 Dimensions (detail)		As specified in chapters "General Data" of this specification						
4.3.1 Initial measurements	Capacitance Tangent of loss angle: for $C \le 470$ nF at 100 kHz for 470 nF < $C \le 10$ μ F at 10 kHz for $C > 10$ μ F at 1 kHz							
4.3 Robustness of terminations	Tensile and bending	No visible damage						
4.4 Resistance to soldering heat	Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s							



GROUP C INSPECTION REQUI	REMENTS	
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.14 Component solvent resistance	Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: min. 1 h, max. 2 h	
4.4.2 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \le 2$ % of the value measured initially
	Tangent of loss angle	Increase of $\tan \delta$ ≤ 0.005 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF $< C \leq 220$ nF or ≤ 0.015 for: 220 nF $< C \leq 470$ nF and ≤ 0.003 for: $C > 470$ nF Compared to values measured in 4.3.1
SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1		
4.6.1 Initial measurements	Capacitance Tangent of loss angle: for $C \le 470$ nF at 100 kHz for 470 nF < $C \le 10$ µF at 10 kHz for $C > 10$ µF at 1 kHz	No visible damage
4.6 Rapid change of temperature	$\theta A = -55 ^{\circ}C$ $\theta B = +105 ^{\circ}C$ 5 cycles Duration t = 30 min	
4.7 Vibration	Visual examination Mounting: see section "Mounting" of this specification Procedure B4 Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s² (whichever is less severe) Total duration 6 h	No visible damage
4.7.2 Final inspection	Visual examination	No visible damage
4.9 Shock	Mounting: see section "Mounting" of this specification Pulse shape: half sine Acceleration: 490 m/s² Duration of pulse: 11 ms	
4.9.3 Final measurements	Visual examination	No visible damage
	Capacitance	$ \Delta C/C \le 3$ % of the value measured in 4.6.1
	Tangent of loss angle	Increase of tan δ ≤ 0.005 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF $< C \leq 220$ nF or ≤ 0.015 for: 220 nF $< C \leq 470$ nF and ≤ 0.003 for: $C > 470$ nF Compared to values measured in 4.6.1
	Insulation resistance	As specified in section "Insulation Resistance" of this specification



GROUP C INSPECTION REQUIREMENTS				
SUB-CLAUSE NUMBER AND TEST SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B		CONDITIONS	PERFORMANCE REQUIREMENTS	
4.10	Climatic sequence			
4.10.2	Dry heat	Temperature: +105 °C Duration: 16 h		
4.10.3	Damp heat cyclic Test Db, first cycle			
4.10.4	Cold	Temperature: -55 °C Duration: 2 h		
4.10.6	Damp heat cyclic Test Db, remaining cycles			
4.10.6.2	Final measurements	Voltage proof = U _{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over	
		Visual examination	No visible damage Legible marking	
		Capacitance	$ \Delta C/C \le 3$ % of the value measured in 4.4.2 or 4.9.3	
		Tangent of loss angle	Increase of tan δ ≤ 0.005 for: $C \leq 100$ nF or ≤ 0.010 for: 100 nF $< C \leq 220$ nF or ≤ 0.015 for: 220 nF $< C \leq 470$ nF and ≤ 0.005 for: $C > 470$ nF Compared to values measured in 4.3.1 or 4.6.1	
		Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification	
SUB-GI	ROUP C2			
4.11	Damp heat steady state	56 days, 40 °C, 90 % to 95 % RH		
4.11.1 I	nitial measurements	Capacitance Tangent of loss angle at 1 kHz		
4.11.3 F	inal measurements	Voltage proof = U _{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over	
		Visual examination	No visible damage Legible marking	
		Capacitance	$ \Delta C/C \le 5$ % of the value measured in 4.11.1	
		Tangent of loss angle	Increase of tan $\delta \le 0.005$ Compared to values measured in 4.11.1	
		Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification	



GROUP C INSPECTION REQUIREMENTS				
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS		
SUB GROUP C3				
4.12 Endurance	Duration: 2000 h 1.25 x U _{RDC} at 85 °C 0.8 x 1.25 U _{RDC} at 105 °C			
4.12.1 Initial measurements	Capacitance Tangent of loss angle: for $C \le 470$ nF at 100 kHz for 470 nF $< C \le 10$ μ F at 10 kHz for $C > 10$ μ F at 1 kHz			
4.12.5 Final measurements	Visual examination	No visible damage Legible marking		
	Capacitance	$ \Delta C/C \le 5$ % compared to values measured in 4.12.1		
	Tangent of loss angle	Increase of tan δ ≤ 0.005 for: C ≤ 100 nF or ≤ 0.010 for: 100 nF < C ≤ 220 nF or ≤ 0.015 for: 220 nF < C ≤ 470 nF and ≤ 0.003 for: C > 470 nF Compared to values measured in 4.12.1		
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification		
SUB-GROUP C4				
4.13 Charge and discharge	10 000 cycles Charged to U_{RDC} Discharge resistance: $R = \frac{U_R}{C \times 2.5 \times (dU/dt)_R}$			
4.13.1 Initial measurements	Capacitance Tangent of loss angle: for C \leq 470 nF at 100 kHz for 470 nF $<$ C \leq 10 μ F at 10 kHz for C $>$ 10 μ F at 1 kHz			
4.13.3 Final measurements	Capacitance	$ \Delta C/C \le 3$ % compared to values measured in 4.13.1		
	Tangent of loss angle	Increase of tan δ ≤ 0.005 for: C ≤ 100 nF or ≤ 0.010 for: 100 nF < C ≤ 220 nF or ≤ 0.015 for: 220 nF < C ≤ 470 nF and ≤ 0.003 for: C > 470 nF Compared to values measured in 4.13.1		
	Insulation resistance	≥ 50 % of values specified in section "Insulation Resistance" of this specification		

Legal Disclaimer Notice



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.