

BYM13-20 thru BYM13-60, SGL41-20 thru SGL41-60

Vishay General Semiconductor

Surface Mount Schottky Barrier Rectifier



DO-213AB

1.0 A

20 V to 60 V

30 A

0.50 V, 0.70 V

125 °C, 150 °C

PRIMARY CHARACTERISTICS

 $I_{F(AV)}$

V_{RRM}

I_{FSM}

 V_{F}

T_J max.

FEATURES

- MELF Schottky rectifier
- Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- Low forward voltage drop
- High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 250 °C
- Solder dip 260 °C, 40 s
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, dc-to-dc converters, and polarity protection applications

MECHANICAL DATA

Case: DO-213AB


Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix for consumer grade, meets JESD 201 class 1A whisker test, HE3 suffix for high reliability grade (AEC Q101 qualified), meets JESD 201 class 2 whisker test

Polarity: Two bands indicate cathode end 1st band denotes device type 2nd band denotes voltage type

MAXIMUM RATINGS ($T_A = 25 \text{ °C}$ unless otherwise noted)							
PARAMETER	SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT
Denotes Schottky devices: 1st band is orange		SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Polarity color bands (2nd band) voltage type		Gray	Red	Orange	Yellow	Green	
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	V
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	V
Maximum average forward rectified current (Fig. 1)	I _{F(AV)}	1.0				А	
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	30					А
Voltage rate of change (rated V _R)	dV/dt	10 000				V/µs	
Operating junction temperature range	ТJ	- 55 to + 125 - 55 to + 150			°C		
Storage temperature range	T _{STG}	- 55 to + 150 °C			°C		



For technical questions within your region, please contact one of the following: PDD-Americas@vishay.com, PDD-Asia@vishay.com, PDD-Europe@vishay.com



ROHS COMPLIANT Vishay General Semiconductor



ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)												
PARAMETER	TEST CONDITIONS		SYMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	UNIT			
FARAMETER	1251 0	ONDITIONS	STMBOL	STMBOL SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	UNIT			
Maximum instantaneous forward voltage ⁽¹⁾	1.0 A		V _F	0.50		0.70		V				
Maximum reverse		T = 25 °C		T 25 °C	T 25 °C		0.5			-		
current at rated DC blocking voltage ⁽¹⁾		$T_A = 25 \degree C$ $T_A = 100 \degree C$ I_R		10		5	.0	mA				
Typical junction capacitance	4.0 V, 1.0 MHz		CJ	110		80		pF				

Note:

(1) Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	SVMBOL	BYM13-20	BYM13-30	BYM13-40	BYM13-50	BYM13-60	
		SGL41-20	SGL41-30	SGL41-40	SGL41-50	SGL41-60	
Maximum thermal resistance (1)	$R_{\theta JA}$	75					°C/W
	$R_{\theta JT}$	30					0,00

Note:

(1) Thermal resistance junction to terminal, 0.24 x 0.24" (6.0 x 6.0 mm) copper pads to each terminal


ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE				
SGL41-40-E3/96	0.137	96	1500	7" diameter plastic tape and reel				
SGL41-40-E3/97	0.137	97	5000	13" diameter plastic tape and reel				
BYM13-40-E3/96	0.137	96	1500	7" diameter plastic tape and reel				
BYM13-40-E3/97	0.137	97	5000	13" diameter plastic tape and reel				
SGL41-40HE3/96 (1)	0.137	96	1500	7" diameter plastic tape and reel				
SGL41-40HE3/97 (1)	0.137	97	5000	13" diameter plastic tape and reel				
BYM13-40HE3/96 ⁽¹⁾	0.137	96	1500	7" diameter plastic tape and reel				
BYM13-40HE3/97 (1)	0.137	97	5000	13" diameter plastic tape and reel				

Note:

(1) Automotive grade AEC Q101 qualified

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)






Figure 2. Maximum Non-Repetitive Peak Forward Surge Current

For technical questions within your region, please contact one of the following: <u>PDD-Americas@vishay.com</u>, <u>PDD-Asia@vishay.com</u>, <u>PDD-Europe@vishay.com</u>



BYM13-20 thru BYM13-60, SGL41-20 thru SGL41-60

Vishay General Semiconductor




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance





Figure 4. Typical Reverse Characteristics





¹st band denotes type and positive end (cathode)



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.