



RoHS

# Specification

Client Name :

客户名称 : \_\_\_\_\_

Client P/N :

客户品号 : \_\_\_\_\_

Product P/N :

产品型号 : HL-C3535F9V395-D1-LVR9(Au120)

Sending Date :

送样日期 : \_\_\_\_\_

Client approval 客户审核		Hongli approval 鸿利光电审核		
Approval 核准	Audit 确认	Approval 核准	Audit 确认	Confirmation 制作
				张强
<input type="checkbox"/> Qualified 接受	<input type="checkbox"/> Disqualified 不接受	DATE: 日期 : 2016. 5. 16		

Adr : NO.1,Xianke Yi Road,Huadong Town,, Huadu District, Guangzhou, China

地址 : 中国广州市花都区花东镇先科一路1号

Tel/电话 : 020-86733333 Fax/传真 : 020-86733883 86733938 86733265

Web/网址 : www.honglitronic.com

注:1. 此规格书以中英文方式书写,若有冲突以中文版本为准文本.

2. 此规格书的最终解释权归广州市鸿利光电股份有限公司

3. 此规格书的有效期限为两年,自盖章或签字之日起计算,期满时双方可以续签协议,但应采用书面形式

4.广州市鸿利光电股份有限公司提供样品和规格书请客户会签审核确认规格参数和样品,客户会签后表示认同产品的 相关参数和品质性能符合客户要求。



Under Development	
Mass production	●

## Catalog目录

<b>1. Product naming rules</b>	
产品命名规则	3
<b>2. Features</b>	
特点	3
<b>3. Application range</b>	
应用范围	4
<b>4. Radiation Pattern</b>	
辐射模式	5
<b>5. Absolute Maximum Ratings</b>	
绝对最大额定值	6
<b>6. Typical Optical/Electrical Characteristics Curves</b>	
典型光学/电性特征曲线	7-9
<b>7. Package Dimensions</b>	
封装尺寸	10
<b>8. Welded plate Dimenseions</b>	
焊盘尺寸	10
<b>9.Label</b>	
标签	11
<b>10.Tape Specifications</b>	
包装规格	12
<b>11.Reflow soldering instructions</b>	
回流焊说明	13
<b>12.Use the matters needing attention</b>	
使用注意事项	14-15


Under Development	
Mass production	●

## Product naming rules 产品命名规则

Under Development	●
Mass production	

HL-C 3535 F9 V 395- D 1 LVR9 (Au 120)  
 1 2 3 4 5 6 7 8 9 10 11

- 1：鸿利代码
- 2：产品系列代码
- 3：尺寸代码
- 4：芯片代码
- 5：表示发光颜色为紫外
- 6：表示产品典型峰值波长
- 7：电路设定
- 8：芯片数量
- 9：齐纳
- 10：基板表面镀金
- 11：发光角度120°



**ATTENTION**  
OBSERVE PRECAUTIONS  
FOR HANDLING  
ELECTROSTATIC  
DISCHARGE  
SENSITIVE  
DEVICES


## Features 特点

- Long operating life 寿命长
- High flux 光通量高
- Low voltage DC operated 低电压直流工作
- High heat dissipation efficiency 散热效率高
- Instant light (less than 100ns) 瞬间点亮 (小于100ns)
- Superior ESD protection 良好的静电防护能力
- RoHS compliant 符合RoHS标准
- Demension 尺寸：3.45mm\*3.45mm\*1.85mm



Under Development	<input type="checkbox"/>
Mass production	<input checked="" type="checkbox"/>

### Application range 应用范围



UV 固化  
UV Curing



UV 印刷  
UV Printing



UV 曝光  
UV Exposure



美甲灯  
Nail Polish Curing



防伪  
Security, Banknote





灭蚊灯  
Mosquito Killer



Under Development	<input type="checkbox"/>
Mass production	<input checked="" type="checkbox"/>

### Radiation Pattern 辐射模式



## Absolute Maximum Ratings at Ta=25°C

### 在25°C时绝对极限条件

Parameter参数	Symbol符号	Rating 值	Units单位
power dissipation功率	Pd	2.8	W
Peak Forward Current 正向电流	I <sub>FP</sub>	700	mA
Reverse Voltage方向电压	Vr	5	V
Operating Temperature Range工作温度	Topr	-20°C To +60°C	
Storage Temperature Range储藏温度	Tstg	-0°C To +40°C	

## Typical Optical/Electrical Characteristics @Ta=25°C Type

Symbol符号	Item名称	Min.最低	Typ.典型	Max.最大	Units单位	Test Conditions 测试条件
Φe	Radiation Flux 辐射功率	700	800	—	Mw	IF=500mA
V <sub>F</sub>	Forward Voltage 正向电压	3	—	3.8	V	IF=500mA
λ <sub>P</sub>	Peak Wavelength峰值波长	390	—	400	nm	IF=500mA
2θ <sub>1/2</sub>	50% Power Angle发光角度	—	120	—	deg	IF=500mA
I <sub>R</sub>	Reverse Current反向电流	—	—	50	uA	VR=5V
L70	Life Time 使用寿命 (70%)	—	6000	—	Hour	IF=500mA

#### Notes注:


- 1.Radiant flux measurement tolerance:±10%;
- 2.Forward voltage measurement tolerance:±3%;



## Typical Optical/Electrical Characteristics Curves ( $T_a=25^{\circ}\text{C}$ Unless Otherwise Noted )


典型光学/电性特征曲线 ( $T_a=25^{\circ}\text{C}$  除非另有注释)

### (1) Wavelength Characteristics






## (2) Relative Radiation Flux-IF



## (3) Relative IF-VF









Under Development	
Mass production	●

#### (4) Allowable Forward Current-Ta




#### (5) Radiation Flux-Ta






Under Development	
Mass production	●



**Notes注:**

1. All dimension units are millimeters.  
所有尺寸单位均为毫米.
2. All dimension tolerance is  $\pm 0.2\text{mm}$  unless otherwise noted.  
所有尺寸误差是 $\pm 0.2$ 毫米除非另有说明

**Welded plate Dimensions 焊盘尺寸**





**Notes注:**

When the circuit configuration is not affected, suggested the increase in the middle of the copper area, or the connection between the middle and the pad and the negative electrode can improve the cooling performance of the product. It is recommended to use 1 mm thickness of steel mask.

在不影响电路配置时，建议增加中间焊盘覆铜区域，或中间焊盘和负极焊盘连接，能提高产品散热性能。建议使用热电分离的铜基板作为散热基板。建议使用钢网厚度为1mm。



## Label 标签

		HONGLITRONIC 鸿利光电			
TYPE:		QTY:			
VF:	IF:	ΦV:			
TC:	X/Y:				
SDCM<	Ra>				
DATE:		LOT.NO:			

Label on ESD shielding 静电袋上标签

		HONGLITRONIC (Product Identity Card) 鸿利光电		成品标示卡 	
品名 (Description):					
产品型号 (Type):					
发光颜色 (Color):					
数量 (QTY):					
生产批号 (LOT NO):					
出货日期 (Date):					
操作员 (Operator):					

Label on box 外箱标签

ΦV: Luminous Flux rank 光通量档次范围

VF: Forward voltage rank 正向电压档次范围

TC: Color temperature 色温



SDCM: 相对色容差




Under Development	
Mass production	●

## Tape Specifications(Units:mm)包装规格

### (1)Reel package (1000pcs/reel) 卷轴包装 (1000pcs/卷)




### (2)Moisture resistant packaging 防潮包装





## Reflow soldering instructions 回流焊说明



Profile Feature	Lead-Based solder	Lead-Free Solder
Average Ramp-Rate ( $T_{Smax}$ to $T_p$ )	3°C/second max	3°C/second max
Preheat: Temperature Min ( $T_{Smin}$ )	100°C	110°C
Preheat: Temperature Max ( $T_{Smax}$ )	150°C	160°C
Preheat: Time ( $t_{Smin}$ to $t_{Smax}$ )	60-120 seconds	60-180 seconds
Time Maintained Above: Temperature ( $T_L$ )	183°C	190°C
Time Maintained Above: Time ( $t_L$ )	60-150 seconds	60-150 seconds
Peak/Classification Temperature ( $T_p$ )	215°C	220°C
Time Within 5°C of Actual Peak Temperature ( $t_p$ )	10-15 seconds	20-40 seconds
Ramp-Down Rate	6°C/second max	6°C/second max
Time 25°C to Peak Temperature	6 minutes max	8 minutes max

### Note:

1. recommend to use a convection type reflow machine with 8 zones.  
建议使用八温区回流焊机。
2. recommend to use Lead-Free Paste with a melting point between 170°C-180°C.  
建议使用熔点为170°C-180°C的无铅锡膏。
3. the reflow soldering time should not be more than 400s.  
总的回流焊时间不要超过400s。
4. all temperature means the temperature measured on the surface of the package body.  
所有温度均指在封装本体表面上测得的温度。
5. When using hot plate, the temperature is no more than 220 °C, the time is not more than 60 seconds.  
当使用热板作业时，温度不超过220°C，时间不超过10秒。

## Use the matters needing attention(使用注意事项 )

### 一、储存(storage)：

为避免受潮的影响，我司建议产品在未开包装前储存条件为 5-30°C，相对湿度小于 60%；已开包装的 LED 光源请在 24H 内使用安装完毕，如未用完之产品，请进行除湿并抽真空后密封保存。开封超过一周或湿度卡发生变化时，请务必进行除湿，除湿条件：60°C±5°C，12H；

产品密封保存有效使用期为一年。

To avoid moisture, we recommend storage conditions for the unopened LED +5 ~ +30 °C, relative humidity <60%. LED should be used within 168 Hrs. of opening the package. Please make sure to dehumidify and vacuum pack the remaining/ unused LED. Dehumidifying condition: +120 ° C ± 5 ° C, 04 Hrs. Effective age for the sealed led is one year.

### 二、组装注意事项(the assembly notes)：

焊接条件：此产品必须使用回流焊接的作业方式,回流曲线最高温度不可超过 220°C.作业或存放过程中不可有 1000g 以上的外力或尖锐物体作用于透镜表面（如压力，摩擦等外力以及钳子镊子等工具），以免造成元件损伤；

如果超出此使用条件，鸿利光电将不能保证产品的稳定性，如需使用超出的操作条件，请务必进行风险评估。

Soldering Conditions：This product must be used reflow soldering practices, the maximum temperature of reflow should not exceed 220°C.Please make sure when soldering, there is no external force on the soldering surface (such as pressure, friction or sharp metal nails, etc.), to avoid gold wire deformation or damage and other abnormalities.

If beyond recommended conditions, we cannot guarantee the LED stability, please do the risk assessment first.

### 三、防静电措施(anti-Static Measures)：

请采取足够的措施来防止静电产生，比如带静电环或防静电手指套等；每个制造工程关于产品（工厂、设备、机器、载波机和运输单位）应当连接地面，避免产品电气带电。

Please take adequate measures to prevent electrostatic generation, such as wearing electrostatic ring or anti-static fingerstall etc; any relative products like plant equipment, machinery, carrier and transportation units shall be connected to discharging unit/ ground. After assembly, please make sure to discharge Static Electricity with proper ESD equipment.

### 四、温度控制(temperature Control)：

保证散热前提条件为：TS点（负极焊盘）为80摄氏度以下，在此温度以下，散热符合产品寿命要求；为确保在组装时降低接触热阻，请注意在组装过程中，散热片采用良好品质的导热膏涂布均匀且分布面积合理，不可出现太少或高低不平等现象。散热介质需保证电介质耐压测试至少通过500V。



Under Development	
Mass production	●

Recommended temperature conditions for enhanced product life: TS (Cathode Point) is  $<80^{\circ}\text{C}$  . During assembly, please ensure that a good quality thermal paste is applied and distributed evenly over the surface. While using thermal pad (Heat Sink), make sure LED is firmly tightened and there is no gap between surfaces. The need to ensure the cooling medium dielectric withstand test at least through 500V.

### 五、驱动控制(drive control)：

本产品需使用恒流源进行驱动，且输出电流符合规格书上的功率使用范围，如需使用恒压源或其他使用条件，请进行使用效果风险评估。

Drive this product at constant current. Output current range specifications should be according to the operational and other conditions, as mentioned in data sheet. Before using a constant voltage source or altered specifications, other than recommended, please consider risk factors.


### 六、其他(other)：

本产品不可在以下条件下使用，如果产品在以下条件下使用，评估其使用效果和风险是有必要的：


- 直接或间接的打湿或受潮，比如淋雨等；
- 被海水损害或侵蚀；
- 被暴露于腐蚀性气体(如  $\text{Cl}_2$ ,  $\text{H}_2\text{S}$ 、 $\text{NH}_3$ 、 $\text{SO}_x$ 、 $\text{NO}_x$ 等)；
- 被暴露于粉尘、液体或油；

Product is not suitable to use in following conditions;

- Direct or indirect wet / damp conditions, such as rain, etc;
- in contact with sea water and erosive materials;
- Exposed to corrosive gases (e.g.,  $\text{Cl}_2$ ,  $\text{H}_2\text{S}$ ,  $\text{NH}_3$ ,  $\text{SO}_x$ ,  $\text{NO}_x$ , etc.);
- Exposed to dust, liquids or oils;



OK



NG

### Notes注：

1.\* All high power emitter LED products mounted on aluminum metal-core printed circuit board, can be lighted directly, but we do not recommend lighting the high power products for more than 5 seconds without a appropriate heat dissipation equipment.

所有高功率的发光LED产品安装在铝金属为核心印刷电路板，可直接点亮，但我们不建议在没有一个适当的散热设备时,照明高功率LED点亮超过5秒，

2.Reflow soldering should not be done more than two times.The reflow temperature we recommend is  $260^{\circ}\text{C}$ ,When the temperature exceeds  $260^{\circ}\text{C}$  , the product failure of LED can be caused

回流焊不能超过两次,回流焊最高温度建议 $260^{\circ}\text{C}$ ，当温度超过 $260^{\circ}\text{C}$ 极大可能引起LED产品失效.



修订次数	修订人	修订内容	修订日期	版次
1	张强	新建文件	2016. 5. 16	A/0
2				
3				
4				
5				
6				
7				
8				
9				
10				
11				
12				
13				
14				
15				
16				
17				
18				
19				
20				
21				
22				
23				
24				
25				
26				