



NOTES / Bemerkungen:

1) MATERIAL: PA66-GF25 black, Ultramid A3X2G5 BK
 Material: PA66-GF25 schwarz, Ultramid A3X2G5 BK

2) FLAMMABILITY: UL94: V0
 Brennbarkeit: UL94: V0

3) IP67 RATED ACHIEVED WHEN PROTECTION CAP IS MATED WITH
 M12 CONNECTOR (ACCORDING IEC 61076-2-101)
 AND FIXED WITH LOCKED TORQUE: 0,5 Nm.
 Schutzart IP67 wird erreicht wenn die Schutzkappe
 mit einem M12 Steckverbinder, nach IEC 61076-2-101,
 montiert und mit einem Drehmoment: 0,5 Nm, angezogen wird.

4) TEMPERATURE RANGE: -40°C +115°C
 Temperatur Bereich: -40°C +115°C

QUALITY SYMBOLS ▽A = 0 ▽E = 0 ▽F = 0 ▼ = 0 ▽C = 0 ⊠ = 0 ■ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	EC NO: 102635 DRWN: JELIZAINCIN CHK'D: RSILLER APPR: RSILLER	2016/01/25 2016/02/05 2016/02/05	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE						
			ANGULAR TOL ± 1.0 °		mm	5:1						
			4 PLACES ±	DRWN BY		DATE		ACC PCAP M12 FE OR 9X1				
			3 PLACES ±	JELIZAINCIN		2016/01/25						
			2 PLACES ± 0.05	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING				
	1 PLACE ± 0.1	RSILLER		2016/02/05								
	0 PLACES ± 0.2	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION	SERIES	MATERIAL NUMBER	CUSTOMER				
	A	REV	A3				120358	1203580007				
	DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER							
1203580007		PSD	010	1 OF 1								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1203580007](#)