




Type: ASK/OOK Super-Heterodyne Receiver Module

Model: CY89-XXX

Description:

The CY89 is a ASK/OOK compatible super heterodyne wireless receiving module with high performance for ISM frequency band. With the adoption of European brand RF wireless data transferring/receiver chipsets. The model has a high receiving sensitivity and strong ability of resisting. From wireless signal input to data output can be done without any electrical circuit. User only use extra simple data decode circuit can achieve wireless products development.

CY89 is for industrial level version.



Order Information:

Model NO.	Frequency
CY89-315	315MHz
CY89-433.92	433.92MHz

Features:

- Frequency: 315MHz/433.92MHz (custom frequency is available);
- High sensitivity -110dBm@433.92 1kbps BER10E-2;
- Supply voltage: VCC= 3 to 3.6 V;
- IF band: 230KHz;
- Low power consumption: 3.9mA@315M, 6mA@433.92M.
- Wide operating temperature:-40~85 °C;
- Excellent selectivity and noise rejection;
- Analog RSSI Output ;
- SIL(single in line) small package

Application

- Remote gate controls
- Remote keyless entry
- Car alarm systems
- Wireless security systems
- Automation systems

Pin Description




Figure1 CY89 Shape & Pins

Pin Name	Pin Definition
ANT	RF signal input pin, connect antenna outside(Note1)
VCC	Connect to positive power supply
DOUT	Data Pin
GND	Connect to negative power supply

Note 1: ANT pin is a 50 ohm antenna input. The length is about:
23cm for 315MHz
17cm for 433.92MHz

**Electrical Characteristics:**

Condition: Ta=25 °C Vcc=5.0V Frequency=315MHz

Parameter	Specification			Unit	Condition
	Min	Typ.	Max		
Frequency Range		315		MHz	Other freq. available
Receiver Sensitivity		-110		dBm	BER=10E-2
Data Rate	0.58	2.4	12	Kbps	Manchester code
Supply Voltage, VDD	3.0		3.6	V	DC
Current		3.9		mA	DC
Operating Temperature	-40		+85	°C	

Condition: Ta=25 °C Vcc=5.0V Frequency=433.92MHz

Parameter	Specification			Unit	Condition
	Min	Typ.	Max		
Frequency Range		433.92		MHz	Other freq available
Receiver Sensitivity		-110		dBm	BER=10E-2
Data Rate	0.58	2.4	12	Kbps	Manchester code
Supply Voltage, VDD	3.0		3.6	V	DC
Current		6.0		mA	DC
Operating Temperature	-40		+85	°C	


Mechanical Size: (Unit: MM)

Figure2 CY89 Dimension

For more information and assistance, please contact us as follows:

CY WIRELESS TECHNOLOGY LIMITED

Add: 1407, Block C, Tairan Building, 8th Tairan Road, Futian District,

Shenzhen, Guangdong Province, China

Website: www.rficy.com

Email: info@rficy.com

sales@rficy.com

www.rficy.com