

# ELECTRICAL

	Product			AL ACCESSORIES Features		Accessory Fo	,
Product  PGA-1100.0010  Diode Logic Unit			Used in installations v and more than one Lit separates the trip path tripped independently Full datasheet and order www.littelfuse.com/pga	PGR-8800 D0920	AF0500 D1000	AF0100	
P1004-XX Versa-Pot  PART NUMBER P1004-199 P1004-174 P1004-175 P1004-95 P1004-16 P1004-15 P1004-14 P1004-12 P1004-13	P1004-95-X P1004-16-X P1004-12-X	VALUE 50 kΩ 100 kΩ 200 kΩ 100 kΩ 500 kΩ 1 M Ω 1.5M Ω 2 M Ω 3 M Ω 5 M Ω	The shaft is slotted for serrated for slip-proof Versa-Knob or Lock Sh two 8 in (20.3 cm) wire (clockwise increase) a	ote time delay adjustment. r screwdriver adjustment and finger adjustment. Accepts naft. May be ordered with	P1004-174 & PHS Series P1004-16 & Series: ERD	P1004-175: P1004-16-X: PM ERDI ERDI TS1 TS6  1004-14, P1004-X: C ORM ORS C TRM TRS	3 TRB TRM
<b>P0700-7</b> Versa-Knob				ed for 0.25 in (6.35 mm) shaft loss industrial black finish.		P1004-XX-(X	)
P0700-8 Lock Shaft						P1004-XX-(X	)
P1004-9 P1004-10 P1004-31 Mini-Pot PART NUMBER P1004-9 P1004-10 P1004-31	VALUE 500kΩ 1MΩ 3MΩ	800	time delay adjustment the timer's center hole mini-mount bracket fo Adjustment by screwd ordered with two 3 in pot (clockwise increas	ial potentiometer for remote t. The shaft extends through to for easy panel mounting. Use r standup mounting of timer. Iriver or mini-knob. May be (7.6 cm) wires soldered to e) and female quick connect ds by adding suffix -X to end of  0.25 W at 55 °C Linear 300° ±5° ±10 % 0.125 in (3.2 mm)	TS	AC1 TS1 54 TS6 SU2000	TS2 TSD7
<b>P0700-21</b> Mini-Knob			Mini-Knob is designed Mini-Pot. Semi-gloss i	for 0.125 in (3.2 mm) shaft of ndustrial black finish.	P1004-9	P1004-10	P1004-31

#### Accessories Electrical

### ELECTRICAL

			ELEC	TRICAL ACC						
	Product			Feature	S		Accessory For			
P0200-19 Heat Sink Compound 2 grams P0200-20 Heat Sink Compound 100 grams			consisting of pr month shelf life	imarily zinc oxi (EOD date on h current, plate	neat sink compound ide and having a 12 the label). P0200-19 ed 2 x 2 in (50.8 x 00-20 mounts	Any 2 x 2 in or flasher.	Any 2 x 2 in (50.8 x 50.8 mm) plated time or flasher.			
P1015-18 Quick Connect Screw Adaptor			modules with 0	1.25 in (6.35 mi als. Screw terr	ned for use with all m) male quick minal accepts ring	male quick o	Modules with 0.25 in (6.35 mm) male quick connect terminals. Consult the individual datasheet to determine compatibility.			
P1015-13 P1015-64 P1015-14 Female Quick Connect Termin	als				le terminals are barrel to provide		Consult individual datasheet to determine compatibility.			
P0400 Time Adjustmer	nt Dials	INCREMENTS								
P0400-12	0.05 - 1 s	0.1 s	Dials for use w	ith remote Ver	sa-Pot and panel	P1004-9	P1004-10 P1004-12			
P0400-86	0.1 - 10 m	1 m	mounted Mini-f	Pot. Reverse so	creen printed on clea		P1004-16 P1004-31			
P0400-82	0.1 - 10 s	1 s	plastic to avoid	damage to pri	inted image.	P1004-95				
P0400-17	1 - 30 s	5 s								
P0400-83	1 - 60 s	10 s								
P0400-27	0 - 10	MRD*								
*Multiplier Referen	nce Dial									
VTPXX VTP (F) FN°	To sureston		The VTP Series mounts on modules with in-line adjustment terminals. Rated at 0.25 W at 55 °C. Available in resistance values from 5 k $\Omega$ to 5 $M\Omega$							
PART NUMBER	R <sub>T</sub> VALUE	RANGE	PART NUMBER	R <sub>T</sub> VALUE	RANGE					
VTP0E	250 kΩ	0.5–20s	VTP3L	2 ΜΩ	0.1–4 m					
VTP1B	0.5 ΜΩ	0.05–3s	VTP4B	3 MΩ	0.05–3 s	Series: TAC				
VTP1C	0.5 ΜΩ	0.1–10s	VTP4F	3 MΩ	0.5–60 s	TS2	TS4 TS6 TSD			
VTP1D	0.5 ΜΩ	0.5–10s	VTP4J	3 MΩ	2–180 s					
VTP2A	1 ΜΩ	0.05–1s	VTP4P	3 MΩ	1–100 m					
VTP2C	1 ΜΩ	0.1–10s	VTP5G	5 MΩ	1–100 s					
VTP2E	1 ΜΩ	0.5–20s	VTP5K	5 MΩ	10–1000 s					
VTP2F	1 ΜΩ	0.5-60s	VTP5N	5 MΩ	0.1–10 m					
VTP2J	1 ΜΩ	2–180s	VTP5P	5 ΜΩ	1–100 m					
VITOCO	1 1 1/1/1	1–100m	VTPDF	50 kΩ	0.5–60 s					
VTP2P VTP3B	1 MΩ 2 MΩ	0.05–3s	VIII DI	00 1112	0.5 00 5					



# ELECTRICAL

			ELEC	TRICAL AC	CESSORIES	3					
	Product		Features				Accessory For				
LPSM003ZXID Indicating Fuse Holder LPSM003Z Non-indicating Fuse Holder			Littelfuse POWR-SAFE Dead Front holders provide optimum protection to personnel for Class CC and Midget-Style fuses. 600 V ac/dc				Class CC and Midget-Style fuses				
OKLK002.T Midget Fuse (2 Amp)			10 x 38 fast acting, high-interrupting capacity, current-limiting type fuse. 600 V ac/500 V dc			FH3P	LPSM003ZXID	LPSM003Z			
			The VRM6048 a								
VRM6048  Voltage Monitor Accessory Module  575 V ac → 460 V ac  L1 ← L1		Voltage  *The VRM6048 mu	If the measured line voltage is 575 V ac, connect as shown and adjust/select the voltage monitor for 460 V ac operation. Molded housing with encapsulated circuitry Surface mount with one #10 (M5 x 0.8) plastic screw. May be DIN-rail mounted using P1023-20 Adaptor. Screw terminals with captive wire clamps for up to No.12 AWG wire40 °C to 70 °C -40 °C to 85 °C 95 % relative, non-condensing Input Output* 600 V ac 480 V ac 575 V ac 460 V ac			Series: PLM PLR PLS TVM TVW (manufactured after December 2003)					
V150LA10	AP (		suppressor, is a is designed to b	, , ,				Any of our products that operate below 150 V ac or 200 V dc.			
				very little mounting space.				ING VOLTAGE			
	MAX. OPERA	TING VOLTAGE	CURRENT 80.20 µs CURRENT WAVE	1MA DC TEST CURRENT  MIN. (V) MAX. (V)		PEAK CLAMPING VOLTAGE WITH 80.20 $\mu$ s WAVE $V_{C}(V) \qquad 1_{PK}(A)$		CAPACITANCE	DISC DIAMETER		
PRODUCT	AC (V)	DC (V)	(A)	MIN. (V)	MAX. (V)	V <sub>C</sub> (V)	1 <sub>PK</sub> (A)		SIZE (MM)		

### **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### Littelfuse:

P0400-12 P0400-86 P0400-27 P0400-82 P0400-17 P0400-83 VTP3B VTP5K VTP3L VTP4P VTP2P VTP4J VTP4F VTP2E VTP2J VTP2A VTP5G VTP1C VTP4B VTPDF VTP1D VTP2C VTP5N VTP1B VTP2F VTP0E VTP5P VRM6048 P1004-10 P0200-19 P0700-21 P0700-7 P0200-20 P0700-409 P0700-8 P1004-95 P1004-12 P1015-64 P1015-13 P1004-16 P1004-16-X P1004-31 P1015-18 P1015-14 P1004-175 P1004-13 P1004-174 P1004-179 P1004-199 P1004-95-X P1004-12-X P1004-15 P1004-9 FH3P