

# Lead-free Green D5V0L4B5S 4 CHANNEL LOW CAPACITANCE BI-DIRECTIONAL TVS ARRAY


#### Features


- Provides ESD Protection per IEC 61000-4-2 Standard: Air – ±30kV, Contact – ±30kV
- 4 Channels of Bi-directional ESD Protection
- Low Channel Input Capacitance
- Typically Used at Portable Electronics, Cellular Handsets and Communication Systems
- Lead Free/RoHS Compliant (Note 1)
- "Green" Device (Note 2)

#### **Mechanical Data**

- Case: SOT353
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish annealed over Alloy 42 leadframe (Lead Free Plating). Solderable per MIL-STD-202, Method 208
- Weight: 0.006 grams (approximate)








Pin Configuration

### Ordering Information (Note 3)




Part Number	Case	Packaging
D5V0L4B5S-7	SOT353	3000/Tape & Reel

Notes: 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. No purposely added lead. Halogen and Antimony free. 2. Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com.

3. For packaging details, go to our website at http://www.diodes.com.

#### **Marking Information**



TB10 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: Z = 2012) M = Month (ex: 9 = September)

Date Code Key												
Year	201	1	2012		2013	20	14	2015		2016	2	2017
Code	Y		Z		А	E	3	С		D		E
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



#### Maximum Ratings @TA = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit	Conditions
Peak Pulse Power Dissipation	PPP	84	W	8/20μs, Per Fig. 2
Peak Pulse Current	IPP	6	A	8/20μs, Per Fig. 2
ESD Protection – Contact Discharge	V <sub>ESD_Contact</sub>	±30	kV	Standard IEC 61000-4-2
ESD Protection – Air Discharge	V <sub>ESD_Air</sub>	±30	kV	Standard IEC 61000-4-2

## **Thermal Characteristics**

Notes:

Characteristic	Symbol	Value	Unit
Package Power Dissipation (Note 5)	PD	200	mW
Thermal Resistance, Junction to Ambient (Note 5)	R <sub>θJA</sub>	625	°C/W
Operating Junction Temperature Range	TJ	-65 to +150	۵°
Storage Temperature Range	T <sub>STG</sub>	-65 to +150	۵°


## Electrical Characteristics @T<sub>A</sub> = 25°C unless otherwise specified


Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
Reverse Working Voltage	V <sub>RWM</sub>	-	-	5.0	V	-
Breakdown Voltage	V <sub>BR</sub>	6	7	8	V	I <sub>R</sub> = 1.0mA
Reverse Leakage Current (Note 6)	IR	-	10	100	nA	V <sub>RWM</sub> = 5V
Clamping Voltage (Note 4)		-	7.0	9.0	V	$I_{PP} = 1A, t_p = 8/20\mu S$
	Vcl	-	8.7	10.7	V	$I_{PP} = 3A, t_p = 8/20\mu S$
	VCL	-	10.5	12.0	V	$I_{PP} = 5A, t_p = 8/20\mu S$
		-	11.5	14.0	V	$I_{PP} = 6A, t_p = 8/20\mu S$
Differential Resistance	R <sub>DIF</sub>	-	0.2	-	Ω	$I_R = 1.0A, t_p = 8/20\mu S$
Channel Input Capacitance	Ст	-	15	20	pF	V <sub>IN</sub> = 0 V, f = 1MHz (Channel to Pin 2)

4. Measured from channel to pin 2; Non-repetitive current pulse per Fig. 2.


5. Device mounted on FR-4 PCB pad layout (2oz copper) as shown on Diodes, Inc. suggested pad layout AP02001, which can be found on our website at http://www.diodes.com.

6. Short duration pulse test used to minimize self-heating effect.











## **Typical Applications**






# Package Outline Dimensions



SOT353						
Dim	Min	Max				
Α	0.10	0.30				
в	1.15	1.35				
С	2.00	2.20				
D	0.65	0.65 Typ				
F	0.40	0.45				
Н	1.80	2.20				
J	0	0.10				
κ	0.90	1.00				
L	0.25	0.40				
М	0.10	0.22				
α	0°	8°				
All Dimensions in mm						

## Suggested Pad Layout



Dimensions	Value (in mm)
Z	2.5
G	1.3
Х	0.42
Y	0.6
C1	1.9
C2	0.65



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDING TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2012, Diodes Incorporated

www.diodes.com

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated: D5V0L4B5S-7