


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1461530050](#)
Status: **Active**
Overview: Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Description: Wi-Fi 6E Flex Cabled Balanced Antenna, 9.00mm Width, 50.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

Documents:

3D Model	Application Specification AS-146153-100-001 (PDF)
Drawing (PDF)	Packaging Specification 1461530100-000 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-146153-100-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Antennas
Series	146153
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	Molex Receptacle 734120110 and other alternatives
Overview	Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee
Product Name	2.4/5GHz Balanced Flex Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Wi-Fi Antenna
UPC	889056310000

Physical

Cable Length	50.00mm
Length	34.90mm
Mounting Style	Adhesive
Net Weight	0.487/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	9.00mm

Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5930
Band#2 F_Start (MHz)	4900
Electrical Connectivity	Cable
Peak Gain (dBi)	3.2 @ 2.4 GHz, 4.25 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>78% @2.4 GHz, >79% @ 5 GHz

Material Info

Reference - Drawing Numbers

Application Specification	AS-146153-100-001
Packaging Specification	1461530100-000
Product Specification	PS-146153-100-001
Sales Drawing	SD-146153-050-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[146153 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[146153-0050](#)