Bussmann 10x38mm Photovoltaic fuses — 1000Vdc, 1-30A



Description

A range 10x38mm, 1000Vdc PV fuses for the protection and isolation of photovoltaic strings. The fuses are specifically designed for use in PV systems with extreme ambient temperature, high cycling and low fault current conditions (reverse current, multi-array fault) string arrays.

Available with four mounting styles for application flexibility.

Basic fuse size

• 10x38mm

Catalog symbols and mounting style

- 1-20A* PV-(amp)A10F
 - (cylindrical)
 - PV-(amp)A10-T
 - (bolt mounting) — PV-(amp)A10-1P
 - (single PCB tab)
 - PV-(amp)A10-2P
 - (dual PCB tab)
 - PV-(amp)10F-CT
 - (In-line with crimp terminals)
- 25-30A** PV10M-(amp) (cylindrical)
 PV10M-(amp)-CT
 - (in-line with crimp terminals)
 - * Ceramic tube construction.
 - ** Melamine tube construction.

Ratings

- Volts: 1000Vdc
- Amps: 1-30A
- Interrupting Rating: 50kA (1-20A)
 20kA (25-30A)
- Time Constant: 1-3ms

Operating class

· gPV and UL PV fuse links

PV Fuse coordination

 With thin film cells and 4", 5" and 6" crystalline silicon cells

Agency information

- · UL Listed to 2579*, Guide JFGA, File E335324
- · IEC 60269-6 (gPV)
- CSA File 53787, Class 1422-30 (1-15A), 20-30A Pending
- CCC (1-20A) (25-30A pending)
- RoHS Compliant
- * Except crimp terminal version that is UL Recognized to UL 2579, Guide JFGA2, File E335324.

Packaging (carton quantity)

- PV-(amp)A10F, PV-(amp)A10T, PV-(amp)A10-_P and PV10M-(amp): 10
- PV-(amp)10F-CT & PV10M-(amp)-CT inline: 180

Features

- Meets UL and IEC photovoltaic standards for global acceptance
- Low watts loss performance for energy efficiency
- Low temperature rise performance for more precise sizing
- In-line crimp terminal version is easy to apply in wire harness construction

Typical applications

- Combiner boxes
- Inverters
- PV Wire harnesses

Recommended fuse holders & fuseclips

Part Number	Description & Date Sheet/Brochure #					
CHPV1IU	1-Pole modular fuse holder with indication # 3185					
CHPV1U	1-Pole modular fuse holder without indication # 3185					
CHPV2IU	2-Pole modular fuse holder with indication # 3185					
CHPV2U	2-Pole modular fuse holder without indication # 3185					
1A3400	PCB Fuseclips # 2131					
HPVDVA	Inline fuse holder assembly # 2157					

Specifications


Catalog Numbers / Configurations				Current	Voltage	Energy Integrals I ² t (A ² s)		Watts Loss (W)		
Cylindrical Ferrule	Bolt Fixing	PCB Fixing Single Pin	PCB Fixing Double Pin	In-line with Crimp Terminal	Rating (Amps)	Rating (Vdc)	Pre- Arcing	Total @ 1000V	0.8l _n	I _n
PV-1A10F	PV-1A10-T	PV-1A10-1P	PV-1A10-2P	PV-1A10F-CT	1	1000	0.15	0.4	0.8	1.5
PV-2A10F	PV-2A10-T	PV-2A10-1P	PV-2A10-2P	PV-2A10F-CT	2	1000	1.2	3.4	0.6	1.0
PV-3A10F	PV-3A10-T	PV-3A10-1P	PV-3A10-2P	PV-3A10F-CT	3	1000	4	11	0.8	1.3
PV-3-5A10F	PV-3-5A10-T	PV-3-5A10-1P	PV-3-5A10-2P	PV-3-5A10F-CT	3.5	1000	6.6	18	0.9	1.4
PV-4A10F	PV-4A10-T	PV-4A10-1P	PV-4A10-2P	PV-4A10F-CT	4	1000	9.5	26	1.0	1.5
PV-5A10F	PV-5A10-T	PV-5A10-1P	PV-5A10-2P	PV-5A10F-CT	5	1000	19	50	1.0	1.6
PV-6A10F	PV-6A10-T	PV-6A10-1P	PV-6A10-2P	PV-6A10F-CT	6	1000	30	90	1.1	1.8
PV-8A10F	PV-8A10-T	PV-8A10-1P	PV-8A10-2P	PV-8A10F-CT	8	1000	3	32	1.2	2.1
PV-10A10F	PV-10A10-T	PV-10A10-1P	PV-10A10-2P	PV-10A10F-CT	10	1000	7	70	1.2	2.3
PV-12A10F	PV-12A10-T	PV-12A10-1P	PV-12A10-2P	PV-12A10F-CT	12	1000	12	120	1.5	2.7
PV-15A10F	PV-15A10-T	PV-15A10-1P	PV-15A10-2P	PV-15A10F-CT	15	1000	22	220	1.7	2.9
PV-20A10F	PV-20A10-T	PV-20A10-1P	PV-20A10-2P	PV-20A10F-CT	20	1000	34	350	2.1	3.6
PV10M-25*	_	_	_	PV10M-25-CT*	25	1000	325	1860**	1.65	2.91
PV10M-30*			—	PV10M-30-CT*	30	1000	536	3360**	1.65	3.31

* Consult factory for availability.


** Total I2t @ 20kA IR.

Dimensions/configurations - mm


Cylindrical PV-(amp)A10F, PV10M-(amp)




Cylindrical with PCB tabs PV-(amp)A10-1P (single pin), PV-(amp)A10-2P (double pin)



Cylindrical with bolt fixings PV-(amp)A10-T



In-line with crimp terminals PV-(amp)A10F-CT (1-20A), PV10M(amp)A-CT (25-30A)



The in-line crimp terminal version can be electrically insulated with customer supplied overmolding or approved heat-shrink.

Operating temperature range

• -40°C to 90°C

Wire range and type

Single conductor, 12-10AWG 75°C/90°C Cu stranded PV

Overmolding temperature parameters

· 233°C for 180 sec Max

Terminals


Crimp terminal for 12-10AWG PV copper conductors

Recommended tools:

Sta-Kon terminal crimping tool, catalog # ERG4002

10x38mm Photovoltaic Fuses 1000Vdc, 1-30A


Time-current characteristics - 1-20A




Available Current, DC - Time Constant < 1ms (Amps)

10x38mm Photovoltaic Fuses 1000Vdc, 1-30A


Temperature derating curves - 1-20A



No additional derating is required for PV fuse links installed in ganged modular fuse holders without spacing between units, provided that the rating used is $>1.56 \times I_{sc}$.



Temperature derating curves - 25-30A



The only controlled copy of this Data Sheet is the electronic read-only version located on the Bussmann Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton's Bussmann Business 114 Old State Road Ellisville, MO 63021 United States www.bussmann.com

© 2014 Eaton All Rights Reserved Publication No. 10121 – BU-SB14107 March 2014 Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

 PV-10A10F
 PV-12A10F
 PV-15A10-1P
 PV-15A10-2P
 PV-15A10F
 PV-15A10-T
 PV-1A10F
 PV-2A10F
 PV-3A10F

 PV-4A10F
 PV-5A10F
 PV-6A10F
 PV-8A10F
 PV-10A10-T
 PV-8A10-T
 PV-5A10-1P
 PV-3A10-T
 PV-3A10-T

 6A10-T
 PV-6A10-2P
 PV-6A10-1P
 PV-3A10-2P
 PV-4A10-1P
 PV-4A10-T
 PV-5A10-T
 PV-4A10-2P
 PV-12A10-T