



MATERIAL SAFETY DATA SHEET

Over-the-Spill® System Absorbents

Page 1 of 2

1. Product and Company Identification

Product Identifier: Over-the-Spill® System Absorbents
General Use: Over-the-Spill® System Absorbents are designed to confine and absorb leaks, drips, over-spray and spills of a broad range of chemicals, which include oil, water, coolants and solvents.

Specific Product Identifier: 4251, 4252, 4253, 4254
Over-the-Spill® System

COMPANY PROFILE:	EMERGENCY TELEPHONE:
Rubbermaid Commercial Products, LLC	INFOTRAC
3124 Valley Avenue	200 North Palmetto Street
Winchester, VA 22601	Leesburg, FL 34748
Customer Service:	24 hrs, 7 days/week
1-800-347-9800	1-800-535-5053

Date of Last Revision: January 18, 2006

2. Composition/Information on Ingredients

<u>Components</u>	<u>wt. %</u>	<u>CAS Registry #</u>
Polypropylene Mat	>97	9003-07-0
Grey or yellow pigment	<0.3	Not available

May contain one or more of the following:

Double Faced Acrylic Adhesive Strip		
Pan High Density		
Polyethylene		9002-88-4
Polypropylene Mesh		9003-07-0
Polyester Yarn		25038-59-9
Polypropylene Film		9003-07-0
Polyethylene Film		9002-88-4

Ink

Aqua Ammonia	1-1.5	1336-21-6
Dimethylethanolamine	1-1.5	108-01-0

OSHA HAZARDOUS COMPONENTS (29 CFR 1910.1200):
EXPOSURE LIMITS 8 hrs. TWA (ppm)
OSHA PEL ACGIH TLV

Polypropylene	N.E.	N.E.
Polyethylene	N.E.	N.E.

N.E. = Not Established

3. Hazards Identification

POTENTIAL HEALTH EFFECTS:

Eye Contact: May cause irritation
Ingestion: No hazard in normal use of product
Inhalation: No hazard in normal use of product
Skin Contact: Not applicable
Chronic: Not applicable

4. First Aid Measures

Eye Contact: Flush with water for 15 minutes.
Consult a physician.

Ingestion: Not applicable

Inhalation: Not applicable

Skin Contact: Not applicable

5. Fire Fighting Measures

Flash Point: Not available **Method:** Not applicable

Auto Ignition Temperature: 825° F (440° C)

Flammable Limits: Not applicable

Conditions of Flammability: Not established

Explosive Properties: Not applicable

Extinguishing Media: Unused form: Not applicable Used form: that which is compatible to liquid(s) absorbed.

Special Fire Fighting Procedures: Wear a self-contained breathing apparatus and refer to absorbed liquid(s) MSDS(s).

Hazardous Combustion Products: Carbon monoxide, carbon dioxide, acrolein, ketones, aldehydes and other unidentified organic compounds may be formed upon combustion.

Unusual Hazards: Refer to absorbed liquid(s) MSDS(s). The Over-the-Spill® System Absorbents do not render liquids nonflammable, neutral or less hazardous.

6. Accidental Release Measures

Spill or Leak Procedures: If material is unused, sweep or pick up and dispose of as a non-hazardous material.

7. Handling and Storage

Handling and Storage Precautions: None

Storage Temperature: Store in a cool, dry place.

Storage Pressure: Not applicable

Shelf Life: Indefinitely - as long as product is kept in a clean, dry place away from direct sunlight.

General: Refer to absorbed liquid(s) MSDS(s). The Over-the-Spill® System Absorbents do not render liquids nonflammable, neutral or less hazardous. The container can be hazardous when empty. Follow label cautions even after the container is empty. Do not re-use empty containers for food, clothing or products for human or animal consumption, or where skin contact can occur.

8. Exposure Controls/Personal Protection

Engineering Controls: None required

PERSONAL PROTECTION

Eyes: Safety glasses with side shields are a good industrial practice

Respirator: Not required.

Gloves: Not normally required. However, use of cloth, canvas or leather gloves is a good industrial practice.

Other: None required.



MATERIAL SAFETY DATA SHEET

Over-the-Spill® System Absorbents

Page 2 of 2

9. Physical and Chemical Properties

Appearance: Available in yellow, some on a holder.
Physical State: Solid
Odor: No odor
Odor Threshold: Not applicable
Vapor Pressure: Not applicable
Vapor Density: Not applicable
Specific Gravity: 0.9
Solubility in Water: Insoluble
Coefficient of Water/Oil Distribution: Not available
pH: Not applicable
Boiling Point: Not applicable
Evaporation Rate: Not applicable
Melting Point: 320° F (160° C)

10. Stability and Reactivity

General: This is a stable material.
Conditions of Reactivity: Not established
Incompatible Materials: Strong oxidizing agents may degrade product over an extended period of time.
Conditions to Avoid: Not applicable
Hazardous Decomposition: When heated, it may emit toxic fumes.
Hazardous Polymerization: Will not occur

11. Toxicological Information

LD50: Not available
LC50: Not available
Carcinogenicity: IARC: Not established
National Toxicology Program: Not established
OSHA: Not established
California Prop 65: No listed ingredient
Reproduction Toxicity: Not available
Teratogenicity: Not available
Mutagenicity: Not available
Synergistic Products: Not available
Irritancy of Product: See Section 3.
Sensitization to Product: Not available

12. Ecological Information

No data available

13. Disposal Considerations

Waste Disposal Method: If unused, no special precautions are necessary. Dispose of in accordance with federal, state and local regulations. In certain types of cleanup applications the nature of the material recovered will classify the resulting spent material as a hazardous component. In such instances the material should be disposed of via an approved hazardous waste disposal service and the appropriate manifesting obtained.

14. Transport Information

DOT (Department of Transportation):
Proper Shipping Name: Not regulated
Hazard Class: Not regulated
Identification Number: Not applicable

15. Regulatory Information

CERCLA (Comprehensive Environmental Response Compensation and Liability Act): No Reportable Quantity
OSHA Hazard Communication Standard, 29 CFR 1910.1200: No listed ingredient
SARA Title III (Superfund Amendments and Reauthorization Act): No listed ingredient
TSCA (Toxic Substances Control Act): Ingredients of this product are on the Inventory list.

16. Other Information

NFPA Hazard Ratings:	Health - 0
none → extreme	Fire - 1
0 → 4	Reactivity - 0

The following is in lieu of all warranties, expressed or implied: All information provided is based on testing and data believed to be accurate.