

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : KLEENEX® Gel Hand Sanitiser

Product code : 6382, 6383

UFI : 6PU7-00A0-W00D-0KSH

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Substance/Mixture : Biocidal product

Recommended restrictions on use : For professional users only.

1.3 Details of the supplier of the safety data sheet

Company name of supplier : Kimberly-Clark Europe Limited

Address : Walton Oaks, Dorking Road
Tadworth
Surrey KT20 7NS
United Kingdom

Telephone : +44 1737 736000

E-mail address of person responsible for the SDS : sdscontact@kcc.com

1.4 Emergency telephone number

Emergency telephone number : +44 1235 239670 (24/7 Service)

Poison Center Name : NHS 111

Poison Center Telephone : 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Flammable liquids, Category 2	H225: Highly flammable liquid and vapour.
Eye irritation, Category 2	H319: Causes serious eye irritation.
Long-term (chronic) aquatic hazard, Category 3	H412: Harmful to aquatic life with long lasting effects.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version 1.20 Revision Date: 29.12.2022 SDS Number: 100000002838 Date of last issue: 23.12.2022
Date of first issue: 16.04.2015

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Danger

Hazard statements : H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H412 Harmful to aquatic life with long lasting effects.

Precautionary statements : **Prevention:**
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P233 Keep container tightly closed.
P273 Avoid release to the environment.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection/ hearing protection.

Response:

P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.
P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Chemical nature : Mixture

Components

Chemical name	CAS-No. EC-No.	Classification	Concentration (% w/w)
---------------	-------------------	----------------	--------------------------

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version 1.20 Revision Date: 29.12.2022 SDS Number: 100000002838 Date of last issue: 23.12.2022
Date of first issue: 16.04.2015

	Index-No. Registration number		
Ethanol	64-17-5 200-578-6 603-002-00-5	Flam. Liq. 2; H225 Eye Irrit. 2; H319	>= 70 - < 90
Tetradecanol	112-72-1 204-000-3	Eye Irrit. 2; H319 Aquatic Chronic 1; H410	>= 1 - < 2.5

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

- General advice : No hazards which require special first aid measures.
- If inhaled : If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.
- In case of skin contact : No hazards which require special first aid measures.
- In case of eye contact : If in eyes, rinse with water for 15 minutes.
If eye irritation persists, consult a specialist.
- If swallowed : Not required under normal use.

4.2 Most important symptoms and effects, both acute and delayed

None known.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : No hazards which require special first aid measures.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media : Alcohol-resistant foam
Dry chemical
Carbon dioxide (CO₂)

- Unsuitable extinguishing media : Water spray jet

5.2 Special hazards arising from the substance or mixture

- Specific hazards during firefighting : Highly flammable liquid and vapour.
- Hazardous combustion products : Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

5.3 Advice for firefighters

- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Standard procedure for chemical fires.
-

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

- Personal precautions : Ensure adequate ventilation.
Remove all sources of ignition.

6.2 Environmental precautions

- Environmental precautions : Do not allow uncontrolled discharge of product into the environment.
- If the product contaminates rivers and lakes or drains inform respective authorities.

6.3 Methods and material for containment and cleaning up

- Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Shovel into suitable container for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

- Advice on safe handling : No special precautions required.
- Advice on protection against fire and explosion : Normal measures for preventive fire protection.
- Hygiene measures : General industrial hygiene practice.

7.2 Conditions for safe storage, including any incompatibilities

- Requirements for storage areas and containers : Keep containers tightly closed in a cool, well-ventilated place.
- Advice on common storage : No materials to be especially mentioned.
- Further information on storage stability : No decomposition if stored and applied as directed.
-

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version 1.20 Revision Date: 29.12.2022 SDS Number: 100000002838 Date of last issue: 23.12.2022
Date of first issue: 16.04.2015

7.3 Specific end use(s)

Specific use(s) : Biocidal product

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
Ethanol	64-17-5	TWA	1,000 ppm 1,920 mg/m ³	GB EH40
Further information: Where no specific short-term exposure limit is listed, a figure three times the long-term exposure limit should be used.				
Glycerol	GLYCERIN	TWA (Mist)	10 mg/m ³	GB EH40
Further information: Where no specific short-term exposure limit is listed, a figure three times the long-term exposure limit should be used.				

8.2 Exposure controls

Personal protective equipment

Eye protection : Not required under normal use.

Hand protection

Remarks : Not required under normal use

Skin and body protection : Not required under normal use.

Respiratory protection : No personal respiratory protective equipment normally required.

Protective measures : No special protective equipment required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state : liquid

Colour : colourless

Odour : alcohol-like

Melting point/range : < -20 °C

Boiling point/boiling range : 85 °C

Upper explosion limit / Upper flammability limit : 15 %(V)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

Lower explosion limit / Lower flammability limit : 3.5 %(V)

Flash point : 14 °C

Auto-ignition temperature : > 425 °C

pH : 8.0

Viscosity
Viscosity, dynamic : 250 mPa.s

Solubility(ies)
Water solubility : partly miscible

Density : 0.833 - 0.843 g/cm³

Relative vapour density : No data available

Particle characteristics
Particle size : No data available

9.2 Other information

Evaporation rate : No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.
No decomposition if stored and applied as directed.

10.2 Chemical stability

Stable
No decomposition if stored and applied as directed.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.
No hazards to be specially mentioned.

10.4 Conditions to avoid

Conditions to avoid : Heat, flames and sparks.

10.5 Incompatible materials

Materials to avoid : Oxidizing agents

10.6 Hazardous decomposition products

Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity

Not classified based on available information.

Components:

Ethanol:

Acute oral toxicity : LD50 (Rat, male and female): 10,470 mg/kg
Method: OECD Test Guideline 401
GLP: no

LD50 Oral (Rat): 7,060 mg/kg

Acute inhalation toxicity : LC50 (Rat, male and female): 124.7 mg/l
Test atmosphere: vapour
Method: OECD Test Guideline 403
GLP: no

Skin corrosion/irritation

Not classified based on available information.

Product:

Result : No skin irritation

Components:

Ethanol:

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation
GLP : yes

Tetradecanol:

Result : No skin irritation

Serious eye damage/eye irritation

Causes serious eye irritation.

Product:

Result : Mild eye irritation

Components:

Ethanol:

Species : Rabbit
Method : OECD Test Guideline 405
Result : Irritation to eyes, reversing within 21 days
GLP : no

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

Tetradecanol:

Species : Rabbit
Result : Eye irritation

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Product:

Remarks : Based on available data, the classification criteria are not met.

Components:

Ethanol:

Species : Mouse
Assessment : Does not cause skin sensitisation.
Method : OECD Test Guideline 429
Result : Did not cause sensitisation on laboratory animals.
GLP : no

Tetradecanol:

Result : Did not cause sensitisation on laboratory animals.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

Product:

Remarks : Not applicable

STOT - repeated exposure

Not classified based on available information.

Product:

Remarks : Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

Aspiration toxicity

Not classified based on available information.

Product:

No aspiration toxicity classification

11.2 Information on other hazards

Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Further information

Product:

Remarks : No data available

SECTION 12: Ecological information

12.1 Toxicity

Components:

Ethanol:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): > 100 mg/l
Exposure time: 96 h
Test Type: static test

LC50 (Pimephales promelas (fathead minnow)): 13,400 - 15,100 mg/l
Exposure time: 96 h
Test Type: flow-through test

Toxicity to daphnia and other aquatic invertebrates : EC50 (Ceriodaphnia dubia (water flea)): 5,012 mg/l
Exposure time: 48 h
Test Type: static test

LC50 (Daphnia magna (Water flea)): 9,268 - 14,221 mg/l
Exposure time: 48 h

Toxicity to algae/aquatic plants : EC50 (Pseudokirchneriella subcapitata (green algae)): 275 mg/l
Exposure time: 72 h
Test Type: static test

Tetradecanol:

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

Toxicity to fish : LC50 (Brachydanio rerio (zebrafish)): > 10,000 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 : 3.2 mg/l
Exposure time: 48 h
Remarks: No toxicity at the limit of solubility

Toxicity to algae/aquatic plants : EC50 (Desmodesmus subspicatus (green algae)): > 10 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC: 0.0016 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Method: OECD Test Guideline 211
GLP: yes

Ecotoxicology Assessment

Acute aquatic toxicity : This product has no known ecotoxicological effects.

12.2 Persistence and degradability

Components:

Ethanol:

Biodegradability : Test Type: aerobic
Inoculum: activated sludge
Biodegradation: 97 %
Exposure time: 28 d
Remarks: Readily biodegradable, according to appropriate OECD test.

12.3 Bioaccumulative potential

Components:

Ethanol:

Bioaccumulation : Bioconcentration factor (BCF): 0.66
Remarks: No bioaccumulation is to be expected (log Pow <= 4).

Tetradecanol:

Partition coefficient: n-octanol/water : log Pow: 5.5

12.4 Mobility in soil

Components:

Ethanol:

Stability in soil : Remarks: Not expected to adsorb on soil.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

Components:

Ethanol:

Assessment : This substance is not considered to be persistent, bioaccumulating and toxic (PBT).. This substance is not considered to be very persistent and very bioaccumulating (vPvB)..

12.6 Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7 Other adverse effects

Product:

Additional ecological information : No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations.

Contaminated packaging : Dispose of as unused product.
Do not re-use empty containers.

Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14: Transport information

14.1 UN number or ID number

ADR : UN 1987

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

IMDG : UN 1987

IATA (Cargo) : UN 1987

14.2 UN proper shipping name

ADR : ALCOHOLS, N.O.S.
(Ethanol)

IMDG : ALCOHOLS, N.O.S.
(Ethanol)

IATA (Cargo) : Alcohols, n.o.s.
(Ethanol)

14.3 Transport hazard class(es)

ADR : 3

IMDG : 3

IATA (Cargo) : 3

14.4 Packing group

ADR
Packing group : III
Classification Code : F1
Hazard Identification Number : 30
Labels : 3
Tunnel restriction code : (D/E)

IMDG
Packing group : III
Labels : 3
EmS Code : F-E, S-D

IATA (Cargo)
Packing instruction (cargo aircraft) : 366
Packing instruction (LQ) : Y344
Packing group : III
Labels : Class 3 - Flammable liquids

14.5 Environmental hazards

ADR
Environmentally hazardous : no

IMDG
Marine pollutant : no

14.6 Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

14.7 Maritime transport in bulk according to IMO instruments

Not applicable for product as supplied.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59) : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances. P5c FLAMMABLE LIQUIDS

34 Petroleum products: (a) gasolines and naphthas, (b) kerosenes (including jet fuels), (c) gas oils (including diesel fuels, home heating oils and gas oil blending streams),(d) heavy fuel oils

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 82.43 %
Volatile CMR compounds: 0 %

15.2 Chemical safety assessment

SECTION 16: Other information

Full text of H-Statements

H225 : Highly flammable liquid and vapour.
H319 : Causes serious eye irritation.
H410 : Very toxic to aquatic life with long lasting effects.

Full text of other abbreviations

Aquatic Chronic : Long-term (chronic) aquatic hazard
Eye Irrit. : Eye irritation
Flam. Liq. : Flammable liquids
GB EH40 : UK. EH40 WEL - Workplace Exposure Limits
GB EH40 / TWA : Long-term exposure limit (8-hour TWA reference period)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



KLEENEX® Gel Hand Sanitiser

Version	Revision Date:	SDS Number:	Date of last issue: 23.12.2022
1.20	29.12.2022	100000002838	Date of first issue: 16.04.2015

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Classification of the mixture:

Flam. Liq. 2	H225
Eye Irrit. 2	H319
Aquatic Chronic 3	H412

Classification procedure:

Based on product data or assessment
Based on product data or assessment
Calculation method

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

GB / EN